



切れ刃形状記号 L

本図は右勝手 (R) を示す。

内径用ホルダ

形番	シャンク材	ϕD_m	ϕD_s	f	L_1	L_2	h	θ°	α°	r_e^{**}	インサート	トルク*
A08H-SCLPR/L06-D100	鋼	10	8	5.5	100	16	7.5	5	-8	0.4	CP**0602...	1.2
A10K-SCLPR/L06-D120	鋼	12	10	6	125	20	9	5	-5	0.4	CP**0602...	1.2
A10K-SCLPR/L08-D120	鋼	12	10	6	125	20	9	5	-5	0.4	CP**0802...	1.4
A12M-SCLPR/L06-D140	鋼	14	12	7	150	24	11	5	-4	0.4	CP**0602...	1.2
A12M-SCLPR/L08-D140	鋼	14	12	7	150	24	11	5	-4	0.4	CP**0802...	1.4
A12M-SCLPR/L08-D160	鋼	16	12	9	150	24	11	5	-3	0.4	CP**0802...	1.4
A16Q-SCLPR/L09-D180	鋼	18	16	9	180	32	15	5	-3.5	0.8	CP**0903...	3
A16Q-SCLPR/L09-D200	鋼	20	16	11	180	32	15	5	-3	0.8	CP**0903...	3
A20R-SCLPR/L09-D220	鋼	22	20	11	200	36	18	5	-2	0.8	CP**0903...	3
A25S-SCLPR/L09-D270	鋼	27	25	13.5	250	45	23	5	-1	0.8	CP**0903...	3
E08K-SCLPR/L06-D100	超硬	10	8	5.5	125	22	7.5	5	-8	0.4	CP**0602...	1.2
E10M-SCLPR/L06-D120	超硬	12	10	6	150	25	9	5	-5	0.4	CP**0602...	1.2
E10H-SCLPR08-D120	超硬	12	10	6	100	25	9	5	-5	0.4	CP**0802...	1.4
E10M-SCLPR/L08-D120	超硬	12	10	6	150	25	9	5	-5	0.4	CP**0802...	1.4
E12Q-SCLPR/L06-D140	超硬	14	12	7	180	27	11	5	-4	0.4	CP**0602...	1.2
E12G-SCLPR08-D140	超硬	14	12	7	90	27	11	5	-4	0.4	CP**0802...	1.4
E12J-SCLPR08-D140	超硬	14	12	7	110	27	11	5	-4	0.4	CP**0802...	1.4
E12Q-SCLPR/L08-D140	超硬	14	12	7	180	27	11	5	-4	0.4	CP**0802...	1.4
E12G-SCLPR08-D160	超硬	16	12	9	90	27	11	5	-3	0.4	CP**0802...	1.4
E12J-SCLPR08-D160	超硬	16	12	9	110	27	11	5	-3	0.4	CP**0802...	1.4
E12Q-SCLPR/L08-D160	超硬	16	12	9	180	27	11	5	-3	0.4	CP**0802...	1.4
E16H-SCLPR09-D180	超硬	18	16	9	100	32	15	5	-3.5	0.8	CP**0903...	3
E16L-SCLPR09-D180	超硬	18	16	9	130	32	15	5	-3.5	0.8	CP**0903...	3
E16R-SCLPL09-D180	超硬	18	16	9	200	32	15	5	-3.5	0.8	CP**0903...	3
E16H-SCLPR09-D200	超硬	20	16	11	100	32	15	5	-3	0.8	CP**0903...	3
E16L-SCLPR09-D200	超硬	20	16	11	130	32	15	5	-3	0.8	CP**0903...	3
E16R-SCLPL09-D200	超硬	20	16	11	200	32	15	5	-3	0.8	CP**0903...	3

*トルク：推奨締付けトルク (N・m) ** r_e ：基準コーナ

(注) 勝手付きインサートの場合、右勝手ホルダ (SCLPR**) には左勝手のインサート (L) を、左勝手ホルダ (SCLPL**) には右勝手のインサート (R) を使用します。

部品



形番	締付けねじ	スパナ
A**-SCLPR/L06-D...	CSTB-2.5S	T-8F
A10K-SCLPR/L08-D120	CSTB-3L042	T-9F
A12M-SCLPR/L08-D...	CSTB-3L050	T-9F
A**-SCLPR/L09-D...	CSTB-4L060	T-15F
E**-SCLPR/L06-D...	CSTB-2.5S	T-8F
E10*-SCLPR/L08-D...	CSTB-3L042	T-9F
E12*-SCLPR/L08-D...	CSTB-3L050	T-9F
E16*-SCLPR/L09-D...	CSTB-4L060	T-15F

参照ページ

A/E-SCLPR/L: インサート → B111 -