



形番	ϕD_c	ϕD_s	ϕD	l	l_s	L_{tm}	L_f	L	最大オフセット量 (半径)	Kg	インサート
TDX125F20-2	12.5	20	25	25	49	28	41	90	0.8	0.2	XPMT040104R-D*
TDX130F20-2	13	20	25	26	49	29	42	91	0.7	0.2	XPMT040104R-D*
TDX135F20-2	13.5	20	25	27	49	30	43	92	0.6	0.2	XPMT040104R-D*
TDX140F20-2	14	20	25	28	49	31	44	93	0.5	0.2	XPMT040104R-D*
TDX145F20-2	14.5	20	25	29	49	32	46	95	0.4	0.2	XPMT040104R-D*
TDX150F20-2	15	20	25	30	49	33	47	96	0.9	0.2	XPMT050204R-D*
TDX155F20-2	15.5	20	32	31	49	34	49	98	0.8	0.2	XPMT050204R-D*
TDX160F20-2	16	20	32	32	49	35	51	100	0.6	0.2	XPMT050204R-D*
TDX165F20-2	16.5	20	32	33	49	36	52	101	0.5	0.2	XPMT050204R-D*
TDX170F20-2	17	20	32	34	49	37	53	102	0.4	0.2	XPMT050204R-D*
TDX175F25-2	17.5	25	32	35	54	38	55	109	1.2	0.3	XPMT06X308R-D*
TDX180F25-2	18	25	32	36	54	39	56	110	1.1	0.3	XPMT06X308R-D*
TDX185F25-2	18.5	25	32	37	54	40	57	111	0.9	0.3	XPMT06X308R-D*
TDX190F25-2	19	25	32	38	54	41	58	112	0.8	0.3	XPMT06X308R-D*
TDX195F25-2	19.5	25	32	39	54	42	60	114	0.7	0.3	XPMT06X308R-D*
TDX200F25-2	20	25	32	40	54	45	61	115	0.5	0.3	XPMT06X308R-D*
TDX205F25-2	20.5	25	32	41	54	46	62.5	116.5	0.4	0.3	XPMT06X308R-D*
TDX210F25-2	21	25	32	42	54	47	64	118	0.3	0.3	XPMT06X308R-D*
TDX215F25-2	21.5	25	32	43	54	48	65	119	0.2	0.3	XPMT06X308R-D*
TDX220F25-2	22	25	32	44	54	49	66	120	1.2	0.3	XPMT07H308R-D*
TDX225F25-2	22.5	25	37	45	54	50	67.5	121.5	1.1	0.3	XPMT07H308R-D*
TDX230F25-2	23	25	37	46	54	51	69	123	0.9	0.4	XPMT07H308R-D*
TDX235F25-2	23.5	25	37	47	54	52	70	124	0.8	0.4	XPMT07H308R-D*
TDX240F25-2	24	25	37	48	54	53	71	125	0.7	0.4	XPMT07H308R-D*
TDX245F25-2	24.5	25	37	49	54	54	72.5	126.5	0.5	0.4	XPMT07H308R-D*
TDX250F25-2	25	25	37	50	54	55	74	128	0.4	0.4	XPMT07H308R-D*
TDX255F25-2	25.5	25	37	51	54	56	75.5	129.5	0.3	0.4	XPMT07H308R-D*
TDX260F25-2	26	25	37	52	54	57	77	131	0.2	0.4	XPMT07H308R-D*
TDX270F32-2	27	32	40	54	59	59	79	138	1.5	0.6	XPMT08T308R-D*
TDX280F32-2	28	32	40	56	59	60.3	82.3	141.3	1.2	0.6	XPMT08T308R-D*
TDX290F32-2	29	32	40	58	59	62.3	84.3	143.3	1	0.7	XPMT08T308R-D*
TDX300F32-2	30	32	40	60	59	64.3	87.3	146.3	0.7	0.7	XPMT08T308R-D*
TDX310F32-2	31	32	40	62	59	66.3	90.3	149.3	0.4	0.7	XPMT08T308R-D*
TDX320F32-2	32	32	40	64	59	68.3	92.3	151.3	0.2	0.8	XPMT08T308R-D*
TDX330F40-2	33	40	50	66	69	70.6	95.6	164.6	2.3	1.2	XPMT110412R-D*
TDX340F40-2	34	40	50	68	69	72.6	98.6	167.6	2.1	1.2	XPMT110412R-D*
TDX350F40-2	35	40	50	70	69	74.6	101.6	170.6	1.8	1.2	XPMT110412R-D*
TDX360F40-2	36	40	50	72	69	76.6	104.6	173.6	1.5	1.3	XPMT110412R-D*
TDX370F40-2	37	40	50	74	69	78.6	105.6	174.6	1.3	1.3	XPMT110412R-D*
TDX380F40-2	38	40	50	76	69	80.6	108.6	177.6	1	1.3	XPMT110412R-D*
TDX390F40-2	39	40	50	78	69	82.6	110.6	179.6	0.7	1.4	XPMT110412R-D*
TDX400F40-2	40	40	50	80	69	84.6	113.6	182.6	0.5	1.4	XPMT110412R-D*
TDX410F40-2	41	40	50	82	69	86.6	117.6	186.6	0.2	1.5	XPMT110412R-D*
TDX420F40-2	42	40	55	84	69	89	120	189	3.1	1.6	XPMT150512R-D*
TDX430F40-2	43	40	55	86	69	91	123	192	2.9	1.6	XPMT150512R-D*
TDX440F40-2	44	40	55	88	69	93	125	194	2.6	1.7	XPMT150512R-D*
TDX450F40-2	45	40	55	90	69	95	128	197	2.3	1.7	XPMT150512R-D*
TDX460F40-2	46	40	55	92	69	97	131	200	2.1	1.8	XPMT150512R-D*
TDX470F40-2	47	40	55	94	69	99	133	202	1.8	1.9	XPMT150512R-D*
TDX480F40-2	48	40	55	96	69	101	136	205	1.5	1.9	XPMT150512R-D*
TDX490F40-2	49	40	55	98	69	103	138	207	1.3	1.9	XPMT150512R-D*
TDX500F40-2	50	40	55	100	69	105	141	210	1	2	XPMT150512R-D*