

色仕様

※PC=ポリカーボネートの略称

色記号	カバー色 / 材質	ボディ色 / 材質
BCAP □ タイプ	ホワイトグレー / ABS樹脂	ホワイトグレー / ABS樹脂
BCAP □ タイプ	透明 / PC	ホワイトグレー / ABS樹脂
BCPC □ タイプ	ライトグレー / PC	ライトグレー / グラスファイバー入りポリカーボネート

■ BCAPシリーズをご注文の際は必ず型番末尾□にG、Tの色記号をつけて下さい。



型番・寸法・標準価格

型番	W	D	H	自重 (g)		標準価格(税別)	
				Gタイプ	Tタイプ	Gタイプ	Tタイプ
BCAP091207□	90	120	70	196	204	970	1,040
BCAP091208□	90	120	85	212	221	990	1,100
BCAP101507□	100	150	70	272	281	1,260	1,370
BCAP101508□	100	150	85	291	300	1,380	1,490
BCAP112107□	110	210	75	359	378	1,520	1,660
BCAP112110□	110	210	100	422	420	1,590	1,730
BCAP112607□	110	260	75	431	446	1,640	1,820
BCAP112610□	110	260	100.5	484	500	1,730	1,940
BCAP131508□	135	155	85	356	357	1,580	1,700
BCAP131808□	135	185	85.5	381	410	1,680	1,830
BCAP131810□	135	185	100.5	396	402	1,710	1,860
BCAP151509□	150	150	90	343	353	1,600	1,730
BCAP151512□	150	150	120.5	411	425	1,730	1,880
BCAP162110□	160	210	100	468	486	1,840	2,040
BCAP162113□	160	210	130	517	537	1,960	2,170
BCAP162610□	160	260	100	577	601	2,070	2,300
BCAP162613□	160	260	130	673	701	2,280	2,510
NEW BCAP172210□	170	220	105	545	581	2,040	2,230
BCAP172711□	170	270	110.5	670	680	2,290	2,540
BCAP192810□	190	280	100.5	722	746	2,630	2,800
BCAP192814□	190	280	141	877	901	3,020	3,280
NEW BCAP203013□N	200	300	130	921	954	3,080	3,330
NEW BCAP203015□N	200	300	150	989	1,022	3,280	3,590
NEW BCAP203018□N	200	300	180	1,110	1,143	3,530	3,780
BCAP212110□	210	210	100	630	656	2,110	2,450
BCAP212113□	210	210	130	704	726	2,470	2,680
NEW BCAP253515□N	250	350	150	1,278	1,320	4,000	4,430
NEW BCAP253518□N	250	350	180	1,415	1,456	4,270	4,870
BCAP282813□	280	280	130.5	1,167	1,200	4,010	4,710
BCAP283813□	280	380	130	1,455	1,512	4,650	5,370
BCAP303015□	300	300	151	1,339	1,418	4,550	5,020
BCAP303018□	300	300	181	1,495	1,576	4,770	5,240
BCAP304012□	300	400	120	1,508	1,575	4,980	5,480
BCAP304015□	300	400	150	1,563	1,675	5,130	5,560
BCAP304018□	300	400	181	1,719	1,853	5,510	5,960
BCAP353515□	350	350	150	1,693	1,764	5,430	6,080
BCAP353518□	350	350	181	1,845	1,906	5,680	6,470
BCAP354512□	350	450	120	2,068	2,167	6,500	7,780
BCAP354516□	350	450	160	2,382	2,514	7,280	8,390
BCAP354520□	350	450	201	2,646	2,794	7,890	8,920
BCAP405016□	400	500	160	2,660	2,839	8,000	9,250
BCAP405020□	400	500	201	3,119	3,232	9,260	10,230
BCAP406018□	400	600	181	3,542	3,652	10,750	12,630
BCAP406023□	400	600	231	3,870	4,044	12,250	14,300
BCAP506018□	530	630	185	5,438	5,611	18,180	22,270
BCAP506025□	530	630	255	6,078	6,273	20,110	23,050
BCAP507018G	530	730	188	6,241	—	20,800	—
BCAP507025G	530	730	255	6,911	—	22,000	—
BCAP608018G	630	830	188	8,131	—	27,490	—
BCAP608028G	630	830	288	9,570	—	32,460	—

型番・寸法・標準価格

型番	W	D	H	自重 (g)	標準価格(税別)	
					Gタイプ	Tタイプ
BCPC091207S	90	120	70	226	▲ 1,420	
BCPC091208S	90	120	85	247	▲ 1,450	
BCPC101507S	100	150	70	312	▲ 1,860	
BCPC101508S	100	150	85	336	▲ 1,890	
BCPC112107S	110	210	75	420	▲ 2,360	
BCPC112110S	110	210	100	473	▲ 2,420	
BCPC112607S	110	260	75	493	▲ 2,620	
BCPC112610S	110	260	100.5	569	▲ 2,670	
BCPC131508S	135	155	85	406	▲ 2,420	
BCPC131808S	135	185	85.5	452	▲ 2,640	
BCPC131810S	135	185	100.5	448	▲ 2,700	
BCPC151509S	150	150	90	395	▲ 2,450	
BCPC151512S	150	150	120.5	482	▲ 2,730	
BCPC162110S	160	210	100	556	▲ 3,040	
BCPC162113S	160	210	130	611	▲ 3,280	
BCPC162610S	160	260	100	671	▲ 3,430	
BCPC162613S	160	260	130	779	▲ 3,930	
NEW BCPC172210S	170	220	105	642	▲ 3,370	
BCPC172711S	170	270	110.5	775	▲ 3,890	
BCPC192810S	190	280	100.5	858	▲ 4,150	
BCPC192814S	190	280	141	1,028	▲ 5,040	
NEW BCPC203013SN	200	300	130	1,070	▲ 5,200	
BCPC203015S	200	300	151.5	1,127	▲ 5,510	
NEW BCPC203018SN	200	300	180	1,295	▲ 5,940	
BCPC212110S	210	210	100	742	▲ 3,850	
BCPC212113S	210	210	130	827	▲ 4,190	
NEW BCPC253515SN	250	350	150	1,485	▲ 7,100	
NEW BCPC253518SN	250	350	180	1,648	▲ 7,560	
BCPC282813S	280	280	130.5	1,371	▲ 6,560	
BCPC283813S	280	380	130	1,695	▲ 8,190	
BCPC303015S	300	300	151	1,610	▲ 7,990	
BCPC303018S	300	300	181	1,760	▲ 8,400	
BCPC304012S	300	400	120	1,846	▲ 8,310	
BCPC304015S	300	400	150	1,862	▲ 8,760	
BCPC304018S	300	400	181	2,030	▲ 9,480	
BCPC353515S	350	350	150	2,045	▲ 9,700	
BCPC353518S	350	350	181	2,142	▲ 10,050	
BCPC354512S	350	450	120	2,397	▲ 11,670	
BCPC354516S	350	450	160	2,826	▲ 12,760	
BCPC354520S	350	450	201	3,151	▲ 14,420	
BCPC405016S	400	500	160	3,188	▲ 14,690	
BCPC405020S	400	500	201	3,811	▲ 16,870	
BCPC406018S	400	600	181	4,153	▲ 18,920	
BCPC406023S	400	600	231	4,637	▲ 20,110	
BCPC506018S	530	630	185	6,305	▲ 28,690	
BCPC506025S	530	630	255	7,213	▲ 32,060	
BCPC507018S	530	730	188	7,410	▲ 31,690	
BCPC507025S	530	730	255	8,200	▲ 37,520	
BCPC608018S	630	830	188	9,820	▲ 41,760	
BCPC608028S	630	830	288	11,550	▲ 51,240	

■ BCAP507018、507025、608018、608028はGタイプのみになります。■ 詳細寸法はP3-45~48をご覧ください。

▲は値上げした製品です。

オプション部品 (別売)



取付ベース
BMPシリーズ
P3-51~53



外部取付足
CK・BFLシリーズ
P3-54



ボール取付金具
SSKシリーズ
P3-55~56



ケーブルグランド
P5-73~81



プロテクティブベント・ルーバー
P3-113~116