


## IDS (高荷重/金属インサート成形品)

RoHS



Code	Part No.	D <sup>±0.1</sup> [mm]	d <sup>+0.1</sup> [mm]	d1 <sup>-0.1</sup> [mm]	W <sup>±0.2</sup> [mm]	C <sup>±0.4</sup> [mm]	L <sup>±0.2</sup> [mm]	<sup>*1</sup> (d2×θ)	W1 <sup>*1</sup> [mm]	W2 <sup>*1</sup> [mm]	N [mm]	Load <sup>*2</sup> [N] (kgf)	Type	Q'ty [pcs/box]	Gross Weight [kg/box]
221400	IDS-22-A1	22	—	5	7	1	3.5	φ2.5×90°	—	—	(11.0)	392 (40)	1	1,000	12.4
221401	IDS-22-A2.5	22	—	5	7	2.5	3.5	nothing	—	—	(9.0)	392 (40)	1	1,000	14.0
221403	IDS-22-A3.4-4.5	22	—	5.1	7	3.4	4.5	φ2.5×90°	—	—	(9.5)	392 (40)	1	1,000	13.4
221450	IDS-26-A1.5	26	—	6	8	1.5	3.5	φ5.5×90°	—	—	(11.0)	588 (60)	1	800	15.5
221504	IDS-22-B1.5-8	22	—	—	7	1.5	8 <sup>±0.5</sup>	—	—	—	(11.0)	392 (40)	2	1,000	13.2
221501	IDS-22-B1.5-11	22	—	—	7	1.5	11 <sup>±0.5</sup>	—	—	—	(11.0)	392 (40)	2	1,000	15.3
221505	IDS-22-B4-7	22	—	—	7	4	7 <sup>±0.5</sup>	—	—	—	(9.5)	392 (40)	2	1,000	14.5
221518	IDS-22-B11	22	—	—	7	11	8 <sup>±0.5</sup>	—	—	—	(9.5)	392 (40)	2	1,000	18.6
221600	IDS-26-B2-11	26	—	—	8	2	11 <sup>±0.5</sup>	—	—	—	(11.0)	588 (60)	2	500	10.2
221603	IDS-26-B5-9	26	—	—	8	5 <sup>±0.5</sup>	9 <sup>±0.5</sup>	—	—	—	(9.5)	588 (60)	2	500	11.1
221650	IDS-30-B2-11	30	—	—	9	2	11 <sup>±0.5</sup>	—	—	—	(11.0)	588 (60)	2	500	12.1
221700	IDS0-26-B2-11	26 <sup>-0.2</sup>	—	—	8	2	11 <sup>±0.5</sup>	—	—	—	(11.0)	588 (60)	3	500	10.2
221901	IDS-26-H6.35W0.8	26	6.35	—	8	—	—	—	0.8	0.8	(17.0)	294 (30)	4	800	16.3
221954	IDS-35-H6.35W0.26	35 <sup>-0.1</sup>	6.35	—	9	—	—	—	0.26	0.26	(17.0)	294 (30)	4	500	13.3

\*1 参考値 Reference Dimension

\*2 許容荷重 (毎分 300 回 回転時) Allowable Load at 300min<sup>-1</sup> (300r.p.m)

\*3 上記以外のサイズ・形状につきましては、弊社までご相談ください。Each limiting size can be changed for practical application. Please ask our engineer for further information.