










コレット

外観×寸法 (mm)		部品番号	電極径 (mm)	適用トーチ (ページ番号)	
A					
		53N15 53N16 53N14 24C332	0.5 1.0 1.6 2.4	ヘッド 24/24-90 (P.64) トーチ WP-24F (P.13) WP-24 (P.18) WP-24W (P.34)	
B					
ガス スレン ズ用		53N62 53N63 53N64 24GLC332	0.5 1.0 1.6 2.4		
C					
		13N20 13N21 13N22 13C2M 13N23 13N24	0.5 1.0 1.6 2.0 2.4 3.2	ヘッド 9-70/9-90/9P (P.64) トーチ WP-9F (P.12) WP-R9F (P.13) WP-9/9P (P.20) WP-25 (P.30) WP-20/20P (P.36) WP-280 (P.38) CS310 (P.40) W-375 (P.44)	
D					
大口 径ガ スレ ンズ 用		13N20L 13N21L 13N22L 13N23L 13N24L	0.5 1.0 1.6 2.4 3.2		
E					
		10N21 10N22 10N23 10N2M 10N24 10N24-AAA ^{※1} 10N25 54N20	0.5 1.0 1.6 2.0 2.4 2.4 3.2 4.0	ヘッド 1726/1726P (P.64) トーチ WP-17F (P.12) WP-26F (P.12) WP-R17F (P.13) WP-R26F (P.13) WP-17A (P.22) WP-17-PSH (P.22) WP-26 (P.24) WP-26P WP-18 (P.42) WP-18SP WP-18SC (P.46) CS410 (P.48) WP-18P (P.52)	
F					
スタ ビー 用		10N22S 10N23S 10N24S 10N25S	1.0 1.6 2.4 3.2		
G					
		10N25HD 54N20HD 18C36	3.2 4.0 4.8	WP-18SC (P.46) (重作業用)	
H					
		22N20A 22N20B 22N21A 22N21B	0.5 1.0	WP-23A/B (P.54) WP-22A/B (P.56)	
		22N22A 22N22B	1.6		
		22N23A 22N23B	2.4	※A型トーチには Aのコレット、 B型トーチには Bのコレットを ご使用下さい。	
		22N24A 22N24B	3.2		
I					
大口 径ガ スレ ンズ 用		22N20AL 22N20BL	0.5	WP-23A/B (P.54) WP-22A/B (P.56)	
		22N21AL 22N21BL	1.0		
		22N22AL 22N22BL	1.6	※A型トーチには Aのコレット、 B型トーチには Bのコレットを ご使用下さい。	
		22N23AL 22N23BL	2.4		
		22N24AL 22N24BL	3.2		
J					
		85Z14 85Z15 85Z16 85Z17 85Z18 85Z19	1.6 2.4 3.2 4.0 4.8 6.4	WP-12 (P.50)	

※1 四つ割れ ※2 タングステンを締める際は53N20(専用チャックレンチ)を使用して下さい。

外観×寸法 (mm)	部品番号	電極径 (mm)	適用トーチ (ページ番号)
K			
	57N45 57N46 57N47 57N48 57N49 57N50 57N51	1.0 1.6 2.4 3.2 4.0 4.8 6.4	WP-27A/B (P.58) WP-27AAC WP-27BHD

コレットボディ・チャック

外観×寸法 (mm)	部品番号	電極径 (mm)	適用トーチ (ページ番号)
A			
	50C20 ^{※2} 50C40 ^{※2} 125C116 ^{※2}	0.5/180° 1.0/180° 1.6/180°	WP-50 WP-125M/L (P.32)
B			
	125C40-90 125C40-45 125C116-90 125C116-45 125C332-90 125C332-45	1.0/90° 1.0/45° 1.6/90° 1.6/45° 2.4/90° 2.4/45°	WP-125M/L (P.32)
C			
	53N17 ^{※2} 53N18 ^{※2} 53N19 ^{※2} 24CB332 ^{※2}	0.5 1.0 1.6 2.4	ヘッド 24/24-90 (P.64) トーチ WP-24F (P.13) WP-24 (P.18) WP-24W (P.34)
D			
	13N25 13N26 13N27 13CB2M 13N28 13N29	0.5 1.0 1.6 2.0 2.4 3.2	ヘッド 9-70/9-90/9P (P.64) トーチ WP-9F (P.12) WP-R9F (P.13) WP-9/9P (P.20) WP-25 (P.30) WP-20/20P (P.36) WP-280 (P.38) CS-310 (P.40) W-375 (P.44) WP-23A/B (P.54) WP-22A/B (P.56)
E			
	10N29 10N30 10N31 10CB2M 10N32 10N28 406488	0.5 1.0 1.6 2.0 2.4 3.2 4.0	ヘッド 1726/1726 (P.64) トーチ WP-17F (P.12) WP-26F (P.12) WP-R17F (P.13) WP-R26F (P.13) WP-17A (P.22) WP-17-PSH (P.22) WP-26 (P.24) WP-26P WP-18 (P.42) WP-18SP CS410 (P.48) WP-18P (P.52)
F			
スタ ビー 用 	17CB20	1.0-3.2	ヘッド 1726/1726 (P.64) トーチ WP-17F (P.12) WP-26F (P.12) WP-R17F (P.13) WP-R26F (P.13) WP-17A (P.22) WP-17-PSH (P.22) WP-26 (P.24) WP-26P WP-18 (P.42) WP-18SP CS410 (P.48) WP-18P (P.52)
G			
	NCB-53 NCB-36	0.5-3.2 3.2-4.8	WP-18SC (P.46)
H			
	11WP65	1.6-6.4	WP-12 (P.50)

手動／空冷／フレキシブル

手動／空冷／固定

手動／水冷／フレキシブル

手動／水冷／固定

自動／空冷

自動／水冷

交換部品

その他