

マジックリング付 蛍光色  
ボールポイント六角レンチ



蛍光色

型番	●	┌	└	◁	⊞	価格
369RF30	3	128	23	orange	10	¥1,050
369RF40	4	142	29	purple	10	¥1,260
369RF50	5	163	33	Dark green	10	¥1,350
369RF60	6	184	38	red	10	¥1,650
369RF80	8	206	44	Dark blue	10	¥2,650
369RF100	10	231	50	Anthracite	10	¥3,400

蛍光色 ボールポイント六角レンチ



蛍光色

型番	●	┌	└	◁	⊞	価格
369F15	1.5	91	15	yellow	10	¥ 580
369F20	2	101	18	light blue	10	¥ 580
369F25	2.5	113	20	Light green	10	¥ 610
369F30	3	128	23	orange	10	¥ 650
369F40	4	142	29	purple	10	¥ 850
369F50	5	163	33	Dark green	10	¥ 930
369F60	6	184	38	red	10	¥1,160
369F80	8	206	44	Dark blue	10	¥2,050
369F100	10	231	50	Anthracite	5	¥2,600

マジックリング付 ボールポイント  
六角レンチ (ロングタイプ)



クロームメッキ

型番	●	┌	└	⊞	価格
369R30	3	128	23	10	¥ 880
369R40	4	142	29	10	¥ 900
369R50	5	163	33	10	¥ 990
369R60	6	184	38	10	¥1,160
369R80	8	206	44	10	¥1,590
369R10	10	231	50	5	¥2,090

マジックリング付 ボールポイント  
インチサイズ六角レンチ (ロングタイプ)



クロームメッキ

型番	●	┌	└	mm	⊞	価格
HRR430MBH1/8	1/8	121	23	3.17	10	¥ 890
HZR430MBH9/64	9/64	136	27	3.57	10	¥ 920
HSR430MBH5/32	5/32	148	29	3.96	10	¥ 940
HWR430MBH3/16	3/16	163	33	4.76	10	¥1,030
HLR430MBH7/32	7/32	176	36	5.55	10	¥1,080
HQR430MBH1/4	1/4	191	38	6.35	10	¥1,230
HPR430MBH5/16	5/16	210	43	7.93	10	¥1,700
HYR434MBH3/8	3/8	232	49	9.52	10	¥2,130

ボールポイント六角レンチ  
(スタビータイプ)



クロームメッキ

型番	●	┌	└	⊞	価格(10本)
HRS548BH15S	1.5	91	5.5	1	¥ 4,000
HSS548BH20S	2	101	9	1	¥ 4,000
HZS548BH25S	2.5	113	9.5	1	¥ 4,200
HWS548BH30S	3	128	11	1	¥ 5,800
HLS548BH40S	4	142	13	1	¥ 5,800
HQS548BH50S	5	163	15	1	¥ 6,800
HPS548BH60S	6	184	18	1	¥ 8,300
HGS548BH80S	8	206	22	1	¥14,600
HXS549BH100S	10	231	28	1	¥9,250(5本)

ボールポイント六角レンチ ショート



クロームメッキ

型番	●	┌	└	⊞	価格(10本)
HYZ040BHS15	1.5	46	15	1	¥ 2,800
HRZ040BHS20	2	51	18	1	¥ 2,800
HSZ040BHS25	2.5	57	20	1	¥ 2,800
HZZ040BHS30	3	64	23	1	¥ 2,800
HWZ040BHS40	4	72	29	1	¥ 3,200
HLZ040BHS50	5	83	33	1	¥ 4,200
HQZ040BHS60	6	94	38	1	¥ 5,300
HPZ040BHS80	8	105	44	1	¥ 8,300
HGZ040BHS100	10	119	50	1	¥11,300

ボールポイント六角レンチ



クロームメッキ

型番	●	┌	└	⊞	価格
369W15	1.5	91	15	10	¥ 390
369W20	2	101	18	10	¥ 390
369W25	2.5	113	20	10	¥ 410
369W30	3	128	23	10	¥ 460
369W40	4	142	29	10	¥ 550
369W50	5	163	33	10	¥ 570
369W60	6	184	38	10	¥ 670
369W70	7	195	39	5	¥1,030
369W80	8	206	44	10	¥1,150
369W90	9	217	47	5	¥1,360
369W100	10	231	50	5	¥1,460
369W120	12	259	57	5	¥2,070

ボールポイント六角レンチ  
インチサイズ



クロームメッキ

型番	●	┌	└	mm	⊞	価格(10本)
HYR947BH005	0.05	72	13	1.27	1	¥4,100
HRR947BH1/16	1/16	80	15	1.59	1	¥4,200
HZR947BH5/64	5/64	88	18	1.98	1	¥4,400
HSR947BH3/32	3/32	101	20	2.38	1	¥4,200
HWR947BH7/64	7/64	111	21	2.78	1	¥4,500

ボールポイント六角レンチ



黒染め酸化処理

型番	●	┌	└	⊞	価格(10本)
HYX139BH13	1.3	74	14	1	¥ 2,600
HPX563BH15	1.5	91	15	1	¥ 2,600
HPX386BH20	2	101	18	1	¥ 2,600
HGX386BH25	2.5	113	20	1	¥ 2,800
HXX387BH30	3	128	23	1	¥ 2,800
HYX387BH40	4	142	29	1	¥ 3,800
HRX387BH50	5	163	33	1	¥ 4,300
HSX387BH60	6	184	38	1	¥ 5,500
HZX387BH80	8	206	44	1	¥ 9,300
HWX387BH100	10	231	50	1	¥12,800
HLX387BH120	12	259	57	1	¥16,800

ボールポイント六角レンチ  
インチサイズ



黒染め酸化処理

型番	●	┌	└	mm	⊞	価格(10本)
HRX142BH005	0.05	72	13	1.27	1	¥2,800
HSX142BH1/16	1/16	80	15	1.59	1	¥2,700
HYX143BH5/64	5/64	88	18	1.98	1	¥2,700
HQX142BH3/32	3/32	101	20	2.38	1	¥3,000
HSX143BH7/64	7/64	111	21	2.78	1	¥3,100
HWX142BH1/8	1/8	121	23	3.18	1	¥3,200
HZX143BH9/64	9/64	136	27	3.57	1	¥3,600
HXX143BH5/32	5/32	148	29	3.97	1	¥4,200
HLX142BH3/16	3/16	163	33	4.76	1	¥5,100
HRX143BH7/32	7/32	176	36	5.56	1	¥5,400
HZX142BH1/4	1/4	191	38	6.35	1	¥6,400
HGX142BH5/16	5/16	210	43	7.94	1	¥9,400
HPX142BH3/8	3/8	232	49	9.53	1	¥6,500(5本)

六角レンチ



黒染め酸化処理

型番	●	┌	└	⊞	価格(10本)
HPX635H07	0.7	67	6	1	¥2,100(5本)
HGX635H09	0.9	70	9	1	¥1,800(5本)
HXX636H13	1.3	73	13	1	¥ 950(5本)
HGX605H15	1.5	91	15	1	¥1,400
HYX636H20	2	101	18	1	¥1,300
HRX636H25	2.5	113	20	1	¥1,600
HSX636H30	3	128	23	1	¥1,900
HZX636H40	4	142	29	1	¥2,400
HWX636H50	5	163	33	1	¥2,600
HLX636H60	6	184	38	1	¥3,500
HQX636H70	7	194	41	1	¥4,400
HPX636H80	8	206	44	1	¥5,200
HGX636H100	10	231	50	1	¥4,000(5本)
HXX637H120	12	259	57	1	¥6,400(5本)
HYX637H140	14	294	70	1	¥9,000(5本)