



CN□□ (ネガティブ)

型式	寸法					ブレード	用途	P 鋼		M ステンレス			K 鋳物			
	L	LC	S	d	r			YBC152	YBC252	YBM251	YBG203	YBG205	YBD152	YBD252		
CNMG 120404	12.9	12.7	4.76	5.16	0.4	DF	仕上	●	●							
						DM	中	●	●			●	●			
						EF	仕上					●	●			
						EM	中					●	●			
						PM	断続								●	●
CNMG 120408	12.9	12.7	4.76	5.16	0.8	DF	仕上	●	●					●		
						DM	中	●	●					●	●	
						EF	仕上									
						EM	中							●		
						PM	断続	●	●						●	●
CNMG 120612	12.9	12.7	4.76	5.16	1.2	DF	仕上									
						DM	中									
						DR	粗									
						EF	仕上									
						EM	中							●		
						PM	断続									●
CNMG 190616	19.3	19.05	6.35	7.94	1.6	DM	中		●							
						DR	粗		●							
						ER	粗									
CNMM 190612	19.3	19.05	6.35	7.94	1.2	HDR	粗~重									
CNMM 190616	19.3	19.05	6.35	7.94	1.6	HDR	粗~重									
CNMM 250724	25.79	25.4	7.94	9.12	2.4	ER	粗									
CNMM 250924	25.79	25.4	9.525	9.12	2.4	ER	粗									

PCLNR/L
Kr:95°

型式	在庫		基本寸法(mm)						ボルト	シム	レンチ	レバーピン	止めピン
	R	L	a	b	L	h	s	e					
PCLNR/L	2020K12		20	20	125	20	25	28	LEM8x21	C12AP	WH30L	L4	SP4
	2525M12		25	25	150	25	32	28					