

XEBCマイスターフィニッシュ

金型の研磨、バリ取りに最適



スティックタイプ

| 番手相当 (色) | 厚さ×幅×長さ (mm) | | | | | | | | | | | | | | | |
|-------------------|--------------|-----------|-----------|-----------|-----------|-----------|------------|------------|-----------|-----------|-----------|-----------|------------|------------|-----------|-----------|
| | 0.3×4×100 | 0.4×4×100 | 0.5×4×100 | 0.5×4×150 | 0.5×6×100 | 0.5×6×150 | 0.5×10×100 | 0.5×10×150 | 0.8×4×100 | 0.8×4×150 | 0.8×6×100 | 0.8×6×150 | 0.8×10×100 | 0.8×10×150 | 1.0×1×100 | 1.0×2×100 |
| #3000相当 (ピンク) | - | - | - | - | - | - | - | - | - | - | - | - | - | - | - | - |
| #2000相当 (クリーム) | - | - | - | - | - | - | - | - | - | - | - | - | - | - | - | - |
| #1500相当 (黄色) | - | - | - | - | - | - | - | - | - | - | - | - | - | - | - | - |
| #1200相当 (赤) | AR-0304M | AR-0404M | AR-0504M | AR-0504L | AR-0506M | AR-0506L | AR-0510M | AR-0510L | AR-0804M | AR-0804L | AR-0806M | AR-0806L | AR-0810M | AR-0810L | AR-1001M | AR-1002M |
| #1000相当 (白) | AW-0304M | AW-0404M | AW-0504M | AW-0504L | AW-0506M | AW-0506L | AW-0510M | AW-0510L | AW-0804M | AW-0804L | AW-0806M | AW-0806L | AW-0810M | AW-0810L | AW-1001M | AW-1002M |
| #800相当 (青) | AB-0304M | AB-0404M | AB-0504M | AB-0504L | AB-0506M | AB-0506L | AB-0510M | AB-0510L | AB-0804M | AB-0804L | AB-0806M | AB-0806L | AB-0810M | AB-0810L | AB-1001M | AB-1002M |
| #600相当 (黒) | AP-0304M | AP-0404M | AP-0504M | AP-0504L | AP-0506M | AP-0506L | AP-0510M | AP-0510L | AP-0804M | AP-0804L | AP-0806M | AP-0806L | AP-0810M | AP-0810L | AP-1001M | AP-1002M |
| #400相当 (オレンジ) | AO-0304M | AO-0404M | AO-0504M | AO-0504L | AO-0506M | AO-0506L | AO-0510M | AO-0510L | AO-0804M | AO-0804L | AO-0806M | AO-0806L | AO-0810M | AO-0810L | AO-1001M | AO-1002M |
| #300相当 (赤茶) | AL-0304M | AL-0404M | AL-0504M | AL-0504L | AL-0506M | AL-0506L | AL-0510M | AL-0510L | AL-0804M | AL-0804L | AL-0806M | AL-0806L | AL-0810M | AL-0810L | AL-1001M | AL-1002M |
| #220相当 (こげ茶) | AD-0304M | AD-0404M | AD-0504M | AD-0504L | AD-0506M | AD-0506L | AD-0510M | AD-0510L | AD-0804M | AD-0804L | AD-0806M | AD-0806L | AD-0810M | AD-0810L | AD-1001M | AD-1002M |
| #120相当 (紫) | - | - | - | - | - | - | - | - | - | - | - | - | - | - | - | - |

| 番手相当 (色) | 厚さ×幅×長さ (mm) | | | | | | | | | | | | | | | |
|------------------|--------------|-----------|-----------|-----------|-----------|-----------|------------|------------|------------|-----------|-----------|-----------|-----------|------------|------------|-----------|
| | 1.0×4×100 | 1.0×4×150 | 1.0×6×100 | 1.0×6×150 | 1.0×8×100 | 1.0×8×150 | 1.0×10×100 | 1.0×10×150 | 1.5×15×100 | 1.5×4×100 | 1.5×4×150 | 1.5×6×100 | 1.5×6×150 | 1.5×10×100 | 1.5×10×150 | 2.0×2×100 |
| #1500相当 (黄色) | AY-1004M | - | AY-1006M | - | - | - | AY-1010M | - | - | - | - | - | - | - | - | - |
| #1200相当 (赤) | AR-1004M | AR-1004L | AR-1006M | AR-1006L | AR-1008M | AR-1008L | AR-1010M | AR-1010L | AR-15015M | AR-1504M | AR-1504L | AR-1506M | AR-1506L | AR-1510M | AR-1510L | AR-2002M |
| #1000相当 (白) | AW-1004M | AW-1004L | AW-1006M | AW-1006L | AW-1008M | AW-1008L | AW-1010M | AW-1010L | AW-15015M | AW-1504M | AW-1504L | AW-1506M | AW-1506L | AW-1510M | AW-1510L | AW-2002M |
| #800相当 (青) | AB-1004M | AB-1004L | AB-1006M | AB-1006L | AB-1008M | AB-1008L | AB-1010M | AB-1010L | AB-15015M | AB-1504M | AB-1504L | AB-1506M | AB-1506L | AB-1510M | AB-1510L | AB-2002M |
| #600相当 (黒) | AP-1004M | AP-1004L | AP-1006M | AP-1006L | AP-1008M | AP-1008L | AP-1010M | AP-1010L | AP-15015M | AP-1504M | AP-1504L | AP-1506M | AP-1506L | AP-1510M | AP-1510L | AP-2002M |
| #400相当 (オレンジ) | AO-1004M | AO-1004L | AO-1006M | AO-1006L | AO-1008M | AO-1008L | AO-1010M | AO-1010L | AO-15015M | AO-1504M | AO-1504L | AO-1506M | AO-1506L | AO-1510M | AO-1510L | AO-2002M |
| #300相当 (赤茶) | AL-1004M | AL-1004L | AL-1006M | AL-1006L | AL-1008M | AL-1008L | AL-1010M | AL-1010L | AL-15015M | AL-1504M | AL-1504L | AL-1506M | AL-1506L | AL-1510M | AL-1510L | AL-2002M |
| #220相当 (こげ茶) | AD-1004M | AD-1004L | AD-1006M | AD-1006L | AD-1008M | AD-1008L | AD-1010M | AD-1010L | AD-15015M | AD-1504M | AD-1504L | AD-1506M | AD-1506L | AD-1510M | AD-1510L | AD-2002M |
| #120相当 (紫) | AV-1004M | AV-1004L | AV-1006M | AV-1006L | AV-1008M | AV-1008L | AV-1010M | AV-1010L | - | AV-1504M | AV-1504L | AV-1506M | AV-1506L | AV-1510M | AV-1510L | - |

| 番手相当 (色) | 厚さ×幅×長さ (mm) | | | | | | | | | | | | | | | |
|------------------|--------------|-----------|-----------|-----------|------------|------------|-----------|-----------|-----------|-----------|------------|------------|--|--|--|--|
| | 2.0×4×100 | 2.0×4×150 | 2.0×6×100 | 2.0×6×150 | 2.0×10×100 | 2.0×10×150 | 3.0×4×100 | 3.0×4×150 | 3.0×6×100 | 3.0×6×150 | 3.0×10×100 | 3.0×10×150 | | | | |
| #1200相当 (赤) | AR-2004M | AR-2004L | AR-2006M | AR-2006L | AR-2010M | AR-2010L | AR-3004M | AR-3004L | AR-3006M | AR-3006L | AR-3010M | AR-3010L | | | | |
| #1000相当 (白) | AW-2004M | AW-2004L | AW-2006M | AW-2006L | AW-2010M | AW-2010L | AW-3004M | AW-3004L | AW-3006M | AW-3006L | AW-3010M | AW-3010L | | | | |
| #800相当 (青) | AB-2004M | AB-2004L | AB-2006M | AB-2006L | AB-2010M | AB-2010L | AB-3004M | AB-3004L | AB-3006M | AB-3006L | AB-3010M | AB-3010L | | | | |
| #600相当 (黒) | AP-2004M | AP-2004L | AP-2006M | AP-2006L | AP-2010M | AP-2010L | AP-3004M | AP-3004L | AP-3006M | AP-3006L | AP-3010M | AP-3010L | | | | |
| #400相当 (オレンジ) | AO-2004M | AO-2004L | AO-2006M | AO-2006L | AO-2010M | AO-2010L | AO-3004M | AO-3004L | AO-3006M | AO-3006L | AO-3010M | AO-3010L | | | | |
| #300相当 (赤茶) | AL-2004M | AL-2004L | AL-2006M | AL-2006L | AL-2010M | AL-2010L | AL-3004M | AL-3004L | AL-3006M | AL-3006L | AL-3010M | AL-3010L | | | | |
| #220相当 (こげ茶) | AD-2004M | AD-2004L | AD-2006M | AD-2006L | AD-2010M | AD-2010L | AD-3004M | AD-3004L | AD-3006M | AD-3006L | AD-3010M | AD-3010L | | | | |
| #120相当 (紫) | AV-2004M | AV-2004L | AV-2006M | AV-2006L | AV-2010M | AV-2010L | AV-3004M | AV-3004L | AV-3006M | AV-3006L | AV-3010M | AV-3010L | | | | |

丸棒タイプ

| 番手相当 (色) | 径×長さ (mm) | | | | | | | | | | | | |
|------------------|-----------|--------|---------|----------|--------|--------|----------|-----------|--------|--------|--------|--------|--------|
| | φ1×50 | φ1×100 | φ1.5×50 | φ1.5×100 | φ2×50 | φ2×100 | φ2.34×50 | φ2.34×100 | φ3×50 | φ3×100 | φ3×150 | φ6×50 | φ6×100 |
| #1200相当 (赤) | PR-10S | PR-10M | PR-15S | PR-15M | PR-20S | PR-20M | PR-234S | PR-234M | PR-30S | PR-30M | PR-30L | - | - |
| #1000相当 (白) | PW-10S | PW-10M | PW-15S | PW-15M | PW-20S | PW-20M | PW-234S | PW-234M | PW-30S | PW-30M | PW-30L | - | - |
| #800相当 (青) | PB-10S | PB-10M | PB-15S | PB-15M | PB-20S | PB-20M | PB-234S | PB-234M | PB-30S | PB-30M | PB-30L | - | - |
| #600相当 (黒) | PP-10S | PP-10M | PP-15S | PP-15M | PP-20S | PP-20M | PP-234S | PP-234M | PP-30S | PP-30M | PP-30L | - | - |
| #400相当 (オレンジ) | PO-10S | PO-10M | PO-15S | PO-15M | PO-20S | PO-20M | PO-234S | PO-234M | PO-30S | PO-30M | PO-30L | - | - |
| #300相当 (赤茶) | PL-10S | PL-10M | PL-15S | PL-15M | PL-20S | PL-20M | PL-234S | PL-234M | PL-30S | PL-30M | PL-30L | - | - |
| #220相当 (グレー) | PM-10S | PM-10M | PM-15S | PM-15M | PM-20S | PM-20M | PM-234S | PM-234M | PM-30S | PM-30M | PM-30L | PM-60S | PM-60M |

使用方法はP38