


45°エルボ

DV 45L




サイズ	コード	価格	梱包	備考	Z	L
30	5 226571 -	92	340	◎	12	30
40	5 226573 -	108	190	◎	14	36
50	5 226574 -	163	100	◎	18	43
65	5 226575 -	271	46	◎	22	57

サイズ	コード	価格	梱包	備考	Z	L
75	5 226576 -	352	40	◎	25	65
100	5 226577 -	695	20	◎	30	80
125	5 226578 -	1,494	10	◎	38	103
150	5 226579 -	2,439	6	◎	44	124

90°Y

DV DT




サイズ	コード	価格	梱包	備考	Z1	Z2	Z3	L1	L2	L3
30	5 226590 -	118	180	◎	22	22	22	40	40	40
40	5 226593 -	173	100	◎	27	27	27	49	49	49
50	5 226594 -	278	50	◎	34	34	34	59	59	59
65	5 226595 -	457	24	◎	42	43	42	77	78	77
75	5 226596 -	597	24	◎	48	49	48	88	89	88
100	5 226597 -	1,239	12	◎	62	63	62	112	113	112
125	5 226600 -	2,293	6	◎	75	76	75	140	141	140
150	5 226599 -	4,128	4	◎	89	90	89	169	170	169
40×30	5 226616 -	157	120	◎	22	22	27	44	44	45
50×40	5 226620 -	216	76	◎	22	22	33	47	47	51
50×40	5 226622 -	216	66	◎	27	27	33	52	52	55
65×40	5 226625 -	392	40	◎	27	28	42	62	63	64

サイズ	コード	価格	梱包	備考	Z1	Z2	Z3	L1	L2	L3
65×50	5 226627 -	392	34	◎	34	35	42	69	70	67
75×40	5 226629 -	548	34	◎	27	28	48	67	68	70
75×50	5 226630 -	548	34	◎	34	35	48	74	75	73
75×65	5 226631 -	548	30	◎	42	43	48	82	83	83
100×40	5 226639 -	1,056	24	◎	27	28	62	77	78	84
100×50	5 226635 -	1,056	22	◎	34	35	62	84	85	87
100×65	5 226636 -	1,056	16	◎	42	43	62	92	93	97
100×75	5 226637 -	1,056	14	◎	48	49	62	98	99	102
125×75	5 226648 -	2,293	8	◎	48	49	72	113	114	112
125×100	5 226649 -	2,293	8	◎	60	64	74	125	129	124
150×75	5 226659 -	4,128	7	◎	54	51	90	134	131	130
150×100	5 226651 -	4,128	6	◎	62	63	92	142	143	142

90°大曲りY

DV LT



サイズ	コード	価格	梱包	備考	Z1	Z2	Z3	L1	L2	L3
40	5 226673 -	291	70	◎	52	23	52	74	45	74
50	5 226674 -	382	34	◎	66	26	66	91	51	91
65	5 226675 -	666	18	◎	90	33	90	125	68	125
75	5 226676 -	937	16	◎	100	30	100	140	70	140
100	5 226677 -	1,797	8	◎	128	45	128	178	95	178
125	5 226678 -	3,010	4	◎	140	50	140	205	115	205
150	5 226679 -	6,269	3	◎	170	65	170	250	145	250
50×40	5 226686 -	372	46	◎	52	23	57	77	48	79
65×40	5 226687 -	548	30	◎	52	24	66	87	59	88
65×50	5 226697 -	548	24	◎	66	27	74	101	62	99
75×40	5 226689 -	783	30	◎	52	25	71	92	65	93
75×50	5 226690 -	783	26	◎	66	29	79	106	69	104

サイズ	コード	価格	梱包	備考	Z1	Z2	Z3	L1	L2	L3
75×65	5 226691 -	783	20	◎	90	32	95	130	72	130
100×40	5 226692 -	1,488	18	◎	52	28	82	102	78	104
100×50	5 226693 -	1,488	14	◎	66	32	90	116	82	115
100×65	5 226694 -	1,488	12	◎	90	36	107	140	86	142
100×75	5 226695 -	1,488	12	◎	100	33	110	150	83	150
125×65	5 226698 -	3,010	6	◎	90	38	120	155	103	155
125×75	5 226701 -	3,010	6	◎	100	42	124	165	107	164
125×100	5 226717 -	3,010	4	◎	128	52	140	193	117	190
150×65	5 226702 -	5,087	5	◎	90	42	130	170	122	165
150×75	5 226703 -	5,087	5	◎	100	45	135	180	125	175
150×100	5 226704 -	5,087	4	◎	128	53	152	208	133	202
150×125	5 226705 -	5,087	3	◎	140	60	152	220	140	217