

多機能加工用

スーパーエンドチッパーモジュラーヘッド MEC形

■対応チップ

アルミ用ポリッシュチップ拡張

Z○MT-L形



(先端刃)

Z○MT-LP形



(先端刃、アルミ用ポリッシュチップ)

Z○MT-R形



(外周刃)

Z○MT-RP形



(外周刃、アルミ用ポリッシュチップ)





Fig.2 外周刃



形 番	PVDコーティング		超硬合金	寸 法 (mm)					Fig.
	JC5015	JC5040		A	B	T	α°	r_ϵ	
ZDMT08T208L	●	●		7.9	6	2.78	15	0.8	1
ZDMT08T208LP			●	7.9	6	2.78	15	0.8	1
ZPMT09T208R	●	●		9	5.4	2.78	11	0.8	2
ZPMT09T208RP			●	9	5.4	2.78	11	0.8	2
ZDMT100308L	●	●		10.4	6.35	3.4	15	0.8	1
ZDMT100308LP			●	10.4	6.35	3.4	15	0.8	1
ZCMT100308R	●	●		10.4	6.35	3.4	7	0.8	2
ZCMT100308RP			●	10.4	6.35	3.4	7	0.8	2
ZDMT13T308L	●	●		12.9	7.938	3.97	15	0.8	1
ZDMT13T308LP			●	12.9	7.938	3.97	15	0.8	1
ZPMT13T308R	●	●		13.3	7.938	3.97	11	0.8	2
ZPMT13T308RP			●	13.3	7.938	3.97	11	0.8	2
ZDMT13T320L	●	●		12.9	7.938	3.97	15	2.0	1
ZDMT13T320LP			●	12.9	7.938	3.97	15	2.0	1
ZPMT13T320R	●	●		13.3	7.938	3.97	11	2.0	2
ZPMT13T320RP			●	13.3	7.938	3.97	11	2.0	2
ZPMT150408L	●	●		15.45	9.525	4.76	11	0.8	1
ZPMT150408LP			●	15.45	9.525	4.76	11	0.8	1
ZPMT160408L	●	●		16.45	9.525	4.76	11	0.8	1
ZPMT160408LP			●	16.45	9.525	4.76	11	0.8	1
ZPMT160408R	●	●		16	9.525	4.76	11	0.8	2
ZPMT160408RP			●	16	9.525	4.76	11	0.8	2
ZPMT160416L	●	●		16.45	9.525	4.76	11	1.6	1
ZPMT160416LP			●	16.45	9.525	4.76	11	1.6	1
ZPMT160416R	●	●		16	9.525	4.76	11	1.6	2
ZPMT160416RP			●	16	9.525	4.76	11	1.6	2
ZPMT160420L	●	●		16.45	9.525	4.76	11	2.0	1
ZPMT160420LP			●	16.45	9.525	4.76	11	2.0	1
ZPMT160420R	●	●		16	9.525	4.76	11	2.0	2
ZPMT160420RP			●	16	9.525	4.76	11	2.0	2
ZPMT160430L	●	●		16.45	9.525	4.76	11	3.0	1
ZPMT160430LP			●	16.45	9.525	4.76	11	3.0	1
ZPMT160430R	●	●		16	9.525	4.76	11	3.0	2
ZPMT160430RP			●	16	9.525	4.76	11	3.0	2
ZPMT160432L	●	●		16.45	9.525	4.76	11	3.2	1
ZPMT160432LP			●	16.45	9.525	4.76	11	3.2	1
ZPMT160432R	●	●		16	9.525	4.76	11	3.2	2
ZPMT160432RP			●	16	9.525	4.76	11	3.2	2
ZPMT170508R	●	●		17	11	5.56	11	0.8	2
ZPMT170516R	●	●		17	11	5.56	11	1.6	2
ZPMT170520R	●	●		17	11	5.56	11	2.0	2
ZPMT170530R	●	●		17	11	5.56	11	3.0	2
ZPMT180508L	●	●		18	11	5.56	11	0.8	1
ZPMT180516L	●	●		18	11	5.56	11	1.6	1
ZPMT180520L	●	●		18	11	5.56	11	2.0	1
ZPMT180530L	●	●		18	11	5.56	11	3.0	1

1ケース10個入りです。

●:メーカー在庫品

□:流通在庫品

☆:海外在庫品

◎:近日在庫品

○:在庫がなくなり次第廃番

※:受注生産品