



フラップホイール



…ハンドグラインダー



…電気ドリル



…ボール盤



品番	直径×幅 (mm)	軸径×軸長 (mm)	最高使用回転数	粒度分布														包装 単位	希望小売価格
				24	36	40	60	80	100	120	150	180	240	320	400	600	800		
AF2505	25×5	3×35	20,000r.p.m.				●	●	●	●	●	●	●	●	●			5	780円
AF2525	25×25	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	860円
AF3005	30×5	3×35	20,000r.p.m.				●	●	●	●	●	●	●	●	●			5	780円
AF30103	30×10	3×35	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	780円
AF30106	30×10	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	860円
AF3015	30×15	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	860円
AF3025	30×25	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	860円
AF4005	40×5	6×40	20,000r.p.m.				●	●	●	●	●	●	●	●	●			5	860円
AF4015	40×15	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	860円
AF4025	40×25	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	860円
AF4030	40×30	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	860円
AF5005	50×5	6×40	20,000r.p.m.				●	●	●	●	●	●	●	●	●			5	860円
AF5015	50×15	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	860円
AF5025	50×25	6×40	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	930円
AF5030	50×30	6×40	18,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	980円
AF6005	60×5	6×40	18,000r.p.m.				●	●	●	●	●	●	●	●	●			5	1,020円
AF6015	60×15	6×40	18,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	1,020円
AF6025	60×25	6×40	18,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	1,110円
AF6030	60×30	6×40	18,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	1,200円
AF8005	80×5	6×40	15,000r.p.m.				●	●	●	●	●	●	●	●	●			5	1,240円
AF8015	80×15	6×40	15,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	1,240円
AF8025	80×25	6×40	15,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	1,480円
AF8030	80×30	6×40	15,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	1,640円
AF10025	100×25	6×40	9,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		5	1,980円



マイクロフラップ



…ハンドグラインダー



…電気ドリル



…ボール盤



品番	直径×幅 (mm)	軸径×軸長 (mm)	最高使用回転数	粒度分布														包装 単位	希望小売価格
				24	36	40	60	80	100	120	150	180	240	320	400	600	800		
MF1005	10×5	3×30	25,000r.p.m.				●	●	●	●	●	●	●	●	●			10	690円
MF1010	10×10	3×30	25,000r.p.m.				●	●	●	●	●	●	●	●	●	●		10	690円
MF1020	10×20	3×30	25,000r.p.m.				●	●	●	●	●	●	●	●	●	●		10	690円
MF1505	15×5	3×30	25,000r.p.m.				●	●	●	●	●	●	●	●	●			10	690円
MF1510	15×10	3×30	25,000r.p.m.				●	●	●	●	●	●	●	●	●	●		10	690円
MF1520	15×20	3×30	25,000r.p.m.				●	●	●	●	●	●	●	●	●	●		10	690円
MF2005	20×5	3×30	20,000r.p.m.				●	●	●	●	●	●	●	●	●			10	690円
MF2010	20×10	3×30	20,000r.p.m.				●	●	●	●	●	●	●	●	●	●		10	690円
MF2020	20×20	3×30	20,000r.p.m.				●	●	●	●	●	●	●	●	●	●		10	690円
MF2510	25×10	3×30	20,000r.p.m.			●	●	●	●	●	●	●	●	●	●	●		10	720円