


14 径違いソケット


Reducing sockets, plain, with ribs (RS)



(呼び $\frac{3}{4}$ ~2)

15 径違いソケット(バンド付)

Reducing sockets, banded, with ribs (BRS)



(呼び $\frac{1}{4}$ ~6)

単位 mm


呼び径(A)	呼 び ①×②	品 名		L
		RS	BRS	
8×6	$\frac{1}{4} \times \frac{1}{8}$		●	25
10×6	$\frac{3}{8} \times \frac{1}{8}$		●	28
10×8	$\frac{3}{8} \times \frac{1}{4}$		●	28
15×6	$\frac{1}{2} \times \frac{1}{8}$		●	34
15×8	$\frac{1}{2} \times \frac{1}{4}$		●	34
15×10	$\frac{1}{2} \times \frac{3}{8}$		●	34
※ 20×6	$\frac{3}{4} \times \frac{1}{8}$		●	38
20×8	$\frac{3}{4} \times \frac{1}{4}$		●	38
20×10	$\frac{3}{4} \times \frac{3}{8}$		●	38
20×15	$\frac{3}{4} \times \frac{1}{2}$	●	●	38
※ 25×8	$1 \times \frac{1}{4}$		●	42
25×10	$1 \times \frac{3}{8}$		●	42
25×15	$1 \times \frac{1}{2}$	●	●	42
25×20	$1 \times \frac{3}{4}$	●	●	42
32×15	$1\frac{1}{4} \times \frac{1}{2}$	●	●	48
32×20	$1\frac{1}{4} \times \frac{3}{4}$	●	●	48
32×25	$1\frac{1}{4} \times 1$	●	●	48
※ 40×10	$1\frac{1}{2} \times \frac{3}{8}$		●	52
40×15	$1\frac{1}{2} \times \frac{1}{2}$	●	●	52
40×20	$1\frac{1}{2} \times \frac{3}{4}$	●	●	52
40×25	$1\frac{1}{2} \times 1$	●	●	52
40×32	$1\frac{1}{2} \times 1\frac{1}{4}$	●	●	52
※ 50×10	$2 \times \frac{3}{8}$		●	58
50×15	$2 \times \frac{1}{2}$	●	●	58
50×20	$2 \times \frac{3}{4}$	●	●	58
50×25	2×1	●	●	58
50×32	$2 \times 1\frac{1}{4}$	●	●	58
50×40	$2 \times 1\frac{1}{2}$	●	●	58
65×15	$2\frac{1}{2} \times \frac{1}{2}$		●	65
65×20	$2\frac{1}{2} \times \frac{3}{4}$		●	65
65×25	$2\frac{1}{2} \times 1$		●	65

単位 mm

呼び径(A)	呼 び ①×②	品 名		L
		RS	BRS	
65×32	$2\frac{1}{2} \times 1\frac{1}{4}$		●	65
65×40	$2\frac{1}{2} \times 1\frac{1}{2}$		●	65
65×50	$2\frac{1}{2} \times 2$		●	65
△□ 80×15	$3 \times \frac{1}{2}$		●	72
80×20	$3 \times \frac{3}{4}$		●	72
80×25	3×1		●	72
80×32	$3 \times 1\frac{1}{4}$		●	72
80×40	$3 \times 1\frac{1}{2}$		●	72
80×50	3×2		●	72
80×65	$3 \times 2\frac{1}{2}$		●	72
△□ 100×15	$4 \times \frac{1}{2}$		●	85
△□ 100×20	$4 \times \frac{3}{4}$		●	85
△□ 100×25	4×1		●	85
□ 100×32	$4 \times 1\frac{1}{4}$		●	85
□ 100×40	$4 \times 1\frac{1}{2}$		●	85
100×50	4×2		●	85
100×65	$4 \times 2\frac{1}{2}$		●	85
100×80	4×3		●	85
※ 125×32	$5 \times 1\frac{1}{4}$		●	95
□ 125×40	$5 \times 1\frac{1}{2}$		●	95
□ 125×50	5×2		●	95
□ 125×65	$5 \times 2\frac{1}{2}$		●	95
125×80	5×3		●	95
125×100	5×4		●	95
□ 150×40	$6 \times 1\frac{1}{2}$		●	105
□ 150×50	6×2		●	105
□ 150×65	$6 \times 2\frac{1}{2}$		●	105
□ 150×80	6×3		●	105
150×100	6×4		●	105
150×125	6×5		●	105

16 めすおすソケット

Extension Pieces, plain (X)



(呼び $\frac{3}{8}$ ~2)

単位 mm

呼び径(A)	呼 び	L
10	$\frac{3}{8}$	32
15	$\frac{1}{2}$	40
20	$\frac{3}{4}$	48
25	1	55
32	$1\frac{1}{4}$	60
40	$1\frac{1}{2}$	65
50	2	70