



3300M・3300A

六角ディープソケット



3305M・3305A

12角ディープソケット



3300M 3305M (mm)	D ₁ (mm)	D ₂ (mm)	ℓ (mm)	H (mm)	L (mm)	重量 (g)	包装個数 (pcs.)	希望小 売価格
5.5	8.9	17.3	6.5	41.5	55	37	10	¥ 1,320
6	9.9	17.3	7	41.5	55	37	10	¥ 1,320
7	10.6	17.3	8	41.5	55	37	10	¥ 1,320
8	12	17.3	9	41.5	55	40	10	¥ 1,320
9	13	17.3	10	41.5	55	42	10	¥ 1,320
10	14.5	17.3	11	41.5	55	46	10	¥ 1,320
11	16	17.2	12	41.5	55	51	10	¥ 1,320
12	16.8	17.2	13	41.5	55	52	10	¥ 1,320
13	18	17	14	41.5	55	53	10	¥ 1,450
14	20	18	16	41.5	55	60	10	¥ 1,450
15	21	20	16	40.5	55	74	10	¥ 1,450
16	22	20	17	40.5	55	76	10	¥ 1,450
17	23.5	22	18	40.5	55	93	10	¥ 1,480
18	24.5	23	19	39.5	55	98	10	¥ 1,570
19	25	24	20	39.5	55	98	10	¥ 1,570
20	26	25	21	49.5	65	126	10	¥ 1,810
21	27	26	22	49.5	65	126	10	¥ 1,680
22	29	28	23	48.5	65	163	10	¥ 1,720
23	30	29	24	48.5	65	168	10	¥ 1,850
24	31	30	25	47.5	65	191	10	¥ 1,950
25	33	30	26	47.5	65	199	10	¥ 2,190
26	34	31	27	47.5	65	209	10	¥ 2,080
27	35	32.5	28	47.5	65	218	10	¥ 2,080

3300A 3305A (inch)	D ₁ (mm)	D ₂ (mm)	ℓ (mm)	H (mm)	L (mm)	重量 (g)	包装個数 (pcs.)	希望小 売価格
New 7/32	8.9	17.3	6	41.5	55	35	10	¥ 1,500
1/4	9.9	17.3	7	41.5	55	37	10	¥ 1,500
5/16	12	17.3	9	41.5	55	40	10	¥ 1,500
11/32	12.3	17.3	10	41.5	55	41	10	¥ 1,500
3/8	14	17.3	11	41.5	55	46	10	¥ 1,500
7/16	16	17.2	12	41.5	55	51	10	¥ 1,500
1/2	18	17	14	41.5	55	53	10	¥ 1,650
9/16	20	18	16	41.5	55	60	10	¥ 1,650
19/32	21	20	16	40.5	55	74	10	¥ 1,650
5/8	22	20	17	40.5	55	76	10	¥ 1,650
11/16	23.5	22	18	40.5	55	93	10	¥ 1,650
3/4	25	24	20	39.5	55	98	10	¥ 1,740
13/16	27	26	22	49.5	65	126	10	¥ 1,950
7/8	29	28	23	48.5	65	163	10	¥ 1,950
15/16	31	30	25	47.5	65	191	10	¥ 2,160

RS3300M/8

六角ディープソケット

レールセット

RS3305M/8

12角ディープソケット

レールセット



RS3300M/8	8ヶ組/レール200mm	重量 (g)	希望小 売価格
8, 10, 11, 12, 13, 14, 17, 19		540	¥ 11,300

RS3305M/8	8ヶ組/レール200mm	重量 (g)	希望小 売価格
8, 10, 11, 12, 13, 14, 17, 19		540	¥ 11,300

RS3300M/12

六角ディープソケット

レールセット

RS3305M/12

12角ディープソケット

レールセット



RS3300M/12	12ヶ組/レール300mm	重量 (g)	希望小 売価格
8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19		878	¥ 17,200

RS3305M/12	12ヶ組/レール300mm	重量 (g)	希望小 売価格
8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19		878	¥ 17,200

RS3300A/9

六角ディープソケット

レールセット

RS3305A/9

12角ディープソケット

レールセット



RS3300A/9	9ヶ組/レール200mm	重量 (g)	希望小 売価格
1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4		628	¥ 14,400

RS3305A/9	9ヶ組/レール200mm	重量 (g)	希望小 売価格
1/4, 5/16, 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4		628	¥ 14,400