

旋削用インサート[ポジ]




DCMT 07 02 04- MS

切れ刃長 厚さ コーナR プレーカ
* 詳細はA002ページをご参照ください。

被削材別切りくず有効範囲

仕上げ切削... 軽切削... 中切削...



切削状態(目安): ●: 安定切削 ●: 一般切削 * : 不安定切削

被削材	呼び記号		コーティング																	サメット	コーテッド サメット	超硬合金			参照ホルダ															
	P 鋼	M ステンレス鋼	UE6105	UE6110	UE6020	MC6015	MC6025	UH6400	MS6015	MC7025	MP7035	US7020	US735	US905	MC5005	MC5015	UC5105	UC5115	MH5115	MP9005	MP9015	VP05RT	VP10RT	VP15TF		UP20M	NX2525	NX3035	MP3025	AP25N	VP25N	VP45N	UTi20T	HTi05T	HTi10	RT9010	MT9005	TF15		
MS NEW 中切削	DCMT070204-MS	0.4																		●	●																			
	DCMT070208-MS	0.8																		●	●																			
	DCMT11T304-MS	0.4																			●	●																	●	
	DCMT11T308-MS	0.8																			●	●																	●	
	DCMT11T312-MS	1.2																			●	●																	●	
Standard 中切削	DCMT070202	0.2	●	▲											●												●	●	●											
	DCMT070204	0.4	●	▲											●												●	●	●											
	DCMT070208	0.8	●													●											●	●	●											
	DCMT11T302	0.2	●	▲												●											●	●	●											
	DCMT11T304	0.4	●	▲												●											●	●	●											
	DCMT11T308	0.8	●	▲												●											●	●	●											
	DCMT11T312	1.2	●																																					
DCMT150404	0.4	●	▲												●											●	●	●												
DCMT150408	0.8	●	▲												●											●	●	●												
DCMT150412	1.2	●																																						
MV 中切削	DCMT070202-MV	0.2	●	▲	●										▲	●									●	●	●	●												
	DCMT070204-MV	0.4	●	▲	●										▲	●	●								●	●	●	●												
	DCMT070208-MV	0.8	●	▲	●										▲	●	●								●	●	●	●												
	DCMT11T302-MV	0.2	●	▲	●											▲	●									●	●	●	●											
	DCMT11T304-MV	0.4	●	▲	●											▲	●	●								●	●	●	●											
	DCMT11T308-MV	0.8	●	▲	●											▲	●	●								●	●	●	●											
R/L-SR 中切削	DCET0702V3R-SR	0.03																									●													
	DCET0702V3L-SR	0.03																									●													
	DCET070201R-SR	0.1																									●													
	DCET070201L-SR	0.1																									●													
	DCET070202R-SR	0.2																									●													
	DCET070202L-SR	0.2																									●													
	DCET070204R-SR	0.4																									●													
	DCET070204L-SR	0.4																									●													
	DCET11T3V3R-SR	0.03																									●													
	DCET11T3V3L-SR	0.03																									●													

● = NEW

●: 標準在庫品 ▲: 現在標準在庫品で将来新製品と置き換わる製品
(1ケース10個入りです)