


KDZ-HP レギュラー (クーラントホールあり) Type C



型番	在庫	DC	外径公差	LCF	LN	DCON	OAL	メーカー希望小売価格(円)
KDZ0300X3.0S030C-HP	●	3.0	$0_{-0.010}^0$	13.5	15.5	3	68	9,380
KDZ0310X3.0S040C-HP	●	3.1	$0_{-0.012}^0$	14.0	16.0	4	72	9,380
KDZ0320X3.0S040C-HP	●	3.2		14.4	16.4			
KDZ0330X3.0S040C-HP	●	3.3		14.9	16.9			
KDZ0340X3.0S040C-HP	●	3.4		15.3	17.3			
KDZ0350X3.0S040C-HP	●	3.5		15.8	17.8			
KDZ0360X3.0S040C-HP	●	3.6	$0_{-0.012}^0$	16.2	18.2	4	72	9,640
KDZ0370X3.0S040C-HP	●	3.7		16.7	18.7			
KDZ0380X3.0S040C-HP	●	3.8		17.1	19.1			
KDZ0390X3.0S040C-HP	●	3.9		17.6	19.6			
KDZ0400X3.0S040C-HP	●	4.0		18.0	20.0			
KDZ0410X3.0S050C-HP	●	4.1	$0_{-0.012}^0$	18.5	20.5	5	80	10,300
KDZ0420X3.0S050C-HP	●	4.2		18.9	20.9			
KDZ0430X3.0S050C-HP	●	4.3		19.4	21.4			
KDZ0440X3.0S050C-HP	●	4.4		19.8	21.8			
KDZ0450X3.0S050C-HP	●	4.5		20.3	22.3			
KDZ0460X3.0S050C-HP	●	4.6	$0_{-0.012}^0$	20.7	22.7	5	80	10,390
KDZ0470X3.0S050C-HP	●	4.7		21.2	23.2			
KDZ0480X3.0S050C-HP	●	4.8		21.6	23.6			
KDZ0490X3.0S050C-HP	●	4.9		22.1	24.1			
KDZ0500X3.0S050C-HP	●	5.0		22.5	24.5			
KDZ0510X3.0S060C-HP	●	5.1	$0_{-0.012}^0$	23.0	25.0	6	82	10,980
KDZ0520X3.0S060C-HP	●	5.2		23.4	25.4			
KDZ0530X3.0S060C-HP	●	5.3		23.9	25.9			
KDZ0540X3.0S060C-HP	●	5.4		24.3	26.3			
KDZ0550X3.0S060C-HP	●	5.5		24.8	26.8			
KDZ0560X3.0S060C-HP	●	5.6	$0_{-0.012}^0$	25.2	27.2	6	82	11,220
KDZ0570X3.0S060C-HP	●	5.7		25.7	27.7			
KDZ0580X3.0S060C-HP	●	5.8		26.1	28.1			
KDZ0590X3.0S060C-HP	●	5.9		26.6	28.6			
KDZ0600X3.0S060C-HP	●	6.0		27.0	29.0			
KDZ0610X3.0S070C-HP	●	6.1	$0_{-0.015}^0$	27.5	29.5	7	88	12,230
KDZ0620X3.0S070C-HP	●	6.2		27.9	29.9			
KDZ0630X3.0S070C-HP	●	6.3		28.4	30.4			
KDZ0640X3.0S070C-HP	●	6.4		28.8	30.8			
KDZ0650X3.0S070C-HP	●	6.5		29.3	31.3			
KDZ0660X3.0S070C-HP	●	6.6	$0_{-0.015}^0$	29.7	31.7	7	88	12,300
KDZ0670X3.0S070C-HP	●	6.7		30.2	32.2			
KDZ0680X3.0S070C-HP	●	6.8		30.6	32.6			
KDZ0690X3.0S070C-HP	●	6.9		31.1	33.1			
KDZ0700X3.0S070C-HP	●	7.0		31.5	33.5			
KDZ0710X3.0S080C-HP	●	7.1	$0_{-0.015}^0$	32.0	34.0	8	94	13,490
KDZ0720X3.0S080C-HP	●	7.2		32.4	34.4			
KDZ0730X3.0S080C-HP	●	7.3		32.9	34.9			
KDZ0740X3.0S080C-HP	●	7.4		33.3	35.3			
KDZ0750X3.0S080C-HP	●	7.5		33.8	35.8			

型番	在庫	DC	外径公差	LCF	LN	DCON	OAL	メーカー希望小売価格(円)
KDZ0760X3.0S080C-HP	●	7.6	$0_{-0.015}^0$	34.2	36.2	8	94	13,490
KDZ0770X3.0S080C-HP	●	7.7		34.7	36.7			
KDZ0780X3.0S080C-HP	●	7.8		35.1	37.1			
KDZ0790X3.0S080C-HP	●	7.9		35.6	37.6			
KDZ0800X3.0S080C-HP	●	8.0		36.0	38.0			
KDZ0810X3.0S090C-HP	●	8.1	$0_{-0.015}^0$	36.5	38.5	9	100	14,910
KDZ0820X3.0S090C-HP	●	8.2		36.9	38.9			
KDZ0830X3.0S090C-HP	●	8.3		37.4	39.4			
KDZ0840X3.0S090C-HP	●	8.4		37.8	39.8			
KDZ0850X3.0S090C-HP	●	8.5		38.3	40.3			
KDZ0860X3.0S090C-HP	●	8.6	$0_{-0.015}^0$	38.7	40.7	9	100	15,060
KDZ0870X3.0S090C-HP	●	8.7		39.2	41.2			
KDZ0880X3.0S090C-HP	●	8.8		39.6	41.6			
KDZ0890X3.0S090C-HP	●	8.9		40.1	42.1			
KDZ0900X3.0S090C-HP	●	9.0		40.5	42.5			
KDZ0910X3.0S100C-HP	●	9.1	$0_{-0.015}^0$	41.0	43.0	10	106	16,670
KDZ0920X3.0S100C-HP	●	9.2		41.4	43.4			
KDZ0930X3.0S100C-HP	●	9.3		41.9	43.9			
KDZ0940X3.0S100C-HP	●	9.4		42.3	44.3			
KDZ0950X3.0S100C-HP	●	9.5		42.8	44.8			
KDZ0960X3.0S100C-HP	●	9.6	$0_{-0.015}^0$	43.2	45.2	10	106	16,670
KDZ0970X3.0S100C-HP	●	9.7		43.7	45.7			
KDZ0980X3.0S100C-HP	●	9.8		44.1	46.1			
KDZ0990X3.0S100C-HP	●	9.9		44.6	46.6			
KDZ1000X3.0S100C-HP	●	10.0		45.0	47.0			
KDZ1010X3.0S110C-HP	●	10.1	$0_{-0.018}^0$	45.5	47.5	11	116	18,750
KDZ1020X3.0S110C-HP	●	10.2		45.9	47.9			
KDZ1030X3.0S110C-HP	●	10.3		46.4	48.4			
KDZ1040X3.0S110C-HP	●	10.4		46.8	48.8			
KDZ1050X3.0S110C-HP	●	10.5		47.3	49.3			
KDZ1060X3.0S110C-HP	●	10.6	$0_{-0.018}^0$	47.7	49.7	11	116	19,000
KDZ1070X3.0S110C-HP	●	10.7		48.2	50.2			
KDZ1080X3.0S110C-HP	●	10.8		48.6	50.6			
KDZ1090X3.0S110C-HP	●	10.9		49.1	51.1			
KDZ1100X3.0S110C-HP	●	11.0		49.5	51.5			
KDZ1110X3.0S120C-HP	●	11.1	$0_{-0.018}^0$	50.0	52.0	12	122	20,670
KDZ1120X3.0S120C-HP	●	11.2		50.4	52.4			
KDZ1130X3.0S120C-HP	●	11.3		50.9	52.9			
KDZ1140X3.0S120C-HP	●	11.4		51.3	53.3			
KDZ1150X3.0S120C-HP	●	11.5		51.8	53.8			
KDZ1160X3.0S120C-HP	●	11.6	$0_{-0.018}^0$	52.2	54.2	12	122	20,670
KDZ1170X3.0S120C-HP	●	11.7		52.7	54.7			
KDZ1180X3.0S120C-HP	●	11.8		53.1	55.1			
KDZ1190X3.0S120C-HP	●	11.9		53.6	55.6			
KDZ1200X3.0S120C-HP	●	12.0		54.0	56.0			

●: 標準在庫

加工深さは2.0D (2.0 × DC) を目安としてください
2D以上の深さとなる場合はステップ加工を推奨します