


MC6100シリーズ

ネガティブインサート(穴つき)

M級精度



(mm)

呼び記号	切削領域	NEW			IC	S	RE	D1
		MC6115	MC6125	MC6135				
SNMG120408-RP	R	●	●	●	12.7	4.76	0.8	5.16
SNMG120412-RP	R	●	●	●	12.7	4.76	1.2	5.16
SNMG120416-RP	R	●	●	●	12.7	4.76	1.6	5.16
SNMG150612-RP	R	●	●	●	15.875	6.35	1.2	6.35
SNMG150616-RP	R	●	●	●	15.875	6.35	1.6	6.35
SNMG190612-RP	R	●	●	●	19.05	6.35	1.2	7.93
SNMG190616-RP	R	●	●	●	19.05	6.35	1.6	7.93
SNMG120408-GH	R	●	●	○	12.7	4.76	0.8	5.16
SNMG120412-GH	R	●	●	○	12.7	4.76	1.2	5.16
SNMG120416-GH	R	●	●	○	12.7	4.76	1.6	5.16
SNMG150612-GH	R	●	●	○	15.875	6.35	1.2	6.35
SNMG150616-GH	R	●	○	○	15.875	6.35	1.6	6.35
SNMG190612-GH	R	●	●	○	19.05	6.35	1.2	7.93
SNMG190616-GH	R	●	●	○	19.05	6.35	1.6	7.93
SNMM120408-HX	H	○	○	●	12.7	4.76	0.8	5.16
SNMM120412-HX	H	○	○	●	12.7	4.76	1.2	5.16
SNMM150612-HX	H	○	○	●	15.875	6.35	1.2	6.35
SNMM190612-HX	H	●	○	●	19.05	6.35	1.2	7.93
SNMM190616-HX	H	●	○	●	19.05	6.35	1.6	7.93
SNMM190624-HX	H	●	○	●	19.05	6.35	2.4	7.93
SNMM250724-HX	H	●	○	○	25.4	7.94	2.4	9.12
SNMM250924-HX	H	●	○	○	25.4	9.52	2.4	9.12
SNMM120408-HL	H	○	○	●	12.7	4.76	0.8	5.16
SNMM120412-HL	H	○	○	●	12.7	4.76	1.2	5.16
SNMM150612-HL	H	○	○	●	15.875	6.35	1.2	6.35
SNMM190612-HL	H	○	○	●	19.05	6.35	1.2	7.93
SNMM190616-HL	H	○	○	●	19.05	6.35	1.6	7.93
SNMM190624-HL	H	○	○	●	19.05	6.35	2.4	7.93
SNMM250724-HR	H	●	○	○	25.4	7.94	2.4	9.12
SNMM250924-HR	H	●	○	○	25.4	9.52	2.4	9.12
SNMM190616-HV	H	●	○	●	19.05	6.35	1.6	7.93
SNMM190624-HV	H	●	○	●	19.05	6.35	2.4	7.93
SNMM250724-HV	H	●	○	○	25.4	7.94	2.4	9.12
SNMM250924-HV	H	●	○	○	25.4	9.52	2.4	9.12

呼び記号	切削領域	NEW			IC	S	RE	D1
		MC6115	MC6125	MC6135				
SNMM120408-HZ	H	●	○	●	12.7	4.76	0.8	5.16
SNMM120412-HZ	H	●	○	●	12.7	4.76	1.2	5.16
SNMM150612-HZ	H	●	○	○	15.875	6.35	1.2	6.35
SNMM190612-HZ	H	●	○	○	19.05	6.35	1.2	7.93
SNMM190616-HZ	H	●	○	○	19.05	6.35	1.6	7.93
SNMM150612-HM	H	○	○	●	15.875	6.35	1.2	6.35
SNMM190612-HM	H	○	○	●	19.05	6.35	1.2	7.93
SNMM190616-HM	H	○	○	●	19.05	6.35	1.6	7.93
SNMM190624-HM	H	○	○	●	19.05	6.35	2.4	7.93
SNMM250724-HM	H	●	○	○	25.4	7.94	2.4	9.12
SNMM250924-HM	H	●	○	○	25.4	9.52	2.4	9.12

● = NEW

●：標準在庫品 ○：近日発売

(インサートは、1ケース 10個入りです)