

**PB 8200 S**

**Socket wrenches with SwissGrip handle, with hexagon portion**

**Chiavi a bussola con impugnatura SwissGrip per dadi esagonali, con esagono**



PB 8200.S 8-120	5	120	230	10	101		10	7 610733 068616
PB 8200.S 9-140	-	140	250	10	120		10	7 610733 068623
PB 8200.S 10-160	6	160	270	10	133		10	7 610733 068630
PB 8200.S 11-180	7	180	300	13	183		10	7 610733 068647
PB 8200.S 12-190	-	190	310	13	210		10	7 610733 068654
PB 8200.S 13-200	8	200	320	17	262		10	7 610733 068661

**PB 8205**

**Hex keys with handle for hexagon socket screws**

**Giraviti con impugnatura per viti ad esagono incassato**




PB 8205.0,71-40	0,71	1.4	-	40	117	13	10	7 610733 089253
PB 8205.0,89-40	0,89	2	-	40	117	13	10	7 610733 089260
PB 8205.1,27-50	1,27	2.5	1.4	50	127	11	10	7 610733 089277
PB 8205.1,5-70	1,5	3	1.6-2	70	147	13	10	7 610733 089284
PB 8205.2-80	2	4	2.5	80	157	14	10	7 610733 089291
PB 8205.2,5-90	2,5	5	3	90	170	20	10	7 610733 079100
PB 8205.3-100	3	6	4	100	190	29	10	7 610733 079117
PB 8205.4-120	4	8	5	120	220	50	10	7 610733 079124
PB 8205.5-140	5	10	6	140	245	73	10	7 610733 079131
PB 8205.6-160	6	12-14	8	160	270	103	10	7 610733 079148
PB 8205.8-180	8	16	10	180	300	167	10	7 610733 079155

**PB 8206 S**

**Ball point hex keys with handle for hexagon socket screws**

**Giraviti con punta sferica e con impugnatura per viti ad esagono incassato**



PB 8206.S1,27-50	1,27	2.5	1.4	50	127	12	10	7 610733 089307
PB 8206.S1,5-70	1,5	3	1.6-2	70	147	12	10	7 610733 089314
PB 8206.S2-80	2	4	2.5	80	157	13	10	7 610733 089321
PB 8206.S2,5-90	2,5	5	3	90	167	15	10	7 610733 089338
PB 8206.S3-100	3	6	4	100	180	22	10	7 610733 079162
PB 8206.S4-120	4	8	5	120	210	37	10	7 610733 079179
PB 8206.S5-140	5	10	6	140	235	55	10	7 610733 079186
PB 8206.S6-160	6	12-14	8	160	260	81	10	7 610733 079193
PB 8206.S8-180	8	16	10	180	290	148	10	7 610733 079780