



インサート



呼び記号	在庫		寸法 (mm)			対応ホルダ
	VP15TF	VP10H	CDI	LF	S	
STAWN1000TH	●	□	10.0	3.8	4.6	STAWSS1000S16 STAWSN1000S16 STAWMN1000S16 STAWLN1000S16
STAWN1010TH	●	□	10.1	3.8	4.6	
STAWN1020TH	●	□	10.2	3.8	4.6	
STAWN1030TH	●	□	10.3	3.8	4.6	
STAWN1040TH	●	□	10.4	3.8	4.6	
STAWN1050TH	●	□	10.5	4.0	4.8	STAWSS1050S16 STAWSN1050S16 STAWMN1050S16 STAWLN1050S16
STAWN1060TH	●	□	10.6	4.0	4.8	
STAWN1070TH	●	□	10.7	4.0	4.8	
STAWN1080TH	●	□	10.8	4.0	4.8	
STAWN1090TH	●	□	10.9	4.0	4.8	
STAWN1100TH	●	□	11.0	4.2	5.1	STAWSS1100S16 STAWSN1100S16 STAWMN1100S16 STAWLN1100S16
STAWN1110TH	●	□	11.1	4.2	5.1	
STAWN1120TH	●	□	11.2	4.2	5.1	
STAWN1130TH	●	□	11.3	4.2	5.1	
STAWN1140TH	●	□	11.4	4.2	5.1	
STAWN1150TH	●	□	11.5	4.4	5.3	STAWSS1150S16 STAWSN1150S16 STAWMN1150S16 STAWLN1150S16
STAWN1160TH	●	□	11.6	4.4	5.3	
STAWN1170TH	●	□	11.7	4.4	5.3	
STAWN1180TH	●	□	11.8	4.4	5.3	
STAWN1190TH	●	□	11.9	4.4	5.3	
STAWN1200TH	●	□	12.0	4.6	5.5	STAWSS1200S16 STAWSN1200S16 STAWMN1200S16 STAWLN1200S16
STAWN1210TH	●	□	12.1	4.6	5.5	
STAWN1220TH	●	□	12.2	4.6	5.5	
STAWN1230TH	●	□	12.3	4.6	5.5	
STAWN1240TH	●	□	12.4	4.6	5.5	
STAWN1250TH	●	□	12.5	4.8	5.8	STAWSS1250S16 STAWSN1250S16 STAWMN1250S16 STAWLN1250S16
STAWN1260TH	●	□	12.6	4.8	5.8	
STAWN1270TH	●	□	12.7	4.8	5.8	
STAWN1280TH	●	□	12.8	4.8	5.8	
STAWN1290TH	●	□	12.9	4.8	5.8	
STAWN1300TH	●	□	13.0	4.9	6.0	STAWSS1300S16 STAWSN1300S16 STAWMN1300S16 STAWLN1300S16
STAWN1310TH	●	□	13.1	4.9	6.0	
STAWN1320TH	●	□	13.2	4.9	6.0	
STAWN1330TH	●	□	13.3	4.9	6.0	
STAWN1340TH	●	□	13.4	4.9	6.0	
STAWN1350TH	●	□	13.5	5.1	6.2	STAWSS1350S16 STAWSN1350S16 STAWMN1350S16 STAWLN1350S16
STAWN1360TH	●	□	13.6	5.1	6.2	
STAWN1370TH	●	□	13.7	5.1	6.2	
STAWN1380TH	●	□	13.8	5.1	6.2	
STAWN1390TH	●	□	13.9	5.1	6.2	

●: 標準在庫品 □: 受注生産品
(1ケース1個入りです)