

# 黄銅 ⊕ ⊖ 丸皿小ねじ

00010202

黄銅

M3.5

長さ	入り数	ニッケル
6	3000×14	●

# ⊕ トラス小ねじ



00000003

鉄

00010003

黄銅

00020003

ステンレス

00120003

SUS 316L

00170003


SUS 430

00060003

アルミ

00090003

チタン



ねじの呼び (d)	ピッチ P	十字穴の番号	dk		K		m	q(十字穴深さ)	
			基準寸法	許容差	基準寸法	許容差		参考	最大
M2	0.4	1	4.5	0 -0.4	1.2	±0.1	2.2	1.01	0.65
M2.3	0.4		5.2		1.4		2.4	1.21	0.85
M2.5	0.45		5.7		1.5		2.5	1.32	0.95
M2.6	0.45		5.9		1.6		2.6	1.42	1.05
M3	0.5		6.9		1.9		2.9	1.72	1.34
M3.5	0.6	2	8.1	0 -0.5	2.2	±0.15	4.0	1.83	1.30
M4	0.7		9.4		2.5		4.3	2.13	1.60
M5	0.8		11.8		3.1		5.0	2.83	2.29
M6	1.0	3	14	0 -0.7	3.7	±0.2	6.3	2.86	2.31
M8	1.25		17.8		4.8		7.8	4.36	3.78
M10	1.5	4	21	0 -1.0	5.1	±0.4	9.5	5.40	4.60

		M2.0																チタン		
長さ	入り数	鉄																		
		生地	クロム	クロメート	三価ホウ酸	三価フッ素	ニッケル	クロム	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	黄銅	ステンレス
		生地	クロム	クロメート	三価ホウ酸	三価フッ素	ニッケル	クロム	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	亜鉛	黄銅	ステンレス	チタン
2	10000×18																			
2	10000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
3	10000×18																			
3	10000×20																			
3	8000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
4	10000×14																			●
4	10000×18																			
4	8000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
5	7000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
5	8000×18																			●
6	6000×18																			
6	6000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
6	7000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
8	5000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
8	6000×18																			●
10	4000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
10	5000×18																			●
12	3500×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
12	4000×18																			●
14	2500×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
14	4000×18																			●
15	2500×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
15	4000×18																			●
16	2200×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
16	3000×18																			●
18	2000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
18	3000×18																			●
20	1800×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●	
20	2500×18																			●

小ねじ  
マフクロねじ  
組込みねじ  
タツピンねじ  
タツタイト  
ハイテクねじ  
いたすら防止ねじ  
建材用スクリュー  
ボルト  
キャップボルト  
ドリルねじ  
座金  
つまみねじ  
ナット  
樹脂製品  
アンカーボルト