

30B オイレス #300 ブッシュ




適用する内径、外径、長さから Part No. を選んでください。

(例) 内径 25mm、外径 37mm、長さ 20mm の場合

30B - 253720

Part No. でご指示ください。



●オイレス#300は、油中または定期的に給油
(給脂)してご使用ください。

内径		外径		長さ L 公差 -0.2													圧入後 内径公差 (参考値)
φd	公差	φD	公差	5	6	8	10	12	15	16	20	25	30	35	40	50	
5	$+0.058$ $+0.040$	8	$+0.034$ $+0.019$	050805	050806	050808											$+0.030$ $+0.012$
6	$+0.058$ $+0.040$	10	$+0.034$ $+0.019$	061005	061006	061008	061010										$+0.030$ $+0.012$
8	$+0.068$ $+0.046$	12	$+0.041$ $+0.023$		081206	081208	081210	081212	081215								$+0.034$ $+0.012$
10	$+0.068$ $+0.046$	14	$+0.041$ $+0.023$		101406	101408	101410	101412	101415		101420						$+0.034$ $+0.012$
10	$+0.068$ $+0.046$	16	$+0.041$ $+0.023$		101606	101608	101610	101612	101615		101620						$+0.045$ $+0.023$
10	$+0.068$ $+0.046$	18	$+0.041$ $+0.023$			101808	101810	101812	101815		101820						$+0.045$ $+0.023$
12	$+0.068$ $+0.041$	18	$+0.041$ $+0.023$			121808	121810	121812	121815	121816	121820	121825					$+0.045$ $+0.018$
12	$+0.068$ $+0.041$	20	$+0.049$ $+0.028$				122010	122012	122015		122020	122025					$+0.040$ $+0.013$
14	$+0.068$ $+0.041$	20	$+0.049$ $+0.028$				142010	142012	142015		142020	142025					$+0.040$ $+0.013$
14	$+0.068$ $+0.041$	22	$+0.049$ $+0.028$				142210	142212	142215		142220	142225					$+0.040$ $+0.013$
15	$+0.068$ $+0.041$	22	$+0.049$ $+0.028$						152215	152216	152220	152225					$+0.040$ $+0.013$
16	$+0.068$ $+0.041$	22	$+0.049$ $+0.028$						162215	162216	162220	162225	162230	162235			$+0.040$ $+0.013$
16	$+0.068$ $+0.041$	25	$+0.049$ $+0.028$						162515		162520	162525	162530				$+0.040$ $+0.013$
18	$+0.068$ $+0.041$	25	$+0.049$ $+0.028$						182515		182520	182525	182530				$+0.040$ $+0.013$
18	$+0.068$ $+0.041$	28	$+0.049$ $+0.028$						182815		182820	182825	182830				$+0.040$ $+0.013$
20	$+0.068$ $+0.055$	28	$+0.049$ $+0.028$						202815	202816	202820	202825	202830	202835	202840		$+0.060$ $+0.027$
20	$+0.068$ $+0.055$	30	$+0.049$ $+0.028$								203020	203025	203030	203035	203040		$+0.060$ $+0.027$
22	$+0.068$ $+0.055$	30	$+0.049$ $+0.028$								223020	223025	223030		223040		$+0.060$ $+0.027$
22	$+0.068$ $+0.055$	32	$+0.059$ $+0.034$								223220	223225	223230		223240		$+0.054$ $+0.021$
25	$+0.068$ $+0.055$	33	$+0.059$ $+0.034$							253316	253320	253325	253330		253340	253350	$+0.054$ $+0.021$
25	$+0.068$ $+0.055$	35	$+0.059$ $+0.034$								253520	253525	253530	253535	253540	253550	$+0.054$ $+0.021$
25	$+0.068$ $+0.055$	37	$+0.059$ $+0.034$								253720		253730		253740		$+0.054$ $+0.021$
28	$+0.068$ $+0.055$	38	$+0.059$ $+0.034$									283825			283840		$+0.054$ $+0.021$
28	$+0.068$ $+0.055$	40	$+0.059$ $+0.034$									284025			284040		$+0.054$ $+0.021$
30	$+0.068$ $+0.055$	38	$+0.059$ $+0.034$								303820	303825	303830		303840	303850	$+0.054$ $+0.021$
30	$+0.068$ $+0.055$	40	$+0.059$ $+0.034$								304020	304025	304030	304035	304040	304050	$+0.054$ $+0.021$
30	$+0.068$ $+0.055$	42	$+0.059$ $+0.034$									304225	304230		304240		$+0.054$ $+0.021$
32	$+0.112$ $+0.073$	42	$+0.059$ $+0.034$										324230		324240		$+0.078$ $+0.039$
32	$+0.112$ $+0.073$	45	$+0.059$ $+0.034$										324530		324540		$+0.078$ $+0.039$

※圧入後内径公差は参考値です。