

## G-LIST No. | SH1004

## 管用平行ねじ切り丸ダイス

Round Dies • Adjustable type for parallel pipe threads

## SPD(SKS)

管用平行ねじ(PS)

PS: previous JIS

(単位:mm) (Unit:mm)

ツール No. EDP No.	外径 D	ねじ	在庫 Stock	標準価格 (Yen)
47671	38	PS1/8 - 28	B	7,200
47672		PS1/4 - 19		7,200
47673		PS3/8 - 19		7,200
47681	50	PS1/8 - 28	D	16,700
47682		PS1/4 - 19	B	11,900
47683		PS3/8 - 19		11,900
47684		PS1/2 - 14	D	11,900
47685		PS5/8 - 14		16,200
47686		PS3/4 - 14		16,700
47691		PS3/4 - 14		34,000
47701		63	PS3/4 - 14	D
47702	PS7/8 - 14		45,900	
47703	PS1 - 11		37,700	
47704	PS1-1/8 - 11		45,900	
47705	PS1-1/4 - 11		37,700	
47711	75	PS1 - 11	D	76,300
47713		PS1-1/4 - 11		76,300
47715		PS1-1/2 - 11		76,300
47721		PS1-3/4 - 11		132,000
47722	100	PS2 - 11		132,000

## G-LIST No. | SH1004

## 管用平行ねじ切り丸ダイス

Round Dies • Adjustable type for parallel pipe threads

## SPD(SKS)

管用平行ねじ(PF)

PF: previous JIS

(単位:mm) (Unit:mm)

ツール No. EDP No.	外径 D	ねじ	在庫 Stock	標準価格 (Yen)
47601	38	PF1/8 - 28	B	7,200
47602		PF1/4 - 19		7,200
47603		PF3/8 - 19		7,200
47611	50	PF1/8 - 28	D	16,700
47612		PF1/4 - 19	B	11,900
47613		PF3/8 - 19		11,900
47614		PF1/2 - 14	D	11,900
47615		PF5/8 - 14		18,500
47616		PF3/4 - 14		16,700
47617		PF7/8 - 14		18,500
47621		63	PF3/4 - 14	D
47622	PF1 - 11		34,000	
47631	PF3/4 - 14		37,700	
47632	PF7/8 - 14		45,900	
47633	PF1 - 11		37,700	
47634	75	PF1-1/8 - 11	D	45,900
47635		PF1-1/4 - 11		37,700
47641		PF1 - 11		76,300
47644		PF1-3/8 - 11		76,300
47645	100	PF1-1/2 - 11	D	76,300
47651		PF1-3/4 - 11		132,000
47652		PF2 - 11		132,000

## G-LIST No. | SH1004

## 管用平行ねじ切り丸ダイス

Round Dies • Adjustable type for parallel pipe threads

## SPD(SKS)

管用平行ねじ(NPS)

NPS: ANSI

(単位:mm) (Unit:mm)

ツール No. EDP No.	外径 D	ねじ	在庫 Stock	標準価格 (Yen)
47811	38	1/8 - 27 NPS	D	13,500
47812		1/4 - 18 NPS		13,500
47813		3/8 - 18 NPS		13,500
47821	50	1/2 - 14 NPS	D	22,500
47822		3/4 - 14 NPS		22,500
47831	57	1-11-1/2 NPS	D	44,000
47841	63	1-1/4-11-1/2 NPS		59,900
47851	75	1-1/2-11-1/2 NPS		85,300
47861	100	2-11-1/2 NPS		147,000

## G-LIST No. | SH1002

## 管用テーパねじ切り丸ダイス

Round Dies • Solide type for taper pipe threads

## TPD(SKS)

管用テーパねじ(NPT)

ソリッドタイプ

NPT: ANSI

Solid Type

(単位:mm) (Unit:mm)

ツール No. EDP No.	外径 D	ねじ	在庫 Stock	標準価格 (Yen)
47871	38	1/16- 27 NPT	D	20,200
47872		1/8 - 27 NPT		16,100
47873		1/4 - 18 NPT		16,100
47874	50	3/8 - 18 NPT	D	16,100
47881		1/2 - 14 NPT		25,500
47882	57	3/4 - 14 NPT	D	25,500
47885		1 - 11-1/2 NPT		56,000
47891		3/4 - 14 NPT		63,600
47892	63	1-1/4-11-1/2NPT	D	63,600
47895		1-1/2-11-1/2NPT		104,000
47898	100	2 - 11-1/2 NPT		181,000

A、B、C、D=標準在庫品 A、B、C、D=Standard stock item. □=特定代理店在庫品 □=Stocked by specific distributors. Contact us for price &amp; availability.