


⊕ ナベ PK=1 (JIS小形W組込)



小ねじ
マフロねじ
組込みねじ
タツピンねじ
タツタイト
ハイエタねじ
いたすら防止ねじ
建材用スクリュー
ボルト
キャップボルト
ドリルねじ
座金
つまみねじ
ナット
樹脂製品
アンカーボルト

10000007 鉄	10010007 黄銅	10020007 ステンレス
---------------	----------------	-------------------



ねじの呼び	小ねじ本体					平座金 D1×T	a
	dk	k	十字穴				
			十字穴 番号	m (参考)			
M2	3.5 0 -0.4	1.3±0.1	1	2.2	4.3×0.4	1.2	
M2.3	4 0 -0.4	1.5±0.1	1	2.4	4.6×0.4	1.2	
M2.6	4.5 0 -0.4	1.7±0.1	1	2.6	5×0.5	1.4	
M3	5.5 0 -0.5	2±0.15	2	3.6	6×0.5	1.5	
M3.5	6 0 -0.5	2.3±0.15	2	3.9	7×0.5	1.7	
M4	7 0 -0.5	2.6±0.15	2	4.2	8×0.5	2.0	
M5	9 0 -0.6	3.3±0.15	2	4.9	10×0.8	2.5	
M6	10.5 0 -0.7	3.9±0.2	3	6.3	11.5×0.8	2.9	
M8	14 0 -0.8	5.2±0.2	3	7.8	16×1.2	3.8	

長さ	入り数	鉄										ステンレス
		生地	クロメート	ニッケル	クロム	亜鉛黒	黒メタル	ハンコメタル	ハンコメタル	ハンコメタル	ハンコメタル	
4	7000×20	●	●	●	●	●	●	●	●	●	●	●
5	5000×20	●	●	●	●	●	●	●	●	●	●	●
6	5000×20	●	●	●	●	●	●	●	●	●	●	●
8	4000×20	●	●	●	●	●	●	●	●	●	●	●
10	3000×20	●	●	●	●	●	●	●	●	●	●	●
12	2500×20	●	●	●	●	●	●	●	●	●	●	●
14	2500×20	●	●	●	●	●	●	●	●	●	●	●
15	2000×20	●	●	●	●	●	●	●	●	●	●	●
18	1800×20	●	●	●	●	●	●	●	●	●	●	●
20	1800×20	●	●	●	●	●	●	●	●	●	●	●

長さ	入り数	鉄									
		生地	クロメート	ニッケル	クロム	亜鉛黒	黒メタル	ハンコメタル	ハンコメタル	ハンコメタル	ハンコメタル
12	2000×20	●	●	●	●	●	●	●	●	●	●
14	1500×20	●	●	●	●	●	●	●	●	●	●
16	1500×20	●	●	●	●	●	●	●	●	●	●
18	1200×20	●	●	●	●	●	●	●	●	●	●

長さ	入り数	鉄										ステンレス
		生地	クロメート	ニッケル	クロム	亜鉛黒	黒メタル	ハンコメタル	ハンコメタル	ハンコメタル	ハンコメタル	
4	3500×20	●	●	●	●	●	●	●	●	●	●	●
4	4000×20	●	●	●	●	●	●	●	●	●	●	●
5	3000×20	●	●	●	●	●	●	●	●	●	●	●
5	4000×20	●	●	●	●	●	●	●	●	●	●	●
6	3000×20	●	●	●	●	●	●	●	●	●	●	●
6	3500×20	●	●	●	●	●	●	●	●	●	●	●
8	2500×20	●	●	●	●	●	●	●	●	●	●	●
8	3000×20	●	●	●	●	●	●	●	●	●	●	●
10	2000×20	●	●	●	●	●	●	●	●	●	●	●
10	2500×20	●	●	●	●	●	●	●	●	●	●	●
12	1500×20	●	●	●	●	●	●	●	●	●	●	●
12	2000×20	●	●	●	●	●	●	●	●	●	●	●
14	1500×20	●	●	●	●	●	●	●	●	●	●	●
16	1500×20	●	●	●	●	●	●	●	●	●	●	●
18	1200×20	●	●	●	●	●	●	●	●	●	●	●
35	500×14	●	●	●	●	●	●	●	●	●	●	●

長さ	入り数	鉄										黄銅		ステンレス		
		生地	クロメート	ニッケル	クロム	亜鉛黒	黒メタル	ハンコメタル	ハンコメタル	ハンコメタル	ハンコメタル	生地	クロム	生地	クロム	
4	2500×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
4	4000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
5	2000×24	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
5	2500×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
5	4000×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
6	2000×24	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
6	2500×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
6	3500×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
8	2000×18	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
8	2000×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
8	2500×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
10	1800×20	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
10	2000×18	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
10	2500×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
12	1000×24	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
12	2000×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
12	2500×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
14	1000×24	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
14	2000×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
15	1000×18	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
15	1800×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
16	1000×18	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
16	1500×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●
16	1800×14	●	●	●	●	●	●	●	●	●	●	●	●	●	●	●