


C□LQB用取付ボルト

取付方法／通し穴のC□LQB用取付ボルトを用意しました。
手配方法は下記をご参照ください。
数量はご使用ボルト本数にて手配ください。

例) CQ-M5X55L 2本



注)φ50～φ100のシリンダをロッド側より取付ける際は、座面が少ないためシリンダに添付の平座金を必ずご使用ください。

CLQB／オートスイッチなし

シリンダ型式	C	D	取付ボルト品番
CLQB20-5D		55	CQ-M5X55L
-10D		60	X60L
-15D		65	X65L
-20D		70	X70L
-25D	10.5	75	X75L
-30D		80	X80L
-35D		85	X85L
-40D		90	X90L
-45D		95	X95L
-50D		100	X100L
CLQB25-5D		60	CQ-M5X60L
-10D		65	X65L
-15D		70	X70L
-20D	8.5	75	X75L
-25D		80	X80L
-30D		85	X85L
-35D		90	X90L
-40D		95	X95L
-45D		100	X100L
-50D		105	X105L

シリンダ型式	C	D	取付ボルト品番
CLQB32-10D		65	CQ-M5X65L
-15D		70	X70L
-20D		75	X75L
-25D		80	X80L
-30D	7	85	X85L
-35D		90	X90L
-40D		95	X95L
-45D		100	X100L
-50D		105	X105L
-75D		140	X140L
-100D		165	X165L
CLQB40-10D		75	CQ-M5X75L
-15D		80	X80L
-20D	8.5	85	X85L
-25D		90	X90L
-30D		95	X95L
-35D		100	X100L
-40D		105	X105L
-45D		110	X110L
-50D		115	X115L
-75D		150	X150L
-100D		175	X175L

シリンダ型式	C	D	取付ボルト品番
CLQB50-10D		80	CQ-M6X80L
-15D		85	X85L
-20D		90	X90L
-25D	12.5	95	X95L
-30D		100	X100L
-35D		105	X105L
-40D		110	X110L
-45D		115	X115L
-50D		120	X120L
-75D		155	X155L
-100D		180	X180L
CLQB63-10D		90	CQ-M8X90L
-15D	16.5	95	X95L
-20D		100	X100L
-25D		105	X105L
-30D		110	X110L
-35D		115	X115L
-40D		120	X120L
-45D		125	X125L
-50D		130	X130L
-75D		165	X165L
-100D		190	X190L

シリンダ型式	C	D	取付ボルト品番
CLQB80-10D		100	CQ-M10X100L
-15D	17	105	X105L
-20D		110	X110L
-25D		115	X115L
-30D		120	X120L
-35D		125	X125L
-40D		130	X130L
-45D		135	X135L
-50D		140	X140L
-75D		175	X175L
-100D		200	X200L
CLQB100-10D		115	CQ-M10X115L
-15D	15.5	120	X120L
-20D		125	X125L
-25D		130	X130L
-30D		135	X135L
-35D		140	X140L
-40D		145	X145L
-45D		150	X150L
-50D		155	X155L
-75D		190	X190L
-100D		215	X215L

CDLQB／オートスイッチ付

シリンダ型式	C	D	取付ボルト品番
CDLQB20-5D		65	CQ-M5X65L
-10D		70	X70L
-15D		75	X75L
-20D	10.5	80	X80L
-25D		85	X85L
-30D		90	X90L
-35D		95	X95L
-40D		100	X100L
-45D		105	X105L
-50D		110	X110L
CDLQB25-5D		70	CQ-M5X70L
-10D	8.5	75	X75L
-15D		80	X80L
-20D		85	X85L
-25D		90	X90L
-30D		95	X95L
-35D		100	X100L
-40D		105	X105L
-45D		110	X110L
-50D		115	X115L

シリンダ型式	C	D	取付ボルト品番
CDLQB32-10D		75	CQ-M5X75L
-15D	7	80	X80L
-20D		85	X85L
-25D		90	X90L
-30D		95	X95L
-35D		100	X100L
-40D		105	X105L
-45D		110	X110L
-50D		115	X115L
-75D		140	X140L
-100D		165	X165L
CDLQB40-10D		85	CQ-M5X85L
-15D	8.5	90	X90L
-20D		95	X95L
-25D		100	X100L
-30D		105	X105L
-35D		110	X110L
-40D		115	X115L
-45D		120	X120L
-50D		125	X125L
-75D		150	X150L
-100D		175	X175L

シリンダ型式	C	D	取付ボルト品番
CDLQB50-10D		90	CQ-M6X90L
-15D	12.5	95	X95L
-20D		100	X100L
-25D		105	X105L
-30D		110	X110L
-35D		115	X115L
-40D		120	X120L
-45D		125	X125L
-50D		130	X130L
-75D		155	X155L
-100D		180	X180L
CDLQB63-10D		100	CQ-M8X100L
-15D	16.5	105	X105L
-20D		110	X110L
-25D		115	X115L
-30D		120	X120L
-35D		125	X125L
-40D		130	X130L
-45D		135	X135L
-50D		140	X140L
-75D		165	X165L
-100D		190	X190L

シリンダ型式	C	D	取付ボルト品番
CDLQB80-10D		110	CQ-M10X110L
-15D	17	115	X115L
-20D		120	X120L
-25D		125	X125L
-30D		130	X130L
-35D		135	X135L
-40D		140	X140L
-45D		145	X145L
-50D		150	X150L
-75D		175	X175L
-100D		200	X200L
CDLQB100-10D		125	CQ-M10X125L
-15D	15.5	130	X130L
-20D		135	X135L
-25D		140	X140L
-30D		145	X145L
-35D		150	X150L
-40D		155	X155L
-45D		160	X160L
-50D		165	X165L
-75D		190	X190L
-100D		215	X215L

CNG

MWB

CNA2

CNS

CLS

CLQ

RLQ

MLU

MLGP

ML1C

CLJ2

CLM2

CLG1

MLGC

CL1

D-□

-X□