

PB 210

Hex key L-wrenches for hexagon socket screws, chrome-plated for keys 1.27 mm and larger

Chiavi maschio esagonale piegate, da grandezza 1.27 mm cromate



PB 210.0,71	0,71	1.4	-	7	35	0.2	50	7 610733 015795
PB 210.0,89	0,89	2	-	10	40	0.3	50	7 610733 015801
PB 210.1,27	1,27	2.5	1.4	12	45	0.5	50	7 610733 012473
PB 210.1,5	1,5	3	1.6-2	14	50	1	10	7 610733 002795
PB 210.2	2	4	2.5	16	56	2	10	7 610733 002801
PB 210.2,5	2,5	5	3	18	63	3	10	7 610733 002818
PB 210.3	3	6	4	20	71	5	10	7 610733 002825
PB 210.3,5	3,5	-	-	21	75	8	10	7 610733 002832
PB 210.4	4	8	5	22	80	11	10	7 610733 002849
PB 210.4,5	4,5	-	-	23	85	15	10	7 610733 002856
PB 210.5	5	10	6	25	90	19	10	7 610733 002863
PB 210.5,5	5,5	-	-	26	95	24	10	7 610733 002870
PB 210.6	6	12-14	8	28	100	31	10	7 610733 002887
PB 210.7	7	-	-	30	105	44	10	7 610733 002894
PB 210.8	8	16	10	32	112	62	10	7 610733 002900
PB 210.9	9	-	-	34	115	81	10	7 610733 002917
PB 210.10	10	18-20	12	36	125	109	10	7 610733 002924
PB 210.12	12	22-24	14	40	140	175	10	7 610733 002931
PB 210.14	14	-	16-18	45	160	272	10	7 610733 002948
PB 210.17	17	-	20-22	50	180	454	10	7 610733 002955
PB 210.19	19	-	24-27	56	200	642	10	7 610733 002962
PB 210.22	22	-	30	63	224	958	10	7 610733 002979

PB 212

Ball point hex key L-wrenches for hexagon socket screws

Chiavi maschio esagonale piegate con punta sferica



PB 212.1,27	1,27	2.5	1.4	12	45	0.5	10	7 610733 004188
PB 212.1,5	1,5	3	1.6-2	14	50	1	10	7 610733 015672
PB 212.2	2	4	2.5	16	56	2	10	7 610733 015689
PB 212.2,5	2,5	5	3	18	63	3	10	7 610733 015696
PB 212.3	3	6	4	20	71	6	10	7 610733 012497
PB 212.4	4	8	5	22	80	10	10	7 610733 012503
PB 212.5	5	10	6	25	90	19	10	7 610733 012510
PB 212.6	6	12-14	8	28	100	30	10	7 610733 012527
PB 212.7	7	-	-	30	105	43	10	7 610733 045273
PB 212.8	8	16	10	32	112	60	10	7 610733 012534
PB 212.10	10	18-20	12	36	125	105	10	7 610733 012541
PB 212.12	12	22-24	14	40	140	175	10	7 610733 038947