


N03

外牙接頭 Male Connector



產品編號	管牙 T	適用管徑 D1	直牙	D2	L	HEX1	HEX2	I.D
PART NO.	PipeThread T	TubeSize D1	Thread					
N03-C05004	1/4-28UNF	4	M7×1.0	3.8	22.5	9	8	1.8
N03-C05006	1/4-28UNF	6	M10-24	5.6	25.5	12	10	3
N03-C1004	1/8	4	M7×1.0	3.8	24.5	9	10	1.8
N03-C1006	1/8	6	M10-24	5.6	27	12	10	3
N03-C1025	1/8	8	7/16-24	6.9	28	14	12	4.5
N03-C1010	1/8	10	1/2-24	8.3	29	15	12.7	5.2
N03-C2004	1/4	4	M7×1.0	3.8	28	9	14	1.8
N03-C2006	1/4	6	M10-24	5.6	30.5	12	14	3
N03-C2025	1/4	8	7/16-24	6.9	31.5	14	14	4.5
N03-C2010	1/4	10	1/2-24	8.3	32.5	15	14	5.2
N03-C2012	1/4	12	M17-24	10.3	34	19	17	7
N03-C3006	3/8	6	M10-24	5.6	30.5	12	17	3
N03-C3025	3/8	8	7/16-24	6.9	31.5	14	17	4.5
N03-C3010	3/8	10	1/2-24	8.3	32.5	15	17	5.2
N03-C3012	3/8	12	M17-24	10.3	34	19	17	7
N03-C4006	1/2	6	M10-24	5.6	34	12	21	3
N03-C4025	1/2	8	7/16-24	6.9	35	14	21	4.5
N03-C4010	1/2	10	1/2-24	8.3	36	15	21	5.2
N03-C4012	1/2	12	M17-24	10.3	37.5	19	21	7

產品編號	管牙 T	適用管徑 D1	直牙	D2	L	HEX1	HEX2	I.D
PART NO.	PipeThread T	TubeSize D1	Thread					
N03-C0502	1/4-28UNF	1/4	M10-24	5.6	25.5	12	10	3
N03-C102	1/8	1/4	M10-24	5.6	27	12	10	3
N03-C1025	1/8	5/16	7/16-24	6.9	28	14	12	4.5
N03-C103	1/8	3/8	1/2-24	8.3	29	15	12.7	5.2
N03-C202	1/4	1/4	M10-24	5.6	30.5	12	14	3
N03-C2025	1/4	5/16	7/16-24	6.9	31.5	14	14	4.5
N03-C203	1/4	3/8	1/2-24	8.3	32.5	15	14	5.2
N03-C204	1/4	1/2	M17-24	11	34	19	17	8
N03-C302	3/8	1/4	M10-24	5.6	30.5	12	17	3
N03-C3025	3/8	5/16	7/16-24	6.9	31.5	14	17	4.5
N03-C303	3/8	3/8	1/2-24	8.3	32.5	15	17	5.2
N03-C304	3/8	1/2	M17-24	11	34	19	17	8
N03-C402	1/2	1/4	M10-24	5.6	34	12	21	3
N03-C4025	1/2	5/16	7/16-24	6.9	35	14	21	4.5
N03-C403	1/2	3/8	1/2-24	8.3	36	15	21	5.2
N03-C404	1/2	1/2	M17-24	11	37.5	19	21	8

