

インサート ポジティブタイプ


●: 連続加工
●: 軽断続加工
✳: 強断続加工

EP






ひし形穴つき
75° ポジ11°

	P 鋼	M ステンレス	K 鋳鉄	N 非鉄金属	S 難削材	H 高硬度材
●	●●●●	●●●●	●	●	●	●
●	●●●●	●●●●	●	●	●	●
●	●●●●	●●●●	●	●	●	●
●	●●●●	●●●●	●	●	●	●
●	●●●●	●●●●	●	●	●	●
●	●●●●	●●●●	●	●	●	●
●	●●●●	●●●●	●	●	●	●



用途	ブレード記号	形番	コーティング			コートテッド	サーメット	超硬	寸法 (mm)					
			GH110	SH725	SH730	GT9530	NS9530	TH10	UX30	RE	IC	S	D1	
仕上げ切削	W08	EPGT03X100R-W08		●							0.03	3.57	1.39	1.9
		EPGT03X100L-W08		●							0.03	3.57	1.39	1.9
		EPGT03X101R-W08		●							0.1	3.57	1.39	1.9
		EPGT03X101L-W08		●							0.1	3.57	1.39	1.9
		EPGT03X102R-W08		●							0.2	3.57	1.39	1.9
		EPGT03X102L-W08		●							0.2	3.57	1.39	1.9
		EPGT03X104R-W08		●							0.4	3.57	1.39	1.9
		EPGT03X104L-W08		●							0.4	3.57	1.39	1.9
		EPGT040100R-W08		●							0.03	3.97	1.59	2.3
		EPGT040100L-W08	●	●				●			0.03	3.97	1.59	2.3
		EPGT040101R-W08		●							0.1	3.97	1.59	2.3
		EPGT040101L-W08		●							0.1	3.97	1.59	2.3
		EPGT040102R-W08	●	●				●			0.2	3.97	1.59	2.3
		EPGT040102L-W08	●	●		●		●	●		0.2	3.97	1.59	2.3
		EPGT040104R-W08	●	●				●			0.4	3.97	1.59	2.3
EPGT040104L-W08	●	●		●		●	●		0.4	3.97	1.59	2.3		
仕上げ切削 (シャープエッジ)	W08	EPGT03X100FL-W08		●							0.03	3.57	1.39	1.9
		EPGT03X100FR-W08		●							0.03	3.57	1.39	1.9
		EPGT03X101FL-W08		●							0.1	3.57	1.39	1.9
		EPGT03X101FR-W08		●							0.1	3.57	1.39	1.9
		EPGT03X102FL-W08		●							0.2	3.57	1.39	1.9
		EPGT03X102FR-W08		●							0.2	3.57	1.39	1.9
		EPGT03X104FL-W08		●							0.4	3.57	1.39	1.9
		EPGT03X104FR-W08		●							0.4	3.57	1.39	1.9
		EPGT040100FL-W08		●							0.03	3.97	1.59	2.3
		EPGT040100FR-W08		●							0.03	3.97	1.59	2.3
		EPGT040101FL-W08		●							0.1	3.97	1.59	2.3
		EPGT040101FR-W08		●							0.1	3.97	1.59	2.3
		EPGT040102FL-W08		●							0.2	3.97	1.59	2.3
		EPGT040102FR-W08		●							0.2	3.97	1.59	2.3
		EPGT040104FL-W08		●							0.4	3.97	1.59	2.3
EPGT040104FR-W08		●							0.4	3.97	1.59	2.3		

●: 設定アイテム



参照ページ: 内径ホルダ → D031 - ボーリングバイト → K211 - トップボラバイト → K213

材質
インサート
外径用ホルダ
内径用ホルダ
ねじ切り工具
突切り溝入れ
小型旋盤用工具
フライス工具
エンドミル
穴あけ工具
ソーリングシステム
ユーザガイド
索引