


■ アダプタ

QSDR/L-CHP

高圧クーラント対応端面溝入れ用アダプタ



形番	CW	DAXMIN	DAXN	DAXX	シートサイズ	CDX	LF	WF ⁽¹⁾
QSDR/L-3T26-055-CHP	3	49	55	60	3	26	71.6	7.5
QSDR/L-3T26-060-CHP	3	54	60	70	3	26	71.6	7.5
QSDR/L-3T32-070-CHP	3	64	70	85	3	32	77.6	7.5
QSDR/L-3T32-085-CHP	3	79	85	110	3	32	77.6	7.5
QSDR/L-3T32-110-CHP	3	104	110	140	3	32	77.6	7.5
QSDR/L-3T32-140-CHP	3	134	140	180	3	32	77.6	7.5
QSDR/L-3T32-180-CHP	3	174	180	250	3	32	77.6	7.5
QSDR/L-3T32-250-CHP	3	244	250	400	3	32	77.6	7.5
QSDR/L-3T32-400-CHP	3	394	400	800	3	32	77.6	7.5
QSDR/L-3T32-800-CHP	3	794	800	∞	3	32	77.6	7.5
QSDR/L-4T35-060-CHP	4	52	60	70	4	35	80.6	8
QSDR/L-4T35-070-CHP	4	62	70	85	4	35	80.6	8
QSDR/L-4T35-085-CHP	4	77	85	100	4	35	80.6	8
QSDR/L-4T40-100-CHP	4	92	100	130	4	40	85.6	8
QSDR/L-4T40-130-CHP	4	122	130	180	4	40	85.6	8
QSDR/L-4T40-180-CHP	4	172	180	300	4	40	85.6	8
QSDR/L-4T40-300-CHP	4	292	300	600	4	40	85.6	8
QSDR/L-4T40-600-CHP	4	592	600	∞	4	40	85.6	8
QSDR/L-5T42-060-CHP	5	50	60	80	5	42	87.6	8.5
QSDR/L-5T42-080-CHP	5	70	80	110	5	42	87.6	8.5
QSDR/L-5T42-110-CHP	5	100	110	150	5	42	87.6	8.5
QSDR/L-5T42-150-CHP	5	140	150	200	5	42	87.6	8.5
QSDR/L-5T42-200-CHP	5	190	200	300	5	42	87.6	8.5
QSDR/L-5T42-300-CHP	5	290	300	600	5	42	87.6	8.5
QSDR/L-5T42-600-CHP	5	590	600	∞	5	42	87.6	8.5

(1) WFの値は、同表の溝幅(CW)インサートを取り付けた際の寸法です。

部品

形番	スパナ
QSDR/L...	QL-39

インサート	溝幅 CW	端面溝入れ 最小加工径 DAXN
QGM / QGS	3	80
QGM / QGS	4	60
QGM / QGS	5	60
QTX	3	55
QTX	4	60
QTX	5	60

