


DNGA1504

ひし形穴つき
55°



IC : 12.7 mm
D1 : 5.16 mm
S : 4.76 mm

[illegible]

用途	形 番	寸法 (mm)		コーナ 数	ワイパー	BXA10	BXA20	BR35F	BXM10	BXM20														
		RE	LE																					
精密仕上げ切削	2QP-DNGA150402-LF	0.2	2.7	2		●	●																	
	4QS-DNGA150402-LF		2.2	4		●	●																	
	2QP-DNGA150402-L		2.7	2		●	●																	
	2QP-DNGA150404-LF	0.4	2.5	2		●	●																	
	4QS-DNGA150404-LF		2	4		●	●																	
	2QP-DNGA150404-L		2.5	2		●	●		●	●														
	2QP-DNGA150404WJ	2.5	2	○		●		●	●															
	2QP-DNGA150408-LF	0.8	2.1	2		●	●																	
	4QS-DNGA150408-LF		1.6	4		●	●																	
	2QP-DNGA150408-L		2.1	2		●	●		●	●														
	2QP-DNGA150408WJ		2.1	2	○		●		●	●														
	2QP-DNGA150412-LF	1.2	2	2		●	●																	
	4QS-DNGA150412-LF		1.6	4		●	●																	
	2QP-DNGA150412-L		2	2		●	●			●														
	仕上げ切削	2QP-DNGA150402	0.2	2.7	2		●	●																
		4QS-DNGA150402		2.2	4		●	●																
2QP-DNGA150402-LC		2.7		2		●	●																	
4QS-DNGA150402-LC		2.2		4		●	●																	
2QP-DNGA150404		0.4	2.5	2		●	●		●	●														
2QP-DNGA150404SR			2.5	2				●																
4QS-DNGA150404			2	4		●	●																	
4QS-DNGA150404SR			2	4				●																
2QP-DNGA150404-LC			2.5	2		●	●																	
4QS-DNGA150404-LC		2	4		●	●																		
2QP-DNGA150408		0.8	2.1	2		●	●		●	●														
2QP-DNGA150408SR			2.1	2				●																
4QS-DNGA150408			1.6	4		●	●																	
4QS-DNGA150408SR			1.6	4				●																
2QP-DNGA150408-LC			2.1	2		●	●																	
4QS-DNGA150408-LC		1.6	4		●	●																		
2QP-DNGA150412		1.2	2	2		●	●		●	●														
2QP-DNGA150412SR			2	2				●																
4QS-DNGA150412			1.6	4		●	●																	
4QS-DNGA150412SR			1.6	4				●																
2QP-DNGA150412-LC			2	2		●	●																	
4QS-DNGA150412-LC			1.6	4		●	●																	
2QP-DNGA150416		1.6	3.4	2		●	●																	
2QP-DNGA150416SR			3.4	2				●																
2QP-DNGA150420		2	3	2		●	●																	
2QP-DNGA150420SR			3	2				●																
2QP-DNGA150424		2.4	2.6	2		●	●																	
2QP-DNGA150424SR			2.6	2				●																

●:新製品
●:設定アイテム