


K2-0.72II Series for 1.27mm [50mil] Pitch


K2-0.72II Series Plunger Tip Styles

Pin Length: 22.8mm [0.898inch.]


Unit: mm [inch]




K2-0.72II A-4.5M-4
Plunger Material: SK (Steel)




K2-0.72II AH-4.5M-4
Plunger Material: SK (Steel)




K2-0.72II C-4.5M1.0-1
Plunger Material: SK (Steel)




K2-0.72II CH-4.5M1.0-4
Plunger Material: SK (Steel)




K2-0.72II CR-4.5M1.0-3
Plunger Material: SK (Steel)




K2-0.72II F-4.5M-5
Plunger Material: SK (Steel)




K2-0.72II G-4.5M1.0-2
Plunger Material: SK (Steel)



K2-0.72II H-4.5M-4
Plunger Material: SK (Steel)




K2-0.72II LC-4.5M1.0-1
Plunger Material: BeCu



K2-0.72II U-4.5M1.0-4
Plunger Material: SK (Steel)

スプリングピン仕様 Spring Pin Specifications

推奨ストローク Operating Travel	2.0mm [0.079 inch]
荷重 Spring Force at Operating Travel	80gf [2.82oz.]
初期荷重 Initial Force	33gf [1.16oz.]
最大ストローク Max Travel	3.0mm [0.118 inch]
スプリング耐久回数 Life Span at Operating Travel	100万回 (1,000K Cycles)
抵抗値 Resistance (Typ.)	50mΩ
最大許容電流値 Current Rating (Typ.)	4.4A
使用温度 Operating Temp.	-45°C~125°C
Material/Finish	
Plunger	SK (Steel) or BeCu / Au
Barrel	Phosphor Bronze / Au
Spring	Music Wire / Au



リセプタクル 品名 Receptacle

K2-0.72S-1
(末端加工無し / No Termination)

K2-0.72S-1-U
(ソルダーカップ付 / with Solder Cup)

K2-0.72S-3
(末端加工無し / No Termination)

K2-0.72S-3-1-U
(ソルダーカップ付 / with Solder Cup)

リセプタクル仕様 Receptacle Specifications

Material/Finish	Brass / Au
-----------------	------------

*All specifications are subject to change without notice.