


レジューサ (同心、偏心)



レジューサ (同心)

径の呼び (B)	外径 OD	Sch10S		Sch20S		FSGP		Sch40		Sch80		Sch160	
大径×小径		内径 ID	厚さ T	内径 ID	厚さ T	内径 ID	厚さ T	内径 ID	厚さ T	内径 ID	厚さ T	内径 ID	厚さ T
1/2	21.7	17.5	2.1	16.7	2.5	16.1	2.8	16.1	2.8	14.3	3.7	12.1	4.8
3/4 × 1/2	27.2	23.0	2.1	22.2	2.5	21.6	2.8	21.4	2.9	19.4	3.9	16.0	5.6
1 × 3/4, 1/2	34.0	28.4	2.8	28.0	3.0	27.6	3.2	27.2	3.4	25.0	4.5	21.2	6.4
1 1/4 × 1, 3/4, 1/2	42.7	37.1	2.8	36.7	3.0	35.7	3.5	35.5	3.6	32.9	4.9	29.9	6.4
1 1/2 × 1 1/4, 1, 3/4, 1/2	48.6	43.0	2.8	42.7	3.0	41.6	3.5	41.2	3.7	38.4	5.1	34.4	7.1
2 × 1 1/2, 1 1/4, 1, 3/4	60.5	54.9	2.8	53.5	3.5	52.9	3.8	52.7	3.9	49.5	5.5	43.1	8.7
2 1/2 × 2, 1 1/2, 1 1/4, 1	76.3	70.3	3.0	69.3	3.5	67.9	4.2	65.9	5.2	62.3	7.0	57.3	9.5
3 × 2 1/2, 2, 1 1/2, 1 1/4	89.1	83.1	3.0	81.1	4.0	80.7	4.2	78.1	5.5	73.9	7.6	66.9	11.1
3 1/2 × 3, 2 1/2, 2, 1 1/2, 1 1/4	101.6	95.6	3.0	93.6	4.0	93.2	4.2	90.2	5.7	85.4	8.1	76.2	12.7
4 × 3 1/2, 3, 2 1/2, 2, 1 1/2	114.3	108.3	3.0	106.3	4.0	105.3	4.5	102.3	6.0	97.1	8.6	87.3	13.5
5 × 4, 3 1/2, 3, 2 1/2, 2	139.8	133.0	3.4	129.8	5.0	130.8	4.5	126.6	6.6	120.8	9.5	108.0	15.9
6 × 5, 4, 3 1/2, 3, 2 1/2	165.2	158.4	3.4	155.2	5.0	155.2	5.0	151.0	7.1	143.2	11.0	128.8	18.2
8 × 6, 5, 4, 3 1/2	216.3	208.3	4.0	203.3	6.5	204.7	5.8	199.9	8.2	190.9	12.7	170.3	23.0
10 × 8, 6, 5, 4	267.4	259.4	4.0	254.4	6.5	254.2	6.6	248.8	9.3	237.2	15.1	210.2	28.6
12 × 10, 8, 6, 5	318.5	309.5	4.5	305.5	6.5	304.7	6.9	297.9	10.3	283.7	17.4	251.9	33.3
14 × 12, 10, 8, 6	355.6	345.6	5.0	339.6	8.0	339.8	7.9	333.4	11.1	317.6	19.0	284.2	35.7
16 × 14, 12, 10, 8	406.4	396.4	5.0	390.4	8.0	390.6	7.9	381.0	12.7	363.6	21.4	325.4	40.5
18 × 16, 14, 12, 10	457.2	447.2	5.0	441.2	8.0	441.4	7.9	428.6	14.3	409.6	23.8	366.8	45.2
20 × 18, 16, 14, 12	508.0	497.0	5.5	489.0	9.5	492.2	7.9	477.8	15.1	455.6	26.2	408.0	50.0
22 × 20, 18, 16, 14	558.8	547.8	5.5	539.8	9.5	—	—	527.0	15.9	501.6	28.6	450.8	54.0
24 × 22, 20, 18, 16	609.6	596.6	6.5	590.6	9.5	—	—	574.6	17.5	547.6	31.0	490.6	59.5