

製品概要

Line up

ストライクドリル EZN3D形(3Dタイプ) EZN3D type



- 高精度ソリッドドリル High accuracy solid drill
- 有効加工穴深さ3×Dc Drilling depth 3×Dc
- ねじれ角30° Helix angle :30°
- クーラント穴つき Through coolant hole



形番 Cat. No.	在庫 Stock	寸法(mm) Dimensions					標準価格 (円) List Price (JPY)
		φDc	ℓ	L	Lo	φDs	
EZN3DCH0300S03	●	3.0	15	68	68.5	3	8,100
EZN3DCH0310S04	●	3.1	18	71	71.6	4	8,620
EZN3DCH0320S04	●	3.2	18	71	71.6	4	8,620
EZN3DCH0330S04	●	3.3	18	71	71.6	4	8,620
EZN3DCH0340S04	●	3.4	18	71	71.6	4	8,620
EZN3DCH0350S04	●	3.5	18	71	71.6	4	8,620
EZN3DCH0360S04	●	3.6	20	73	73.7	4	9,010
EZN3DCH0370S04	●	3.7	20	73	73.7	4	9,010
EZN3DCH0380S04	●	3.8	20	73	73.7	4	9,010
EZN3DCH0390S04	●	3.9	20	73	73.7	4	9,010
EZN3DCH0400S04	●	4.0	20	73	73.7	4	9,010
EZN3DCH0410S05	●	4.1	23	78	78.7	5	9,710
EZN3DCH0420S05	●	4.2	23	78	78.8	5	9,710
EZN3DCH0430S05	●	4.3	23	78	78.8	5	9,710
EZN3DCH0440S05	●	4.4	23	78	78.8	5	9,710
EZN3DCH0450S05	●	4.5	23	78	78.8	5	9,710
EZN3DCH0460S05	●	4.6	25	80	80.8	5	10,500
EZN3DCH0470S05	●	4.7	25	80	80.9	5	10,500
EZN3DCH0480S05	●	4.8	25	80	80.9	5	10,500
EZN3DCH0490S05	●	4.9	25	80	80.9	5	10,500
EZN3DCH0500S05	●	5.0	25	80	80.9	5	10,500
EZN3DCH0510S06	●	5.1	28	82	82.9	6	11,220
EZN3DCH0520S06	●	5.2	28	82	82.9	6	11,220
EZN3DCH0530S06	●	5.3	28	82	83.0	6	11,220
EZN3DCH0540S06	●	5.4	28	82	83.0	6	11,220
EZN3DCH0550S06	●	5.5	28	82	83.0	6	11,220
EZN3DCH0560S06	●	5.6	30	82	83.0	6	11,770
EZN3DCH0570S06	●	5.7	30	82	83.0	6	11,770
EZN3DCH0580S06	●	5.8	30	82	83.1	6	11,770
EZN3DCH0590S06	●	5.9	30	82	83.1	6	11,770
EZN3DCH0600S06	●	6.0	30	82	83.1	6	11,770
EZN3DCH0610S07	●	6.1	33	86	87.1	7	11,880
EZN3DCH0620S07	●	6.2	33	86	87.1	7	11,880

形番 Cat. No.	在庫 Stock	寸法(mm) Dimensions					標準価格 (円) List Price (JPY)
		φDc	ℓ	L	Lo	φDs	
EZN3DCH0630S07	●	6.3	33	86	87.1	7	11,880
EZN3DCH0640S07	●	6.4	33	86	87.2	7	11,880
EZN3DCH0650S07	●	6.5	33	86	87.2	7	11,880
EZN3DCH0660S07	●	6.6	35	88	89.2	7	12,650
EZN3DCH0670S07	●	6.7	35	88	89.2	7	12,650
EZN3DCH0680S07	●	6.8	35	88	89.2	7	12,650
EZN3DCH0690S07	●	6.9	35	88	89.3	7	12,650
EZN3DCH0700S07	●	7.0	35	88	89.3	7	12,650
EZN3DCH0710S08	●	7.1	38	92	93.3	8	13,530
EZN3DCH0720S08	●	7.2	38	92	93.3	8	13,530
EZN3DCH0730S08	●	7.3	38	92	93.3	8	13,530
EZN3DCH0740S08	●	7.4	38	92	93.3	8	13,530
EZN3DCH0750S08	●	7.5	38	92	93.4	8	13,530
EZN3DCH0760S08	●	7.6	40	94	95.4	8	14,300
EZN3DCH0770S08	●	7.7	40	94	95.4	8	14,300
EZN3DCH0780S08	●	7.8	40	94	95.4	8	14,300
EZN3DCH0790S08	●	7.9	40	94	95.4	8	14,300
EZN3DCH0800S08	●	8.0	40	94	95.5	8	14,300
EZN3DCH0810S09	●	8.1	43	100	101.5	9	15,620
EZN3DCH0820S09	●	8.2	43	100	101.5	9	15,620
EZN3DCH0830S09	●	8.3	43	100	101.5	9	15,620
EZN3DCH0840S09	●	8.4	43	100	101.5	9	15,620
EZN3DCH0850S09	●	8.5	43	100	101.5	9	15,620
EZN3DCH0860S09	●	8.6	45	100	101.6	9	16,280
EZN3DCH0870S09	●	8.7	45	100	101.6	9	16,280
EZN3DCH0880S09	●	8.8	45	100	101.6	9	16,280
EZN3DCH0890S09	●	8.9	45	100	101.6	9	16,280
EZN3DCH0900S09	●	9.0	45	100	101.6	9	16,280
EZN3DCH0910S10	●	9.1	48	106	107.7	10	17,160
EZN3DCH0920S10	●	9.2	48	106	107.7	10	17,160
EZN3DCH0930S10	●	9.3	48	106	107.7	10	17,160
EZN3DCH0940S10	●	9.4	48	106	107.7	10	17,160
EZN3DCH0950S10	●	9.5	48	106	107.7	10	17,160

●：メーカー在庫品 Standard stock items
標準価格は2022年12月時点の価格となります。
標準切削条件は19~20ページをご参照ください