

## CSR-MC 超硬ミクロンリーマ

Φ6.051～Φ12.1までは受注生産品となります。

直径 (ΦD)	食付長 (T)	刃長 (ℓ)	全長 (L)	シャンク径 (Φd)	刃数 (N)	センタ
<i>Dia.</i>	<i>Chamfer Length</i>	<i>Length of Flutes</i>	<i>Overall Length</i>	<i>Shank Dia.</i>	<i>Number of Flutes</i>	<i>Center</i>
6.051 ~ 6.099	0.8	35	80	7	6	60° 凹
6.1 ~ 6.199	0.8	35	80	7	6	60° 凹
6.2 ~ 6.299	0.8	35	80	7	6	60° 凹
6.3 ~ 6.399	0.8	35	80	7	6	60° 凹
6.4 ~ 6.499	0.8	35	80	7	6	60° 凹
6.5 ~ 6.599	0.8	35	80	7	6	60° 凹
6.6 ~ 6.699	0.8	35	80	7	6	60° 凹
6.7 ~ 6.799	0.8	35	80	7	6	60° 凹
6.8 ~ 6.899	0.8	35	80	7	6	60° 凹
6.9 ~ 6.999	0.8	35	80	7	6	60° 凹
7 ~ 7.009	0.8	35	80	7	6	60° 凹
7.01 ~ 7.099	0.8	35	80	8	6	60° 凹
7.1 ~ 7.199	0.8	35	80	8	6	60° 凹
7.2 ~ 7.299	0.8	35	80	8	6	60° 凹
7.3 ~ 7.399	0.8	35	80	8	6	60° 凹
7.4 ~ 7.499	0.8	35	80	8	6	60° 凹
7.5 ~ 7.599	0.8	35	80	8	6	60° 凹
7.6 ~ 7.699	0.8	35	80	8	6	60° 凹
7.7 ~ 7.799	0.8	35	80	8	6	60° 凹
7.8 ~ 7.899	0.8	35	80	8	6	60° 凹
7.9 ~ 7.999	0.8	35	80	8	6	60° 凹
8 ~ 8.009	0.8	35	80	8	6	60° 凹
8.01 ~ 8.099	1	40	90	9	6	60° 凹
8.1 ~ 8.199	1	40	90	9	6	60° 凹
8.2 ~ 8.299	1	40	90	9	6	60° 凹
8.3 ~ 8.399	1	40	90	9	6	60° 凹
8.4 ~ 8.499	1	40	90	9	6	60° 凹
8.5 ~ 8.599	1	40	90	9	6	60° 凹
8.6 ~ 8.699	1	40	90	9	6	60° 凹
8.7 ~ 8.799	1	40	90	9	6	60° 凹
8.8 ~ 8.899	1	40	90	9	6	60° 凹
8.9 ~ 8.999	1	40	90	9	6	60° 凹
9 ~ 9.009	1	40	90	9	6	60° 凹

直径 (ΦD)	食付長 (T)	刃長 (ℓ)	全長 (L)	シャンク径 (Φd)	刃数 (N)	センタ
<i>Dia.</i>	<i>Chamfer Length</i>	<i>Length of Flutes</i>	<i>Overall Length</i>	<i>Shank Dia.</i>	<i>Number of Flutes</i>	<i>Center</i>
9.01 ~ 9.099	1	40	90	10	6	60° 凹
9.1 ~ 9.199	1	40	90	10	6	60° 凹
9.2 ~ 9.299	1	40	90	10	6	60° 凹
9.3 ~ 9.399	1	40	90	10	6	60° 凹
9.4 ~ 9.499	1	40	90	10	6	60° 凹
9.5 ~ 9.599	1	40	90	10	6	60° 凹
9.6 ~ 9.699	1	40	90	10	6	60° 凹
9.7 ~ 9.799	1	40	90	10	6	60° 凹
9.8 ~ 9.899	1	40	90	10	6	60° 凹
9.9 ~ 9.999	1	40	90	10	6	60° 凹
10 ~ 10.009	1	40	90	10	6	60° 凹
10.01 ~ 10.099	1	40	90	11	6	60° 凹
10.1 ~ 10.199	1	40	90	11	6	60° 凹
10.2 ~ 10.299	1	40	90	11	6	60° 凹
10.3 ~ 10.399	1	40	90	11	6	60° 凹
10.4 ~ 10.499	1	40	90	11	6	60° 凹
10.5 ~ 10.599	1	40	90	11	6	60° 凹
10.6 ~ 10.699	1	40	90	11	6	60° 凹
10.7 ~ 10.799	1	40	90	11	6	60° 凹
10.8 ~ 10.899	1	40	90	11	6	60° 凹
10.9 ~ 10.999	1	40	90	11	6	60° 凹
11 ~ 11.009	1	40	90	11	6	60° 凹
11.01 ~ 11.099	1	45	90	12	6	60° 凹
11.1 ~ 11.199	1	45	90	12	6	60° 凹
11.2 ~ 11.299	1	45	90	12	6	60° 凹
11.3 ~ 11.399	1	45	90	12	6	60° 凹
11.4 ~ 11.499	1	45	90	12	6	60° 凹
11.5 ~ 11.599	1	45	90	12	6	60° 凹
11.6 ~ 11.699	1	45	90	12	6	60° 凹
11.7 ~ 11.799	1	45	90	12	6	60° 凹
11.8 ~ 11.899	1	45	90	12	6	60° 凹
11.9 ~ 11.999	1	45	90	12	6	60° 凹
12 ~ 12.009	1	45	90	12	6	60° 凹
12.1	1	45	90	12	6	60° 凹