


LMR

切削条件表

P139

ロングマシンリーマ Long Machine Reamer



公差 (Tolerance)	D					
	5 ~ 6	+0.009 +0.004	6.1~10	+0.012 +0.006	10.1~18	+0.015 +0.007
18.1~30	+0.017 +0.008	30.5~50	+0.02 +0.009	55 ~60	+0.024 +0.011	

右刃ストレート 食付角度45° SKH51
Straight Flute Chamfer Angle45° HSS

直径 (φD)	食付長 (T)	刃長 (ℓ)	全長 (L)	MTNo.	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Overall Length	Shank MTNo.	Number of Flutes	Center
5	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
5.1	1	120	200	1	6	60°凹
5.2	1	120	200	1	6	60°凹
5.3	1	120	200	1	6	60°凹
5.4	1	120	200	1	6	60°凹
5.5	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
6	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
6.1	1	120	200	1	6	60°凹
6.2	1	120	200	1	6	60°凹
6.3	1	120	200	1	6	60°凹
6.4	1	120	200	1	6	60°凹
6.5	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
7	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
7.1	1	120	200	1	6	60°凹
7.2	1	120	200	1	6	60°凹
7.3	1	120	200	1	6	60°凹
7.4	1	120	250	1	6	60°凹
7.5	1	120	200	1	6	60°凹
	1	200	300	1	6	60°凹
8	1	100	200	1	6	60°凹
	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
	1	200	300	1	6	60°凹
8.1	1	120	200	1	6	60°凹
8.2	1	120	200	1	6	60°凹
8.3	1	120	200	1	6	60°凹
8.4	1	120	200	1	6	60°凹
8.5	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
	1	200	300	1	6	60°凹
9	1	100	200	1	6	60°凹
	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
9.1	1	120	200	1	6	60°凹
9.2	1	120	200	1	6	60°凹
9.3	1	120	200	1	6	60°凹
9.4	1	120	200	1	6	60°凹
9.5	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
	1	200	300	1	6	60°凹

直径 (φD)	食付長 (T)	刃長 (ℓ)	全長 (L)	MTNo.	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Overall Length	Shank MTNo.	Number of Flutes	Center
10	1	120	200	1	6	60°凹
	1	150	250	1	6	60°凹
	1	160	250	1	6	60°凹
10.1	1	200	300	1	6	60°凹
	1	150	250	1	6	60°凹
10.2	1	150	250	1	6	60°凹
10.3	1	150	250	1	6	60°凹
10.4	1	150	250	1	6	60°凹
10.5	1	150	250	1	6	60°凹
	1	200	300	1	6	60°凹
	1	150	250	1	6	60°凹
11	1	150	250	1	6	60°凹
	1	150	300	1	6	60°凹
	1	200	300	1	6	60°凹
	1	200	350	1	6	60°凹
11.1	1	250	350	1	6	60°凹
	1	150	250	1	6	60°凹
	1	150	300	1	6	60°凹
	1	200	350	1	6	60°凹
11.2	1	150	250	1	6	60°凹
11.3	1	150	250	1	6	60°凹
11.4	1	150	250	1	6	60°凹
11.5	1	150	250	1	6	60°凹
	1	150	300	1	6	60°凹
	1	160	250	1	6	60°凹
	1	200	300	1	6	60°凹
	1	200	350	1	6	60°凹
12	1	150	250	1	6	60°凹
	1	200	300	1	6	60°凹
	1	200	350	1	6	60°凹
	1	250	350	1	6	60°凹
	1	300	400	1	6	60°凹
12.1	1	150	250	1	6	60°凹
	1	160	250	1	6	60°凹
12.2	1	150	350	1	6	60°凹
	1	150	250	1	6	60°凹
	1	160	250	1	6	60°凹
12.3	1	150	350	1	6	60°凹
	1	150	250	1	6	60°凹
12.4	1	150	250	1	6	60°凹
	1	150	350	1	6	60°凹
12.5	1	150	300	1	6	60°凹
	1	200	300	1	6	60°凹
	1	200	350	1	6	60°凹