


キーシードカッター Keyseat Cutter



公差 (Tolerance)	D				ℓ1				d
	8~16	+0.3 +0.18	18~28	+0.35 +0.21	0.5~ 3	-0.014 -0.028	3.5~ 6	-0.020 -0.038	h8
	30~45	+0.43 +0.26	48~80	+0.5 +0.3	7 ~10	-0.025 -0.047	11 ~16	-0.032 -0.059	

右刃ストレート SKH51
Straight Flute HSS

刃径 (ΦD)	刃厚 (ℓ1)	首径 (d1)	首長 (ℓ2)	全長 (L)	シャンク径 (Φd)	刃数 (N)	形状
Dia.	Cut Width	Neck Dia.	Neck Length	Overall Length	Shank Dia.	Number of Flutes	Shape
8	0.5	3.7	6	50	8	8	図1
	0.6	3.7	6	50	8	8	
	0.7	3.7	6	50	8	8	
	0.8	3.7	6	50	8	8	
	0.9	3.7	6	50	8	8	
	1	3.7	6	50	8	8	
	1.1	3.7	6	50	8	8	
	1.2	3.7	6	50	8	8	
	1.3	3.7	6	50	8	8	
	1.4	3.7	6	50	8	8	
	1.5	3.7	6	50	8	8	
	1.6	3.7	6	50	8	8	
	1.7	3.7	6	50	8	8	
	1.8	3.7	6	50	8	8	
	1.9	3.7	6	50	8	8	
	2	3.7	6	50	8	8	
	2.1	3.7	6	50	8	8	
	2.2	3.7	6	50	8	8	
	2.3	3.7	6	50	8	8	
	2.4	3.7	6	50	8	8	
	2.5	3.7	6	50	8	8	
	2.6	3.7	6	50	8	8	
	2.7	3.7	6	50	8	8	
	2.8	3.7	6	50	8	8	
	2.9	3.7	6	50	8	8	
	3	3.7	6	50	8	8	
	3.5	3.7	6	50	8	8	
	4	3.7	6	50	8	8	
	4.5	3.7	6	50	8	8	
	5	3.7	6	50	8	8	
	6	3.7	6	50	8	8	
10	0.5	4.2	5.8	50	8	8	図1
	0.6	4.2	5.8	50	8	8	
	0.7	4.2	5.8	50	8	8	
	0.8	4.2	5.8	50	8	8	
	0.9	4.2	5.8	50	8	8	
	1	4.2	5.8	50	8	8	
	1.1	4.2	5.8	50	8	8	
	1.2	4.2	5.8	50	8	8	

刃径 (ΦD)	刃厚 (ℓ1)	首径 (d1)	首長 (ℓ2)	全長 (L)	シャンク径 (Φd)	刃数 (N)	形状
Dia.	Cut Width	Neck Dia.	Neck Length	Overall Length	Shank Dia.	Number of Flutes	Shape
10	1.3	4.2	5.8	50	8	8	図1
	1.4	4.2	5.8	50	8	8	
	1.5	4.2	5.8	50	8	8	
	1.6	4.2	5.8	50	8	8	
	1.7	4.2	5.8	50	8	8	
	1.8	4.2	5.8	50	8	8	
	1.9	4.2	5.8	50	8	8	
	2	4.2	5.8	50	8	8	
	2.1	4.2	5.8	50	8	8	
	2.2	4.2	5.8	50	8	8	
	2.3	4.2	5.8	50	8	8	
	2.4	4.2	5.8	50	8	8	
	2.5	4.2	5.8	50	8	8	
	2.6	4.2	5.8	50	8	8	
	2.7	4.2	5.8	50	8	8	
	2.8	4.2	5.8	50	8	8	
	2.9	4.2	5.8	50	8	8	
	3	4.2	5.8	50	8	8	
	3.5	4.2	5.8	50	8	8	
	4	4.2	5.8	50	8	8	
	4.5	4.2	5.8	50	8	8	
	5	4.2	5.8	50	8	8	
	6	4.2	5.8	50	8	8	
	0.5	4.4	7	50	10	8	
	0.6	4.4	7	50	10	8	
	0.7	4.4	7	50	10	8	
	0.8	4.4	7	50	10	8	
	0.9	4.4	7	50	10	8	
	1	4.4	7	50	10	8	
	1.1	4.4	7	50	10	8	
	1.2	4.4	7	50	10	8	
	1.3	4.4	7	50	10	8	
	1.4	4.4	7	50	10	8	
	1.5	4.4	7	50	10	8	
	1.6	4.4	7	50	10	8	
	1.7	4.4	7	50	10	8	
	1.8	4.4	7	50	10	8	
	1.9	4.4	7	50	10	8	
	2	4.4	7	50	10	8	