


マシンリーマ Machine Reamer



公差 (Tolerance)	D								
	0.01トピ Increment 0.01	$+0.005$ 0	3	$+0.007$ $+0.002$	3.1~ 6	$+0.009$ $+0.004$	6.1~ 10	$+0.012$ $+0.006$	10.1~18
	18.1~30	$+0.017$ $+0.008$	30.1~50	$+0.02$ $+0.009$	51 ~80	$+0.024$ $+0.011$	81 ~100	$+0.028$ $+0.013$	

右刃ストレート 食付角度45° SKH51  
Straight Flute Chamfer Angle45° HSS

直径 (φD)	食付長 (T)	刃長 (ℓ1)	首長 (ℓ2)	全長 (L)	MTNo.	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Neck Length	Overall Length	Shank MTNo.	Number of Flutes	Center
3	0.5	35	9.5	110	1	6	60° 凹
3.1	0.5	35	9.5	110	1	6	60° 凹
3.2	0.5	35	9.5	110	1	6	60° 凹
3.3	0.5	35	9.5	110	1	6	60° 凹
3.4	0.5	35	9.5	110	1	6	60° 凹
3.5	0.5	35	9.5	110	1	6	60° 凹
3.6	0.5	35	9.5	110	1	6	60° 凹
3.7	0.5	35	9.5	110	1	6	60° 凹
3.8	0.5	35	9.5	110	1	6	60° 凹
3.9	0.5	35	9.5	110	1	6	60° 凹
4	0.5	35	9.5	110	1	6	60° 凹
4.1	0.5	45	9.5	120	1	6	60° 凹
4.2	0.5	45	9.5	120	1	6	60° 凹
4.3	0.5	45	9.5	120	1	6	60° 凹
4.4	0.5	45	9.5	120	1	6	60° 凹
4.5	0.5	45	9.5	120	1	6	60° 凹
4.6	0.5	45	9.5	120	1	6	60° 凹
4.7	0.5	45	9.5	120	1	6	60° 凹
4.8	0.5	45	9.5	120	1	6	60° 凹
4.9	0.5	45	9.5	120	1	6	60° 凹
5	0.5	45	9.5	120	1	6	60° 凹
5.1	1	45	9.5	120	1	6	60° 凹
5.2	1	45	9.5	120	1	6	60° 凹
5.3	1	45	9.5	120	1	6	60° 凹
5.4	1	45	9.5	120	1	6	60° 凹
5.5	1	45	9.5	120	1	6	60° 凹
5.6	1	50	14.5	130	1	6	60° 凹
5.7	1	50	14.5	130	1	6	60° 凹
5.8	1	50	14.5	130	1	6	60° 凹
5.9	1	50	14.5	130	1	6	60° 凹
6	1	50	14.5	130	1	6	60° 凹
6.1	1	50	14.5	130	1	6	60° 凹
6.2	1	50	14.5	130	1	6	60° 凹
6.3	1	50	14.5	130	1	6	60° 凹
6.4	1	50	14.5	130	1	6	60° 凹
6.5	1	50	14.5	130	1	6	60° 凹
6.6	1	55	19.5	140	1	6	60° 凹
6.7	1	55	19.5	140	1	6	60° 凹
6.8	1	55	19.5	140	1	6	60° 凹
6.9	1	55	19.5	140	1	6	60° 凹
7	1	55	19.5	140	1	6	60° 凹
7.1	1	55	19.5	140	1	6	60° 凹
7.2	1	55	19.5	140	1	6	60° 凹

直径 (φD)	食付長 (T)	刃長 (ℓ1)	首長 (ℓ2)	全長 (L)	MTNo.	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Neck Length	Overall Length	Shank MTNo.	Number of Flutes	Center
7.3	1	55	19.5	140	1	6	60° 凹
7.4	1	55	19.5	140	1	6	60° 凹
7.5	1	55	19.5	140	1	6	60° 凹
7.6	1	60	24.5	150	1	6	60° 凹
7.7	1	60	24.5	150	1	6	60° 凹
7.8	1	60	24.5	150	1	6	60° 凹
7.9	1	60	24.5	150	1	6	60° 凹
8	1	60	24.5	150	1	6	60° 凹
8.1	1	60	24.5	150	1	6	60° 凹
8.2	1	60	24.5	150	1	6	60° 凹
8.3	1	60	24.5	150	1	6	60° 凹
8.4	1	60	24.5	150	1	6	60° 凹
8.5	1	60	24.5	150	1	6	60° 凹
8.6	1	70	24.5	160	1	6	60° 凹
8.7	1	70	24.5	160	1	6	60° 凹
8.8	1	70	24.5	160	1	6	60° 凹
8.9	1	70	24.5	160	1	6	60° 凹
9	1	70	24.5	160	1	6	60° 凹
9.1	1	70	24.5	160	1	6	60° 凹
9.2	1	70	24.5	160	1	6	60° 凹
9.3	1	70	24.5	160	1	6	60° 凹
9.4	1	70	24.5	160	1	6	60° 凹
9.5	1	70	24.5	160	1	6	60° 凹
9.6	1	70	24.5	160	1	6	60° 凹
9.7	1	70	24.5	160	1	6	60° 凹
9.8	1	70	24.5	160	1	6	60° 凹
9.9	1	70	24.5	160	1	6	60° 凹
10	1	70	24.5	160	1	6	60° 凹
10.1	1	70	24.5	160	1	6	60° 凹
10.2	1	70	24.5	160	1	6	60° 凹
10.3	1	70	24.5	160	1	6	60° 凹
10.4	1	70	24.5	160	1	6	60° 凹
10.5	1	70	24.5	160	1	6	60° 凹
10.6	1	75	29.5	170	1	6	60° 凹
10.7	1	75	29.5	170	1	6	60° 凹
10.8	1	75	29.5	170	1	6	60° 凹
10.9	1	75	29.5	170	1	6	60° 凹
11	1	75	29.5	170	1	6	60° 凹
11.1	1	75	29.5	170	1	6	60° 凹
11.2	1	75	29.5	170	1	6	60° 凹
11.3	1	75	29.5	170	1	6	60° 凹
11.4	1	75	29.5	170	1	6	60° 凹
11.5	1	75	29.5	170	1	6	60° 凹