


ウェルディング レデューサー(オス) R



チューブ(ミリサイズ)とパイプ(ANSI)

品番	A 呼び径		F パイプサイズ		D		W		N		H		L		I	
	mm	呼び	mm	呼び	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm	mm
VUWR-3X10.3-V	3	1/8	10.3		2.4		12		23.9		9.7		30.5		12.9	
VUWR-4X10.3-V	4	1/8	10.3		2.4		12		24.6		9.7		31.2		13.7	
VUWR-6X10.3-V	6	1/8	10.3		4.8		14		25.4		9.7		32.8		15.3	
VUWR-6X13.7-V	6	1/4	13.7		4.8		14		30.5		14.2		37.9		15.3	
VUWR-8X10.3-V	8	1/8	10.3		5.1		15		26.7		9.7		34.2		16.2	
VUWR-8X13.7-V	8	1/4	13.7		6.4		15		31.2		14.2		38.7		16.2	
VUWR-8X21.3-V	8	1/2	21.3		6.4		22		38.1		19		45.6		16.2	
VUWR-10X10.3-V	10	1/8	10.3		5.1		18		28.7		9.7		36.3		17.2	
VUWR-10X13.7-V	10	1/4	13.7		7.1		18		33.3		14.2		40.9		17.2	
VUWR-10X17.1-V	10	3/8	17.1		7.9		18		33.3		14.2		40.9		17.2	
VUWR-10X21.3-V	10	1/2	21.3		7.9		22		38.9		19		46.5		17.2	
VUWR-12X13.7-V	12	1/4	13.7		7.1		22		33.3		14.2		43.4		22.8	
VUWR-12X17.1-V	12	3/8	17.1		9.5		22		33.3		14.2		43.4		22.8	
VUWR-12X21.3-V	12	1/2	21.3		9.5		22		38.9		19		49		22.8	
VUWR-12X26.7-V	12	3/4	26.7		9.5		27		40.4		19		50.5		22.8	
VUWR-12X33.4-V	12	1	33.4		9.5		35		47.6		23.9		57.7		22.8	
VUWR-14X17.1-V	14	3/8	17.1		10.4		24		34		14.2		44.1		24.4	
VUWR-14X21.3-V	14	1/2	21.3		11		24		38.9		19		49		24.4	
VUWR-15X21.3-V	15	1/2	21.3		11.9		24		38.9		19		49		24.4	
VUWR-16X21.3-V	16	1/2	21.3		12.7		24		38.9		19		49		24.4	
VUWR-18X21.3-V	18	1/2	21.3		13.5		27		40.4		19		50.5		24.4	
VUWR-20X21.3-V	20	1/2	21.3		13.5		30		42.2		19		52.3		26	
VUWR-20X26.7-V	20	3/4	26.7		15.8		30		44		19		54.1		24.4	

チューブ(インチサイズ)とパイプ(ANSI)

品番	A 呼び径		F パイプサイズ		D		W		N		H		L		I		熱電対 対応品
	in	mm	呼び	mm	in	mm	in	mm	in	mm	in	mm	in	mm	in	mm	
VUWR-3.2X10.3-V	1/8	3.17	1/8	10.3	0.09	2.3	7/16	11.1	0.94	23.9	0.38	9.7	1.2	30.5	0.5	12.7	O
VUWR-4.8X10.3-V	3/16	4.76	1/8	10.3	0.12	3.1	7/16	11.1	0.97	24.6	0.38	9.7	1.23	31.2	0.54	13.7	—
VUWR-6.35X10.3-V	1/4	6.35	1/8	10.3	0.19	4.8	1/2	12.7	1	25.4	0.38	9.7	1.29	32.8	0.6	15.2	—
VUWR-6.35X13.7-V	1/4	6.35	1/4	13.7	0.19	4.8	9/16	14.3	1.2	30.6	0.56	14.2	1.5	38	0.6	15.2	O
VUWR-6.35X21.3-T/C-V	1/4	6.35	1/2	21.3	0.53	13.5	7/8	22.2	1.53	38.9	0.75	19	1.82	46.3	—	—	O
VUWR-7.93X10.3-V	5/16	7.93	1/8	10.3	0.2	5.1	9/16	14.3	1.05	26.7	0.38	9.7	1.34	34.1	0.64	16.3	—
VUWR-7.93X13.7-V	5/16	7.93	1/4	13.7	0.25	6.4	9/16	14.3	1.23	31.3	0.56	14.2	1.52	38.7	0.64	16.3	O
VUWR-9.52X13.7-V	3/8	9.52	1/4	13.7	0.28	7.1	5/8	15.9	1.28	32.5	0.56	14.2	1.57	39.9	0.66	16.8	—
VUWR-9.52X17.1-V	3/8	9.52	3/8	17.1	0.28	7.1	11/16	17.5	1.28	32.5	0.56	14.2	1.57	39.9	0.66	16.8	—
VUWR-9.52X21.3-V	3/8	9.52	1/2	21.3	0.28	7.1	7/8	22.2	1.53	38.9	0.75	19	1.82	46.3	0.66	16.8	—
VUWR-9.52X26.7-V	3/8	9.52	3/4	26.7	0.28	7.1	1 1/16	27	1.59	40.4	0.75	19	1.88	47.8	0.66	16.8	—
VUWR-12.7X17.1-V	1/2	12.7	3/8	17.1	0.41	10.4	13/16	20.6	1.31	33.3	0.56	14.2	1.71	43.4	0.9	22.9	—
VUWR-12.7X21.3-V	1/2	12.7	1/2	21.3	0.41	10.4	7/8	22.2	1.53	38.9	0.75	19	1.93	49	0.9	22.9	O
VUWR-12.7X26.7-V	1/2	12.7	3/4	26.7	0.41	10.4	1 1/16	27	1.59	40.4	0.75	19	1.99	50.5	0.9	22.9	O
VUWR-12.7X33.4-V	1/2	12.7	1	33.4	0.41	10.4	1 3/8	34.9	1.87	47.5	0.94	23.9	2.27	57.6	0.9	22.9	O
VUWR-15.88X21.3-V	5/8	15.87	1/2	21.3	0.5	12.7	15/16	23.8	1.53	38.9	0.75	19	1.93	49	0.96	24.4	—
VUWR-19.05X13.7-V	3/4	19.05	1/4	13.7	0.28	7.1	1 1/16	27	1.5	38.1	0.56	14.2	1.9	48.2	0.96	24.4	—
VUWR-19.05X21.3-V	3/4	19.05	1/2	21.3	0.53	13.5	1 1/16	27	1.53	38.9	0.75	19	1.93	49	0.96	24.4	—
VUWR-19.05X26.7-V	3/4	19.05	3/4	26.7	0.62	15.7	1 1/16	27	1.59	40.4	0.75	19	1.99	50.5	0.96	24.4	—
VUWR-19.05X33.4-V	3/4	19.05	1	33.4	0.62	15.8	1 3/8	34.9	1.85	47	0.94	23.9	2.25	57.1	0.96	24.4	—
VUWR-25.4X21.3-V	1	25.4	1/2	21.3	0.53	13.5	1 3/8	34.9	1.68	42.7	0.75	19	2.16	54.9	1.23	31.2	—
VUWR-25.4X33.4-V	1	25.4	1	33.4	0.88	22.4	1 3/8	34.9	1.97	50	0.94	23.9	2.45	62.2	1.23	31.2	—

チューブ(インチサイズ)とパイプ(インチサイズ)

品番	A 呼び径		F		D	W	N	H	L
	in	mm	in	mm	mm	mm	mm	mm	mm
VUWR-14.2X27.2-T/C-V	9/16	14.29	3/4	27.2	19.4	30	40.5	19.1	50.6

熱電対用タイプも製作できます。

ご注文の際は、選定した継手の品番の最後に-T/Cを付けて下さい。

※AとFの寸法の組合せによっては対応できない場合もあります。

※"D" - 寸法は最小穴径です。 ※技術の進歩のために使用材料、寸法など予告なく多少変更することがありますのであらかじめご了承下さい。