


キャップユニオン

JC



チューブ端キャップ(ミリサイズ)

品番	A 呼び径	W	N	L	I
	mm	mm	mm	mm	mm
VUWJC-2-V	2	12	13.5	20.1	12.9
VUWJC-3-V	3	12	13.5	20.1	12.9
VUWJC-4-V	4	12	14.7	21.3	13.7
VUWJC-6-V	6	14	15.7	23.1	15.3
VUWJC-8-V	8	15	17	24.5	16.2
VUWJC-10-V	10	18	19	26.6	17.2
VUWJC-12-V	12	22	19	29.1	22.8
VUWJC-15-V	15	24	19.8	29.9	24.4
VUWJC-16-V	16	24	19.8	29.9	24.4
VUWJC-18-V	18	27	21.3	31.4	24.4
VUWJC-20-V	20	30	23.9	34	26
VUWJC-22-V	22	30	23.9	34	26
VUWJC-25-V	25	35	26.2	38.4	31.3

チューブ端キャップ(インチサイズ)

品番	A 呼び径		W		N		L		I	
	in	mm	in	mm	in	mm	in	mm	in	mm
VUWJC-1.6-V	1/16	1.58	5/16	7.9	0.44	11.2	0.59	15	0.34	8.6
VUWJC-3.2-V	1/8	3.17	7/16	11.1	0.53	13.5	0.79	20.1	0.5	12.7
VUWJC-4.8-V	3/16	4.76	7/16	11.1	0.58	14.7	0.84	21.3	0.54	13.7
VUWJC-6.35-V	1/4	6.35	1/2	12.7	0.63	16	0.92	23.4	0.6	15.2
VUWJC-7.93-V	5/16	7.93	9/16	14.3	0.67	17	0.96	24.4	0.64	16.3
VUWJC-9.52-V	3/8	9.52	5/8	15.9	0.72	18.3	1.01	25.7	0.66	16.8
VUWJC-12.7-V	1/2	12.7	13/16	20.6	0.75	19.1	1.15	29.2	0.9	22.9
VUWJC-15.88-V	5/8	15.87	15/16	23.8	0.78	19.8	1.18	29.9	0.96	24.4
VUWJC-19.05-V	3/4	19.05	1 1/16	27	0.84	21.3	1.24	31.4	0.96	24.4
VUWJC-22.22-V	7/8	22.22	1 3/16	30.2	0.94	23.9	1.34	34	1.02	25.9
VUWJC-25.4-V	1	25.4	1 3/8	34.9	1.03	26.2	1.51	38.4	1.23	31.2