

Ordering information

1 **SS1** 2 - 3 4 5 - 6 (7)

1 **Current Rating** - 01,02,03, **04,06,08,10,13,15**

1~10A: UL, CUL, VDE, CQC approved

2 Schematic type

Standard(empty),B,D,E,F,H,J,K,M

3 Components table

Refer components table

4 Ground choke (options)

G ; Lg=100uH

G1 ; Lg=6uH

G2 ; Lg=180uH

5 Bleeder resistor (options)

R ; R=1M ohm; 1/4W min.

6 Output terminal type

Q ; fast-on(6.3mm)

S ; solder(4mm)


W; with wire

7 Case type

S,B,SA

Schematic type

Standard



R:options Lg:options

* please call for other's alternates

Insertion loss table

(In 50ohm system according IEC/CISPR No.17)

Code	Rating	Comm.Mode(L-G)in MHz						Diff.Mode(L-L)in MHz					
		.15	.5	1	5	10	30	.15	.5	1	5	10	30
Empty	1A	34	38	40	32	26	11	8	25	37	71	62	12
	2A	29	32	55	48	49	51	8	23	34	68	64	14
	3A	28	36	39	45	48	39	8	19	27	58	65	15
	4A	28	36	39	45	48	39	8	19	27	58	65	15
	6A	18	24	28	44	50	47	8	18	26	43	51	31
	8A	20	26	30	44	47	40	8	18	24	65	59	22
	10A	8	14	18	33	41	39	8	18	25	29	38	31
	13A	7	14	19	34	40	38	7	17	23	39	47	27
	15A	7	14	19	34	40	38	7	17	23	39	47	27
	15A	7	14	19	34	40	38	7	17	23	39	47	27
B	1A	29	33	47	53	57	41	8	23	35	73	58	14
	2A	28	37	44	52	56	41	8	19	27	74	59	17
	3A	25	33	46	53	57	44	8	19	29	63	62	13
	4A	20	24	26	27	25	15	8	18	24	58	57	21
	6A	19	29	36	49	55	46	8	18	23	50	54	24
	8A	20	24	26	27	25	15	8	18	24	58	57	21
	10A	11	19	24	41	63	36	8	18	24	51	46	25
	13A	8	15	21	37	46	36	7	17	23	39	48	27
	15A	7	15	21	37	46	36	7	17	23	39	48	27
	15A	7	15	21	37	46	36	7	17	23	39	48	27

Components table

Code	Cx(uF)	Cy(pF)	Inductance L=mH x 2 in Amps									Max. Leakage(mA)		Rating Volts		Hi-pot test Volts	
			1A	2A	3A	4A	6A	8A	10A	13A	15A	115VAC	250VAC	VAC	Hz	L,N-G	L-N
Empty	0.1	2200	6.5	3.8	2.5	2.5	0.8	1.05	0.2	0.2	0.2	0.2	0.4	115/250	50/60	2250VDC	1450VDC
B	0.1	3300	3.7	2.7	1.8	1.3	0.8	1.05	0.3	0.2	0.2	0.25	0.5	115/250	50/60	2250VDC	1450VDC

* please call for other's combinations