


FITTING

N

NUT

袋ナット



(METRIC)

(Unit:mm)

TUBE O.D. T	PART. No.	G	L
2	N- 2	8	8
3	N- 3	12	12
4	N- 4	14	14
5	N- 5	14	14
6	N- 6	14	14
8	N- 8	15.87	14.5
10	N-10	19	16
12	N-12	23	17.5
14	N-14	26	17.5
15	N-15	26	17.5
16	N-16	26	17.5
18	N-18	30	19
20	N-20	32	19
22	N-22	35	19
25	N-25	38	22

(INCHES)

(Unit:mm)

TUBE O.D. T	PART. No.	G	L
1/16" : 1.6	N-005	8	8
1/8" : 3.18	N- 01	12	12
1/4" : 6.35	N- 02	14	14
3/16" : 4.76	N-015	14	14
5/16" : 7.94	N-025	15.87	14.5
3/8" : 9.53	N- 03	17.46	15.5
1/2" : 12.7	N- 04	23	17.5
5/8" : 15.87	N- 05	26	17.5
3/4" : 19.05	N- 06	30	19
7/8" : 22.23	N- 07	35	19
1" : 25.4	N- 08	38	22

(SCHEDULE)

1/8" B:	PART. No.	G	L
10.5	N-10.5	19	16
13.8	N-13.8	26	17.5
17.3	N-17.3	30	19
21.7	N-21.7	35	19

IN

INSERT

芯管



(METRIC)

(Unit:mm)

TUBE O.D. T	PART. No.	TUBE I.D.
3	IN- 3	2
4	IN- 4	3
6	IN- 6	4
8	IN- 8	6
10	IN-10	8
12	IN-12	10

(INCHES)

(Unit:mm)

TUBE O.D. T	PART. No.	TUBE I.D.
1/8" : 3.18	IN- 01	2.18
1/4" : 6.35	IN- 02	4.35
5/16" : 7.94	IN-025	5.94
3/8" : 9.53	IN- 03	7.53
1/2" : 12.7	IN- 04	10.7

※管外径5φも製作しております。


※管外径3/16も製作しております。

テフロンチューブ以外の軟質チューブにも使用出来ます。各サイズ14~25.05~08も製作できます。

FF

FRONT FERRULE

フェラル(フロント)



(METRIC)

(Unit:mm)

TUBE O.D. T	PART. No.
2	FF- 2
3	FF- 3
4	FF- 4
5	FF- 5
6	FF- 6
8	FF- 8
10	FF-10
12	FF-12
14	FF-14
15	FF-15
16	FF-16
18	FF-18
20	FF-20
22	FF-22
25	FF-25

(INCHES)

(Unit:mm)

TUBE O.D. T	PART. No.
1/16" : 1.6	FF-005
1/8" : 3.18	FF- 01
1/4" : 6.35	FF- 02
3/16" : 4.76	FF-015
5/16" : 7.94	FF-025
3/8" : 9.53	FF- 03
1/2" : 12.7	FF- 04
5/8" : 15.87	FF- 05
3/4" : 19.05	FF- 06
7/8" : 22.23	FF- 07
1" : 25.4	FF- 08


(SCHEDULE)

1/8" B:	PART. No.
10.5	FF-10.5
13.8	FF-13.8
17.3	FF-17.3
21.7	FF-21.7

FR

REAR FERRULE

フェラル(リア)



(METRIC)

(Unit:mm)

TUBE O.D. T	PART. No.
2	FR- 2
3	FR- 3
4	FR- 4
5	FR- 5
6	FR- 6
8	FR- 8
10	FR-10
12	FR-12
14	FR-14
15	FR-15
16	FR-16
18	FR-18
20	FR-20
22	FR-22
25	FR-25

(INCHES)

(Unit:mm)

TUBE O.D. T	PART. No.
1/16" : 1.6	FR-005
1/8" : 3.18	FR- 01
1/4" : 6.35	FR- 02
3/16" : 4.76	FR-015
5/16" : 7.94	FR-025
3/8" : 9.53	FR- 03
1/2" : 12.7	FR- 04
5/8" : 15.87	FR- 05
3/4" : 19.05	FR- 06
7/8" : 22.23	FR- 07
1" : 25.4	FR- 08

(SCHEDULE)

1/8" B:	PART. No.
10.5	FR-10.5
13.8	FR-13.8
17.3	FR-17.3
21.7	FR-21.7