


## 形状・寸法

## ■ スタブエンド(ラップジョイント)

LJ




単位:mm

径の呼び		外径 OD	厚さ T		つば径 G		長さ F	コーナー R	
A	B		10S	20S	5K	10K		最大	最小
15	1/2	21.7	2.1	2.5	44	51	30	3	1.5
20	3/4	27.2	2.1	2.5	49	56	30	3	1.5
25	1	34.0	2.8	3.0	59	67	50	3	1.5
32	1 1/4	42.7	2.8	3.0	70	76	50	4	2
40	1 1/2	48.6	2.8	3.0	75	81	50	4	2
50	2	60.5	2.8	3.5	85	96	50	4	2
65	2 1/2	76.3	3.0	3.5	110	116	50	5	2.5
80	3	89.1	3.0	4.0	121	126	50	5	2.5
90	3 1/2	101.6	3.0	4.0	131	136	50	5	2.5
100	4	114.3	3.0	4.0	141	151	50	5	2.5
125	5	139.8	3.4	5.0	176	182	50	6	3
150	6	165.2	3.4	5.0	206	212	50	6	3
200	8	216.3	4.0	6.5	252	262	65	6	3
250	10	267.4	4.0	6.5	317	324	65	6	3
300	12	318.5	4.5	6.5	360	368	65	9	3
350	14	355.6	5.0	8.0	403	413	75	9	3
400	16	406.4	5.0	8.0	463	475	75	9	3
450	18	457.2	5.0	8.0	523	530	75	9	3
500	20	508.0	5.5	9.5	573	585	75	9	3
550	22	558.8	5.5	9.5	630	640	75	9	3
600	24	609.6	6.5	9.5	680	690	75	9	3

## ■ キャップ

CAP



単位:mm

径の呼び		外径 OD	10S		20S		S40		背から端面 までの距離 E
A	B		内径 ID	厚さ T	内径 ID	厚さ T	内径 ID	厚さ T	
15	1/2	21.7	17.5	2.1	16.7	2.5	16.1	2.8	25.4
20	3/4	27.2	23.0	2.1	22.2	2.5	21.4	2.9	25.4
25	1	34.0	28.4	2.8	28.0	3.0	27.2	3.4	38.1
32	1 1/4	42.7	37.1	2.8	36.7	3.0	35.5	3.6	38.1
40	1 1/2	48.6	43.0	2.8	42.6	3.0	41.2	3.7	38.1
50	2	60.5	54.9	2.8	53.5	3.5	52.7	3.9	38.1
65	2 1/2	76.3	70.3	3.0	69.3	3.5	65.9	5.2	38.1
80	3	89.1	83.1	3.0	81.1	4.0	78.1	5.5	50.8
90	3 1/2	101.6	95.6	3.0	93.6	4.0	90.2	5.7	63.5
100	4	114.3	108.3	3.0	106.3	4.0	102.3	6.0	63.5
125	5	139.8	133.0	3.4	129.8	5.0	126.6	6.6	76.2
150	6	165.2	158.4	3.4	155.2	5.0	151.0	7.1	88.9
200	8	216.3	208.3	4.0	203.3	6.5	199.9	8.2	101.6
250	10	267.4	259.4	4.0	254.4	6.5	248.8	9.3	127.0
300	12	318.5	309.5	4.5	305.5	6.5	297.9	10.3	152.4
350	14	355.6	345.6	5.0	339.6	8.0	333.4	11.1	165.1
400	16	406.4	396.4	5.0	390.4	8.0	381.0	12.7	177.8
450	18	457.2	447.2	5.0	441.2	8.0	428.6	14.3	203.2
500	20	508.0	497.0	5.5	489.0	9.5	477.8	15.1	228.6
550	22	558.8	547.8	5.5	539.8	9.5	527.0	15.9	254.0
600	24	609.6	596.6	6.5	590.6	9.5	574.6	17.5	266.7
650	26	660.4	644.4	8.0	635.0	12.7	622.6	18.9	266.7