

TD 超硬付刃テーパーシャंकドリル

SINCE 1935
F.K.D.®


TD Taper Shank Drills, G-2 Tungsten Carbide Tipped

材質=G2 (ロー付タイプ)
リード角=右振り20°



直径公差

$D \leq 18$ 0~-0.03
 $18 < D \leq 29$ 0~-0.033
 $29 < D \leq 60$ 0~-0.039



●注文例=型番、刃径、数量 「TD 18.4」

型番	刃径(D)	溝長(ℓ)	全長(L)	シャंक
TD	18.4	110	210	MT2
TD	18.5	110	210	MT2
TD	18.6	110	210	MT2
TD	18.7	110	210	MT2
TD	18.8	110	210	MT2
TD	18.9	110	210	MT2
TD	19	110	210	MT2
TD	19.1	110	210	MT2
TD	19.2	110	210	MT2
TD	19.3	110	210	MT2
TD	19.4	110	210	MT2
TD	19.5	110	210	MT2
TD	19.6	110	210	MT2
TD	19.7	110	210	MT2
TD	19.8	110	210	MT2
TD	19.9	110	210	MT2
TD	20	110	210	MT2
TD	20.1	110	210	MT2
TD	20.2	110	210	MT2
TD	20.3	110	210	MT2
TD	20.4	110	210	MT2
TD	20.5	110	210	MT2
TD	20.6	110	210	MT2
TD	20.7	110	210	MT2
TD	20.8	110	210	MT2
TD	20.9	110	210	MT2
TD	21	110	210	MT2
TD	21.1	120	220	MT2
TD	21.2	120	220	MT2
TD	21.3	120	220	MT2
TD	21.4	120	220	MT2
TD	21.5	120	220	MT2
TD	21.6	120	220	MT2
TD	21.7	120	220	MT2
TD	21.8	120	220	MT2
TD	21.9	120	220	MT2
TD	22	120	220	MT2
TD	22.1	120	220	MT2
TD	22.2	120	220	MT2
TD	22.3	120	220	MT2
TD	22.4	120	220	MT2
TD	22.5	120	220	MT2
TD	22.6	120	220	MT2
TD	22.7	120	220	MT2
TD	22.8	120	220	MT2
TD	22.9	120	220	MT2

型番	刃径(D)	溝長(ℓ)	全長(L)	シャंक
TD	23	120	220	MT2
TD	23.1	130	250	MT3
TD	23.2	130	250	MT3
TD	23.3	130	250	MT3
TD	23.4	130	250	MT3
TD	23.5	130	250	MT3
TD	23.6	130	250	MT3
TD	23.7	130	250	MT3
TD	23.8	130	250	MT3
TD	23.9	130	250	MT3
TD	24	130	250	MT3
TD	24.1	140	260	MT3
TD	24.2	140	260	MT3
TD	24.3	140	260	MT3
TD	24.4	140	260	MT3
TD	24.5	140	260	MT3
TD	24.6	140	260	MT3
TD	24.7	140	260	MT3
TD	24.8	140	260	MT3
TD	24.9	140	260	MT3
TD	25	140	260	MT3
TD	25.1	140	260	MT3
TD	25.2	140	260	MT3
TD	25.3	140	260	MT3
TD	25.4	140	260	MT3
TD	25.5	140	260	MT3
TD	25.6	140	260	MT3
TD	25.7	140	260	MT3
TD	25.8	140	260	MT3
TD	25.9	140	260	MT3
TD	26	140	260	MT3
TD	26.1	140	260	MT3
TD	26.2	140	260	MT3
TD	26.3	140	260	MT3
TD	26.4	140	260	MT3
TD	26.5	140	260	MT3
TD	26.6	140	260	MT3
TD	26.7	140	260	MT3
TD	26.8	140	260	MT3
TD	26.9	140	260	MT3
TD	27	140	260	MT3
TD	27.1	140	260	MT3
TD	27.2	140	260	MT3
TD	27.3	140	260	MT3
TD	27.4	140	260	MT3
TD	27.5	140	260	MT3

超硬付刃ドリル