

# Chamfering Mills 面取り用 エンドミル

## センタ面取りミル Center Chamfering Mill



|                        |         |    |   |      |
|------------------------|---------|----|---|------|
| 外径公差<br>Dia. tolerance | 0~-0.03 | h7 | $10 < D_s \leq 16$ : 0~-0.015<br>$18 < D_s \leq 30$ : 0~-0.018<br>$30 < D_s$ : 0~-0.025 | (mm) |
|------------------------|---------|----|---|------|



## 面取りカッタ Chamfering Cutter



|    |  |      |
|----|--|------|
| h7 | $D_s \leq 6$ : 0~-0.012<br>$6 < D_s \leq 10$ : 0~-0.015<br>$10 < D_s \leq 12$ : 0~-0.018 | (mm) |
|----|--|------|



### CM



| 商品コード<br>Item Code | 在庫<br>Stock | 寸法<br>Size (mm)    |                        |                       |                         |                        | 希望小売<br>価格(円)<br>Suggested<br>retail price(¥) |
|--------------------|-------------|--------------------|------------------------|-----------------------|-------------------------|------------------------|---|
|                    |             | 外径<br>Tool<br>Dia. | フラット幅<br>Flat<br>Width | 刃長<br>Flute<br>Length | 全長<br>Overall<br>Length | シャンク径<br>Shank<br>Dia. |   |
| CM4                | ●           | 4                  | 0.4                    | 11                    | 75                      | 8                      | 4,740   |
| CM6                | ●           | 6                  | 0.5                    | 13                    | 85                      | 10                     | 5,510   |
| CM8                | ●           | 8                  | 0.6                    | 19                    | 105                     | 12                     | 6,570   |
| CM10               | ●           | 10                 | 0.7                    | 22                    | 120                     | 16                     | 7,110   |
| CM12               | ●           | 12                 | 0.8                    | 26                    | 125                     | 16                     | 11,200  |
| CM16               | ●           | 16                 | 1                      | 32                    | 145                     | 20                     | 16,700  |
| CM20               | ●           | 20                 | 1.2                    | 38                    | 165                     | 25                     | 19,500  |
| CM25               | ●           | 25                 | 1.3                    | 45                    | 170                     | 32                     | 23,400  |
| CM30               | □           | 30                 | 1.5                    | 50                    | 180                     | 32                     | —   |
| CM35               | □           | 35                 | 1.8                    | 55                    | 180                     | 32                     | —   |
| CM40               | □           | 40                 | 1.8                    | 60                    | 200                     | 42                     | —   |
| CM45               | □           | 45                 | 2                      | 65                    | 200                     | 42                     | —   |
| CM50               | □           | 50                 | 2                      | 65                    | 200                     | 42                     | —   |

- 印：標準在庫品です。
- ：Stocked Items.
- 印：特定代理店在庫です。弊社営業へお問合せください。
- ：Stocked by specified distributor. Contact with our sales department.

### CE



| 商品コード<br>Item Code | 在庫<br>Stock | 寸法<br>Size (mm)    |       |                         |                        | 希望小売<br>価格(円)<br>Suggested<br>retail price(¥) |
|--------------------|-------------|--------------------|-------|-------------------------|------------------------|---|
|                    |             | 外径<br>Tool<br>Dia. | 加工径   | 全長<br>Overall<br>Length | シャンク径<br>Shank<br>Dia. |   |
| CE4                | ●           | 4                  | 2~3   | 50                      | 4                      | 1,750   |
| CE6                | ●           | 6                  | 3~5   | 50                      | 6                      | 1,750   |
| CE10               | ●           | 10                 | 5~9   | 55                      | 8                      | 2,200   |
| CE15               | ●           | 15                 | 7~14  | 70                      | 10                     | 3,000   |
| CE20               | ●           | 20                 | 10~19 | 100                     | 12                     | 4,530   |
| CE30               | ●           | 30                 | 15~29 | 120                     | 12                     | 9,600   |
| CE40               | ●           | 40                 | 20~39 | 170                     | MT3                    | 22,000  |
| CE50               | ●           | 50                 | 22~49 | 180                     | MT3                    | 33,000  |
| CE60               | ●           | 60                 | 25~59 | 195                     | MT3                    | 47,500  |

- 印：標準在庫品です。
- ：Stocked Items.

### 先端部拡大 Enlargement of tip section

