



AT<sub>1</sub>コイル用継手  
AT<sub>1</sub> Coil Fitting標準在庫品  
Standard stock products

## FM (回転メス・ニップル) FM (Rotary female connector)


部品番号 PART NO.	適用チューブ寸法 TUBE SIZE TO BE USED 外径×内径 O.D. (mm)×I.D. (mm)	R <sub>C</sub> (PT)	φd	L <sub>1</sub>	L <sub>2</sub>	L <sub>3</sub>	六角対辺 HEX.			重量 WEIGHT (g)	有効断面積 EFFECTIVE SECTIONAL AREA (mm <sup>2</sup> )
							S <sub>1</sub>	S <sub>2</sub>	S <sub>3</sub>		
FM- 6-PT1/4	7.6× 6	1/4	4.6	18.5	41	124	16	14	14	49	14
FM- 9-PT3/8	11 × 9	3/8	7.0	20.0	47	135	19	17	19	91	35
FM-12-PT1/2	15 ×12	1/2	10.0	26.5	59	165	25	22	23	161	75



## FO (回転オス・ニップル) FO (Rotary male connector)

部品番号 PART NO.	適用チューブ寸法 TUBE SIZE TO BE USED 外径×内径 O.D. (mm)×I.D. (mm)	R (PT)	φd	L <sub>1</sub>	L <sub>2</sub>	L <sub>3</sub>	六角対辺 HEX.			重量 WEIGHT (g)	有効断面積 EFFECTIVE SECTIONAL AREA (mm <sup>2</sup> )
							S <sub>1</sub>	S <sub>2</sub>	S <sub>3</sub>		
FO- 6-PT1/4	7.6× 6	1/4	4.6	10.5	39	122	14	14	14	44	14
FO- 9-PT3/8	11 × 9	3/8	7.0	12.0	46	134	17	17	19	86	35
FO-12-PT1/2	15 ×12	1/2	10.0	14.0	55	162	22	22	23	143	70

## &lt;スリーブ&gt; &lt;Sleeve&gt;



部品番号 PART NO.	適用チューブ外径 TUBE O.D. TO BE USED 外径 / O.D. (mm)
S-06T	7.6
S-09T	11.0
S-12T	15.0

※ジュンロンAT<sub>1</sub>コイル用継手の取付けは、袋ナットを手締後、スパナで底当たりするまで締付けて下さい。



※When fitting the fitting for the AT<sub>1</sub> coil, tighten the union nut by hand first and then with a spanner until it hits the main body.

AT<sub>4</sub>ジュンロン® AT<sub>4</sub>(極軟質ナイロンコイルチューブ)

標準在庫品

AT<sub>4</sub>(Super-flexible nylon coil tube)

Standard stock products



部品番号 PART NO.	チューブ寸法 / TUBE SIZE	最大使用長 MAX. WORKING LENGTH L+S (m)	チューブ破壊圧力 TUBE BURST PRESSURE 23°C (MPa)	最高使用圧力 MAX. WORKING PRESSURE 23°C (MPa)	コイル寸法 COIL DIMENSIONS		
	外径×内径×長さ O.D. × I.D. × LENGTH (mm) (mm) (m)				L (mm)	S (m)	D (mm)
AT <sub>4</sub> -04	4×2.5×10	6	5.0	<1.2	540	5.5	30
AT <sub>4</sub> -06	6×4 ×10	7	4.4	<1.0	540	6.5	45
AT <sub>4</sub> -08	8×6 ×10	7	3.1	<0.78	510	6.5	67
AT <sub>4</sub> -10	10×7.5×10	7	3.1	<0.78	400	6.6	95

●標準色：黒 / Standard color:black

●ご希望の長さに切ってご使用いただけます。 / It can be cut to a desired length.