


首下5Dc・ラジアスタイプ Under neck 5Dc, Radius type



外径公差
 φ1~φ6 : 0~-0.015
 φ7~φ20 : 0~-0.02

h5 h6
 10 < Ds ≤ 6 : 0~-0.005
 6 < Ds ≤ 10 : 0~-0.006
 10 < Ds ≤ 16 : 0~-0.008
 16 < Ds ≤ 20 : 0~-0.011
 Ds = 20 : 0~-0.013 (mm)

4枚刃
 4 Flutes



EP4SM4-0.1-0.2-0.5-1.0-1.5-2.0-3.0-5.0-7.5-10.5-12-15-16.5-18-2.5-3.0-PN



商品コード Item Code	在庫 Stock	寸法 Size(mm)							刃数 No. of flutes	形状 Shape	希望小売価格 Suggested retail price 特定代理店 希望小売価格 Specified distributor suggested retail price/ ¥
		外径 Dc Tool dia.	コーナ半径 r Coner radius	刃長 ℓ Flute length	首下長 ℓ2 Under neck length	首径 D1 Neck dia.	全長 L Overall length	シャンク径 Ds Shank dia.			
EP4SM4010-5-R0.1-PN	●	1	0.1	1.5	5	0.96	68	6	4	A	11,330
EP4SM4020-10-R0.1-PN	●	2	0.1	3	10	1.92	68	6	4	A	11,330
EP4SM4020-10-R0.2-PN	●		0.2	3	10	1.92	68	6	4	A	11,330
EP4SM4030-15-R0.2-PN	●	3	0.2	4.5	15	2.88	68	6	4	A	11,330
EP4SM4030-15-R0.5-PN	●		0.5	4.5	15	2.88	68	6	4	A	11,330
EP4SM4040-20-R0.2-PN	●	4	0.2	6	20	3.7	68	6	4	A	11,630
EP4SM4040-20-R0.5-PN	●		0.5	6	20	3.7	68	6	4	A	11,630
EP4SM4040-20-R1.0-PN	●		1	6	20	3.7	68	6	4	A	11,630
EP4SM4050-25-R0.2-PN	●	5	0.2	7.5	25	4.6	68	6	4	A	12,350
EP4SM4050-25-R0.5-PN	●		0.5	7.5	25	4.6	68	6	4	A	12,350
EP4SM4050-25-R1.0-PN	●		1	7.5	25	4.6	68	6	4	A	12,350
EP4SM4060-30-R0.3-PN	●	6	0.3	9	30	5.5	68	6	4	B	13,160
EP4SM4060-30-R0.5-PN	●		0.5	9	30	5.5	68	6	4	B	13,160
EP4SM4060-30-R1.0-PN	●		1	9	30	5.5	68	6	4	B	13,160
EP4SM4060-30-R1.5-PN	●		1.5	9	30	5.5	68	6	4	B	13,160
EP4SM4070-35-R0.3-PN	●	7	0.3	10.5	35	6.4	80	8	4	A	15,410
EP4SM4070-35-R0.5-PN	●		0.5	10.5	35	6.4	80	8	4	A	15,410
EP4SM4070-35-R1.0-PN	●		1	10.5	35	6.4	80	8	4	A	15,410
EP4SM4080-40-R0.3-PN	●	8	0.3	12	40	7.3	80	8	4	B	15,410
EP4SM4080-40-R0.5-PN	●		0.5	12	40	7.3	80	8	4	B	15,410
EP4SM4080-40-R1.0-PN	●		1	12	40	7.3	80	8	4	B	15,410
EP4SM4080-40-R1.5-PN	●		1.5	12	40	7.3	80	8	4	B	15,410
EP4SM4080-40-R2.0-PN	●		2	12	40	7.3	80	8	4	B	15,410
EP4SM4090-45-R0.3-PN	●	9	0.3	13.5	45	8.3	94	10	4	A	19,890
EP4SM4090-45-R0.5-PN	●		0.5	13.5	45	8.3	94	10	4	A	19,890
EP4SM4090-45-R1.0-PN	●		1	13.5	45	8.3	94	10	4	A	19,890
EP4SM4100-50-R0.3-PN	●	10	0.3	15	50	9.1	94	10	4	B	19,890
EP4SM4100-50-R0.5-PN	●		0.5	15	50	9.1	94	10	4	B	19,890
EP4SM4100-50-R1.0-PN	●		1	15	50	9.1	94	10	4	B	19,890
EP4SM4100-50-R1.5-PN	●		1.5	15	50	9.1	94	10	4	B	19,890
EP4SM4100-50-R2.0-PN	●		2	15	50	9.1	94	10	4	B	19,890
EP4SM4110-55-R0.3-PN	●	11	0.3	16.5	55	10.2	110	12	4	A	23,870
EP4SM4110-55-R0.5-PN	●		0.5	16.5	55	10.2	110	12	4	A	23,870
EP4SM4110-55-R1.0-PN	●		1	16.5	55	10.2	110	12	4	A	23,870
EP4SM4120-60-R0.3-PN	●	12	0.3	18	60	11	110	12	4	B	23,870
EP4SM4120-60-R0.5-PN	●		0.5	18	60	11	110	12	4	B	23,870
EP4SM4120-60-R1.0-PN	●		1	18	60	11	110	12	4	B	23,870
EP4SM4120-60-R1.5-PN	●		1.5	18	60	11	110	12	4	B	23,870
EP4SM4120-60-R2.0-PN	●		2	18	60	11	110	12	4	B	23,870
EP4SM4120-60-R2.5-PN	●		2.5	18	60	11	110	12	4	B	23,870
EP4SM4120-60-R3.0-PN	●	3	18	60	11	110	12	4	B	23,870	