




0~-0.01



0~-0.006

(mm)



○○WHMB○○○○-TH



商品コード Item code	在庫 Stock	寸法 Size (mm)				希望小売 価格(円) Suggested retail price(¥)
		直径 Tool dia. Dc	溝長 Flute length l	全長 Overall length L	シャンク径 Shank dia. Ds	
03WHMB0100-TH	●	1	6	55	3	10,510
05WHMB0100-TH	●		10	55	3	14,280
10WHMB0100-TH	●		15	55	3	18,360
15WHMB0100-TH	●		20	60	3	21,420
20WHMB0100-TH	●		24	65	3	24,690
25WHMB0100-TH	●		28	65	3	27,140
30WHMB0100-TH	●	1.01	33	70	3	29,580
03WHMB0101-TH	□		6	55	3	—
05WHMB0101-TH	□		10	55	3	—
10WHMB0101-TH	□		16	55	3	—
20WHMB0101-TH	□		25	65	3	—
30WHMB0101-TH	□		35	75	3	—
03WHMB0102-TH	□	1.02	6	55	3	—
05WHMB0102-TH	□		10	55	3	—
10WHMB0102-TH	□		16	55	3	—
20WHMB0102-TH	□		25	65	3	—
30WHMB0102-TH	□		35	75	3	—
03WHMB0103-TH	□	1.03	6	55	3	—
05WHMB0103-TH	□		10	55	3	—
10WHMB0103-TH	□		16	55	3	—
20WHMB0103-TH	□		25	65	3	—
30WHMB0103-TH	□		35	75	3	—
03WHMB0105-TH	●	1.05	6	55	3	10,510
05WHMB0105-TH	●		10	55	3	14,280
10WHMB0105-TH	●		16	55	3	18,360
15WHMB0105-TH	●		20	60	3	21,420
20WHMB0105-TH	●		25	65	3	24,690
25WHMB0105-TH	●		30	70	3	27,140
30WHMB0105-TH	●	1.1	35	75	3	29,580
03WHMB0110-TH	●		6	55	3	10,510
05WHMB0110-TH	●		11	55	3	14,280
10WHMB0110-TH	●		17	55	3	18,360
15WHMB0110-TH	●		22	60	3	21,420
20WHMB0110-TH	●		26	65	3	24,690
25WHMB0110-TH	●	1.11	32	70	3	27,140
30WHMB0110-TH	●		37	75	3	29,580
03WHMB0111-TH	□		6	55	3	—
05WHMB0111-TH	□		11	55	3	—
10WHMB0111-TH	□		18	60	3	—
20WHMB0111-TH	□		28	70	3	—
30WHMB0111-TH	□		38	75	3	—

商品コード Item code	在庫 Stock	寸法 Size (mm)				希望小売 価格(円) Suggested retail price(¥)
		直径 Tool dia. Dc	溝長 Flute length l	全長 Overall length L	シャンク径 Shank dia. Ds	
03WHMB0112-TH	□	1.12	6	55	3	—
05WHMB0112-TH	□		11	55	3	—
10WHMB0112-TH	□		18	60	3	—
20WHMB0112-TH	□		28	70	3	—
30WHMB0112-TH	□		38	75	3	—
03WHMB0113-TH	□	1.13	6	55	3	—
05WHMB0113-TH	□		11	55	3	—
10WHMB0113-TH	□		18	60	3	—
20WHMB0113-TH	□		28	70	3	—
03WHMB0115-TH	●	1.15	6	55	3	10,510
05WHMB0115-TH	●		11	55	3	14,280
10WHMB0115-TH	●		18	60	3	18,360
15WHMB0115-TH	●		23	60	3	21,420
20WHMB0115-TH	●		28	70	3	24,690
25WHMB0115-TH	●		33	70	3	27,140
30WHMB0115-TH	●	1.2	38	75	3	29,580
03WHMB0120-TH	●		6	55	3	10,510
05WHMB0120-TH	●		12	55	3	14,280
10WHMB0120-TH	●		18	60	3	18,360
15WHMB0120-TH	●		23	60	3	21,420
20WHMB0120-TH	●		29	70	3	24,690
25WHMB0120-TH	●	1.21	35	75	3	27,140
30WHMB0120-TH	●		40	80	3	29,580
03WHMB0121-TH	□		7	55	3	—
05WHMB0121-TH	□		13	55	3	—
10WHMB0121-TH	□	1.22	20	60	3	—
20WHMB0121-TH	□		31	70	3	—
30WHMB0121-TH	□		42	80	3	—
03WHMB0122-TH	□		7	55	3	—
05WHMB0122-TH	□	1.23	13	55	3	—
10WHMB0122-TH	□		20	60	3	—
20WHMB0122-TH	□		31	70	3	—
30WHMB0122-TH	□		42	80	3	—
03WHMB0123-TH	□	1.23	7	55	3	—
05WHMB0123-TH	□		13	55	3	—
10WHMB0123-TH	□		20	60	3	—
20WHMB0123-TH	□		31	70	3	—
30WHMB0123-TH	□	1.23	42	80	3	—

メーカー再研磨、再コートは行っておりません。
Manufacturer regrinding/recoating is not possible.

●印：標準在庫品です。
●： Stocked Items.

□印：特定代理店在庫です。弊社営業へお問合せください。

□： Stocked by specified distributor. Contact with our sales department.