









■ ポジ

刃先仕様		適合ホルダ参照ページ										
ダイヤモンド全般		ダイヤモンド										
形状	型番	寸法 (mm)					角度	使用コーナ数	ダイヤモンド			
		IC	S	D1	RE	LE			KPD001	KPD010	KPD230	KPD250
勝手付きチップは左勝手(L)を示す												
		WBMT 060102L-SE	3.97	1.59	2.3	0.2	1.3	5°	1	●		
		WBMT 080202L-SE	4.76	2.38	2.3	0.2	1.6	10°	1	●		
		WBMT 060101L-NE	3.97	1.59	2.3	0.1	1.7	5°	1	●		
		060102L-NE				0.2	1.6			●		
		060104L-NE				0.4	1.6			●		
		WBMT 080202L-NE	4.76	2.38	2.3	0.2	2.1	10°	1	●		
		080204L-NE				0.4	2.1			●		
		WBMT 060101L	3.97	1.59	2.3	0.1	1.9	5°	1	●		
		060102L				0.2	1.9			●		
		060104L				0.4	1.9			●		
		WBMT 080202L	4.76	2.38	2.3	0.2	2.4	10°	1	●		
		080204L				0.4	2.3			●		
		WPMT 110202SE	6.35	2.38	2.8	0.2	2.1	-	1	●		
		WPMT 110202NE				0.2	2.7			●		
		WPMT 110202				0.2	3.1			●		
		SPGN 120304NE	12.70	3.18	-	0.4	3.6	-	1	●		
		SPGN 120304				0.4	4.2			●		
		TPGN 110301SE	6.35	3.18	-	0.1	2.6	-	1	●		
		110302SE				0.2	2.5			●		
		110304SE				0.4	2.4			●		
		TPGN 160301SE	9.525	3.18	-	0.1	2.6	-	1	●		
		160302SE				0.2	2.6			●		
		160304SE				0.4	2.4			●		
		TPGN 160304NE	9.525	3.18	-	0.4	3.2	-	1	●		
		160308NE				0.8	2.9			●		
		TPGN 110302	6.35	3.18	-	0.2	3.9	-	1	●		
		110304				0.4	3.7			●		
		110308				0.8	3.4			●		
		TPGN 160302	9.525	3.18	-	0.2	3.9	-	1	□		
		160304				0.4	3.7			●		
		160308				0.8	3.4			●		

・型番末尾のSEはスモールエッジ、NEはニューバリューエッジを示します。