



0~-0.03



$D_s \leq 6$: 0~-0.012
 $6 < D_s \leq 10$: 0~-0.015
 $10 < D_s \leq 18$: 0~-0.018
 $18 < D_s$: 0~-0.021

(mm)



2NKS



商品コード Item Code	在庫 Stock	寸法 Size (mm)				希望小売 価格(円) Suggested retail price(¥)
		外径 Tool Dia.	刃長 Flute Length	全長 Overall Length	シャンク径 Shank Dia.	
2NKS0.8	●	0.8	1.6	55	6	4,000
2NKS0.9	●	0.9	2	55	6	4,000
2NKS1	●	1	2.5	55	6	3,060
2NKS1.05	□	1.05	3	55	6	—
2NKS1.1	●	1.1	2.5	55	6	4,000
2NKS1.15	□	1.15	3	55	6	—
2NKS1.2	●	1.2	3	55	6	4,000
2NKS1.25	□	1.25	3	55	6	—
2NKS1.3	●	1.3	3	55	6	4,000
2NKS1.35	□	1.35	3	55	6	—
2NKS1.4	●	1.4	3	55	6	4,000
2NKS1.45	□	1.45	3	55	6	—
2NKS1.5	●	1.5	3.5	55	6	2,790
2NKS1.55	□	1.55	4	55	6	—
2NKS1.6	●	1.6	3.5	55	6	3,620
2NKS1.65	□	1.65	4	55	6	—
2NKS1.7	●	1.7	3.5	55	6	3,620
2NKS1.75	□	1.75	4	55	6	—
2NKS1.8	●	1.8	3.5	55	6	3,620
2NKS1.85	□	1.85	4	55	6	—
2NKS1.9	●	1.9	3.5	55	6	3,620
2NKS1.95	□	1.95	4	55	6	—
2NKS2	●	2	4	55	6	2,630
2NKS2.05	□	2.05	6	60	6	—
2NKS2.1	●	2.1	5	55	6	3,440
2NKS2.15	□	2.15	6	60	6	—
2NKS2.2	●	2.2	5	55	6	3,440
2NKS2.25	□	2.25	6	60	6	—
2NKS2.3	●	2.3	5	55	6	3,440
2NKS2.35	□	2.35	6	60	6	—
2NKS2.4	●	2.4	5	55	6	3,440
2NKS2.45	□	2.45	6	60	6	—
2NKS2.5	●	2.5	5	55	6	2,590
2NKS2.55	□	2.55	8	60	6	—
2NKS2.6	●	2.6	7	55	6	3,360
2NKS2.65	□	2.65	8	60	6	—
2NKS2.7	●	2.7	7	55	6	3,360
2NKS2.75	□	2.75	8	60	6	—
2NKS2.8	●	2.8	7	55	6	3,360
2NKS2.85	□	2.85	8	60	6	—
2NKS2.9	●	2.9	7	55	6	3,360
2NKS2.95	□	2.95	8	60	6	—
2NKS3	●	3	7	55	6	2,280
2NKS3.05	□	3.05	12	60	6	—
2NKS3.1	●	3.1	8	65	8	2,990
2NKS3.15	□	3.15	12	60	6	—
2NKS3.2	●	3.2	8	65	8	2,990
2NKS3.25	□	3.25	12	60	6	—
2NKS3.3	●	3.3	8	65	8	2,990
2NKS3.35	□	3.35	14	65	8	—
2NKS3.4	●	3.4	8	65	8	2,990
2NKS3.45	□	3.45	14	65	8	—
2NKS3.5	●	3.5	8	65	8	2,280

商品コード Item Code	在庫 Stock	寸法 Size (mm)				希望小売 価格(円) Suggested retail price(¥)
		外径 Tool Dia.	刃長 Flute Length	全長 Overall Length	シャンク径 Shank Dia.	
2NKS3.55	□	3.55	14	65	8	—
2NKS3.6	●	3.6	8	65	8	2,990
2NKS3.65	□	3.65	14	65	8	—
2NKS3.7	●	3.7	8	65	8	2,990
2NKS3.75	□	3.75	14	65	8	—
2NKS3.8	●	3.8	8	65	8	2,990
2NKS3.85	□	3.85	14	65	8	—
2NKS3.9	●	3.9	8	65	8	2,990
2NKS3.95	□	3.95	14	65	8	—
2NKS4	●	4	8	65	8	2,280
2NKS4.05	□	4.05	14	65	8	—
2NKS4.1	●	4.1	10	65	8	2,990
2NKS4.15	□	4.15	14	65	8	—
2NKS4.2	●	4.2	10	65	8	2,990
2NKS4.25	□	4.25	14	65	8	—
2NKS4.3	●	4.3	10	65	8	2,990
2NKS4.35	□	4.35	14	65	8	—
2NKS4.4	●	4.4	10	65	8	2,990
2NKS4.45	□	4.45	14	65	8	—
2NKS4.5	●	4.5	10	65	8	2,280
2NKS4.55	□	4.55	16	65	8	—
2NKS4.6	●	4.6	10	65	8	2,990
2NKS4.65	□	4.65	16	65	8	—
2NKS4.7	●	4.7	10	65	8	2,990
2NKS4.75	□	4.75	16	65	8	—
2NKS4.8	●	4.8	10	65	8	2,990
2NKS4.85	□	4.85	16	65	8	—
2NKS4.9	●	4.9	10	65	8	2,990
2NKS4.95	□	4.95	16	65	8	—
2NKS5	●	5	10	65	8	2,280
2NKS5.05	□	5.05	16	65	8	—
2NKS5.1	●	5.1	12	65	8	2,990
2NKS5.15	□	5.15	16	65	8	—
2NKS5.2	●	5.2	12	65	8	2,990
2NKS5.25	□	5.25	16	65	8	—
2NKS5.3	●	5.3	12	65	8	2,990
2NKS5.35	□	5.35	16	65	8	—
2NKS5.4	●	5.4	12	65	8	2,990
2NKS5.45	□	5.45	16	65	8	—
2NKS5.5	●	5.5	12	65	8	2,280
2NKS5.55	□	5.55	16	65	8	—
2NKS5.6	●	5.6	12	65	8	2,990
2NKS5.65	□	5.65	16	65	8	—
2NKS5.7	●	5.7	12	65	8	2,990
2NKS5.75	□	5.75	16	65	8	—
2NKS5.8	●	5.8	12	65	8	2,990
2NKS5.85	□	5.85	16	65	8	—
2NKS5.9	●	5.9	12	65	8	2,990
2NKS5.95	□	5.95	16	65	8	—
2NKS6	●	6	12	65	8	2,280
2NKS6.05	□	6.05	16	65	8	—
2NKS6.1	●	6.1	14	70	10	3,270
2NKS6.15	□	6.15	16	65	8	—

●印：標準在庫品です。●：Stocked Items。□印：特定代理店在庫です。弊社営業へお問い合わせください。□：Stocked by specified distributor. Contact with our sales department.