


自動調心ころ軸受

d 25 ~ 70 mm



主 要 寸 法 (mm)				基本定格荷重 (kN)		疲労限荷重 (kN)	許容回転速度 (min ⁻¹)		呼 び 番 号	
d	D	B	r (最小)	C_r	C_{0r}	C_u	グリース 潤滑	油潤滑	円筒穴	テーパー穴
25	52	18	1	56.8	48.1	3.90	7 000	9 300	22205RHR	22205RHRK
30	62	20	1	76.6	65.9	5.30	5 900	7 900	22206RHR	22206RHRK
	72	19	1.1	74.2	62.7	4.80	5 200	7 000	21306RH	21306RHK
35	72	23	1.1	100	88.7	7.75	5 000	6 700	22207RHR	22207RHRK
	80	21	1.5	86.8	75.8	5.90	4 500	6 000	21307RH	21307RHK
40	80	23	1.1	114	102	9.55	4 500	6 000	22208RHR	22208RHRK
	90	23	1.5	105	92.8	7.55	4 100	5 500	21308RH	21308RHK
	90	33	1.5	170	152	11.8	4 100	5 500	22308RHR	22308RHRK
45	85	23	1.1	119	110	10.2	4 200	5 600	22209RHR	22209RHRK
	100	25	1.5	132	121	9.95	3 600	4 900	21309RH	21309RHK
	100	36	1.5	208	183	13.8	3 700	4 900	22309RHR	22309RHRK
50	90	23	1.1	128	122	12.7	3 900	5 200	22210RHR	22210RHRK
	110	27	2	157	147	12.0	3 300	4 400	21310RH	21310RHK
	110	40	2	255	237	17.5	3 300	4 500	22310RHR	22310RHRK
55	100	25	1.5	154	144	15.0	3 400	4 600	22211RHR	22211RHRK
	120	29	2	180	165	13.0	3 000	4 100	21311RH	21311RHK
	120	43	2	296	264	21.1	3 000	4 000	22311RHR	22311RHRK
60	110	28	1.5	190	181	18.7	3 100	4 200	22212RHR	22212RHRK
	130	31	2.1	210	193	15.1	2 800	3 700	21312RH	21312RHK
	130	46	2.1	354	334	24.9	2 800	3 700	22312RHR	22312RHRK
65	120	31	1.5	222	211	20.7	2 900	3 800	22213RHR	22213RHRK
	140	33	2.1	242	232	19.8	2 600	3 400	21313RH	21313RHK
	140	48	2.1	382	360	30.8	2 600	3 400	22313RHR	22313RHRK
70	125	31	1.5	233	222	24.4	2 700	3 600	22214RHR	22214RHRK
	150	35	2.1	268	260	21.6	2 400	3 200	21314RH	21314RHK
	150	51	2.1	435	413	35.0	2 400	3 200	22314RHR	22314RHRK

〔備考〕 上表の軸受に適用する標準保持器形式は、小解説の表5をご参照ください。