












ピン規格

形状	型番	在庫	寸法(mm)						角度		備考
			A	B	C	D	E	F	α	θ	
	LL -03N	●	7.8	6.3							
	-03SN	●	11.1	8.9	-	-	-	-	-	-	
	-03TN	●	8.3	8.9							
	LL -05C	●	10.7	11.7					12°		
	-1CN	●	13.0	13.3	-	-	-	-	14°	-	
	-2C	●	18.8	17.6					14°		
	LL -1K	●	10.0	12.0							
	-1N	●	10.3	12.0							
	-1DN	●	12.3	12.0							
	-2K	●	13.3	13.2							
	-2N	●	13.5	13.0	-	-	-	-	-	-	
	-3K	●	16.0	14.8							
	-3N	●	16.4	13.0							
	-4	●	16.4	14.7							
	-5N	●	17.1	16.7							
-6	●	20.7	21.0								
	LP -2S	●	3.65	20.0	-	-	-	-	-	-	
	-6S	●	3.65	25.0	-	-	-	-	-	-	
	LPA -11	●		11.0							
	-13	●	2.8	13.0	4.2	-	-	-	-	60°	
	-17	●		17.0							
	LPF -11	●		11.0							
	-1113	●	2.5	13.0	3.5	-	-	-	-	60°	
	-1117	●		17.0							
	-13	●	3.8	13.0	5.5	-	-	-	-		
-17	●		17.0								
	PP -4	●	4.6	14.0	5.5	-	3.0	-	-	-	
	TS -3S	●	M5X0.8	15.0	3.60	-	2.0	-	-	-	
	WP -1S	●	M5X0.8	18.0	3.65	-	-	-	-	-	
	5X15	●		15.0	5.0	-	-	-	-	-	
	WP 5X11	●	M5X0.8	10.5	5.0	-	2.0	-	-	-	
	LSP -1	●	5.0	5.3							
	-2	●	6.5	5.6							
	-3	●	8.25	7.9							
	-4	●	9.5	10.0							
	LSP -2K	●	5.1	5.2							
-3K	●	6.7	5.7								
	P -03	●	2.8	1.95	-	-	-	-	-	-	
	-03S	●	3.5	1.95	-	-	-	-	-	-	

チップ材種 旋削チップ CBNダイヤモンド

外径

スモールツール

内径

溝入れ

突切り

ねじ切り

ドリル

ソリッドツール

ミリング

ターニング機器

イシオマシン

部品

技術資料

SPKセクション

索引

●：標準在庫