

## スリーブ(スタンダード型)

シャンク径  $\phi 15.875 \sim 19.05$

### NBH型




図-1

シャンク径  $\phi 20 \sim 32$

### NBH型




図-2

## ホルダ寸法

ホルダ形状	コードNo.	ホルダ品番	在庫	寸法(mm)								クランプスクリュー			レンチ
				$\phi d$	$\phi D_1$	$\phi D_2$	$h$	$L_1$	$L_2$	$L_3$	$L_4$	①	②	③	
図1	5631403	NBH02015H	●	2.0	15.875	15	15	100	10	—	9.0	SS0406F	SS0406F	—	LW-2
	5702915	02515H	●	2.5											
	5631411	03015H	●	3.0											
	5586110	03515H	●	3.5											
	5586128	04015H	●	4.0					15	15					
	5585997	04515H	●	4.5											
	5585989	05015H	●	5.0					20	20					
	5585971	06015H	●	6.0											
	5585963	08015H	●	8.0	SS0403F	SS0403F	SS0403F								
	5631429	NBH02016H	●	2.0	16	15	15	100	10	—	9.0	SS0406F	SS0406F	—	
	5702899	02516H	●	2.5											
	5631437	03016H	●	3.0											
	5586102	03516H	●	3.5											
	5586094	04016H	●	4.0					15	15					
	5586086	04516H	●	4.5											
	5586078	05016H	●	5.0					20	20					
5586060	06016H	●	6.0	SS0403F							SS0403F	SS0403F			
5774195	07016H	●	7.0	19.05	18	18	125	10	—	11.0	SS0408F	SS0408F	—		
5586052	08016H	●	8.0												
5631445	NBH02019K	●	2.0												
5702907	02519K	●	2.5												
5631452	03019K	●	3.0												
5586045	03519K	●	3.5												
5586037	04019K	●	4.0					15	15						
5586029	04519K	●	4.5												
5586011	05019K	●	5.0	20	20										
5586003	06019K	●	6.0			SS0404F	SS0404F	SS0404F							
5774203	07019K	●	7.0	SS0403F	SS0403F	SS0403F									
5586227	08019K	●	8.0												
5586219	10019K	●	10.0												

※ボーリングバー（モーグルバー）も取り付け可能です。